

### PERFORMANCE

#### Processor

Intel® Core™ i7-1255U, 10C (2P + 8E) / 12T, P-core 1.7 / 4.7GHz, E-core 1.2 / 3.5GHz, 12MB

#### Graphics

Integrated Intel Iris® Xe Graphics

#### Chipset

Intel SoC Platform

#### Memory

16GB Soldered LPDDR5-4800

#### Memory Slots

Memory soldered to systemboard, no slots, dual-channel

#### Max Memory

16GB soldered memory, not upgradable

#### Storage

512GB SSD M.2 2242 PCIe® 4.0x4 NVMe®

#### Storage Support

One drive, up to 1TB M.2 2242 SSD

#### Storage Slot

One M.2 2280 PCIe Gen 4x4 slot, supports M.2 2242/2280 SSD

#### Card Reader

MicroSD Card Reader

#### Optical

None

#### Audio Chip

High Definition (HD) Audio, Realtek® ALC3306 codec

#### Speakers

Stereo speakers, 2W x2 (woofers), 2W x2 (tweeters), optimized with Dolby® Atmos®, Smart Amplifier (AMP)

#### Camera

FHD 1080p & IR with Privacy Shutter

#### Microphone

2x, Array

#### Battery

Integrated 71Wh

#### Max Battery Life

2.2K IPS model:

MobileMark® 2018@200nits: 11.5 hr

Local video (1080p) playback@150nits: 16.5 hr

#### Power Adapter

65W USB-C® (3-pin)

### DESIGN

#### Display

14" 2.2K (2240x1400) IPS 300nits Glossy, 100% sRGB, TÜV Low Blue Light, Dolby Vision™, Glass, Touch

#### Touchscreen

10-point Multi-touch

#### Keyboard

Backlit, English (US)

#### Case Color

Stone Blue

#### Surface Treatment

Aluminium CNC

#### Case Material

Aluminium (Top), Aluminium (Bottom)

#### Pen

Pen Upgradable

#### Dimensions (WxDxH)

316.66 x 220.25 x 17.35 mm (12.47 x 8.67 x 0.68 inches)

#### Weight

Around 1.45 kg (3.20 lbs)

### SOFTWARE

#### Operating System

Windows® 11 Home 64, English

#### Bundled Software

Office Trial

### CONNECTIVITY

#### Ethernet

None

#### WLAN + Bluetooth®

Wi-Fi® 6E 11ax, 2x2 + BT5.1

#### WWAN

None

#### NFC

None

#### Standard Ports

- 1x USB 3.2 Gen 1 (Always On)
- 1x HDMI® 2.0
- 1x microSD card reader
- 1x Headphone / microphone combo jack (3.5mm)
- 2x Thunderbolt™ 4 (support data transfer, Power Delivery 3.0, and DisplayPort™ 1.4)

#### Monitor Cable

None

### SECURITY & PRIVACY

#### Security Chip

Firmware TPM 2.0

#### Fingerprint Reader

Touch Style

#### Other Security

- Camera privacy shutter
- IR camera for Windows® Hello

### SERVICE

#### Base Warranty

1-year, Depot

#### Included Upgrade

None

### ACCESSORIES

#### Bundled Accessories

None

### CERTIFICATIONS

#### Green Certifications

- EPEAT™ Silver
- ENERGY STAR® 8.0
- ErP Lot 3
- RoHS compliant

#### Other Certifications

- Intel® Evo™ Platform
- TÜV Rheinland® Low Blue Light (Hardware Solution)

### MODEL

TopSeller : No

Announce Date : 2022-04-06

EAN / UPC / JAN : 196379312742

End of Support : 2028-05-05



intel

## Premium Care - Advanced Support from Real People. Real Fast.



### REAL PERSON

Choose how you want to reach us - through the phone, chat or email - our expert technicians will take care of you.



### REAL FAST

Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If needed, our team will schedule an onsite visit for the next business day.



### HASSLE FREE

'Getting started' and 'how-to' assistance for hardware and software. Easy solutions that are simple to reach - that's how Premium Care delivers you the ideal support experience.



### PC HEALTH CHECK

Free annual PC Health Check that allows our experts to spot issues before you do so they can resolve them quickly and help you avoid PC problems.

## Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

## Base Warranty – Included with the systems you purchase, default 1- or 3-year coverage window.

## Warranty Extensions & Upgrades – Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

## Recommended Accessories



### Lenovo USB-C 65W AC Adapter (UL)

GX20P92530

Lenovo AC Adapter offers fast and efficient charging. Keep one in the office, one at home, and another in your case for convenient access to power. Just plug it into an available outlet to deliver AC power to the comp...



### Lenovo 65W USB-C DC Travel Adapter

40AK0065WW

Power up and stay productive on the road with this DC Travel adapter. Lenovo 65W USB-C DC Travel Adapter is the universal DC adapter, providing 65W power via USB-C for outdoor use.

For a full list of accessories and services, please visit:  
<https://smartfind.Lenovo.com>

Lenovo

PSREF  
Product Specifications  
Reference