

## PERFORMANCE

### Processor

Intel® Core™ i3-1115G4 (2C / 4T, 3.0 / 4.1GHz, 6MB)

### Graphics

Integrated Intel UHD Graphics

### Chipset

Intel SoC Platform

### Memory

4GB Soldered DDR4-2666 + 4GB SO-DIMM DDR4-2666

### Memory Slots

One memory soldered to systemboard, one DDR4 SO-DIMM slot, dual-channel capable

### Max Memory

Up to 12GB (4GB soldered + 8GB SO-DIMM) DDR4-2666 offering

### Storage

256GB SSD M.2 2242 PCIe® 3.0x4 NVMe®

### Storage Support

Model with 35Wh battery: up to two drives, 1x 2.5" HDD + 1x M.2 SSD

- 2.5" HDD up to 1TB
- M.2 2242 SSD up to 512GB
- M.2 2280 SSD up to 1TB

### Storage Slot

Model with 35Wh battery: one 2.5" drive slot + one M.2 slot

- One 2.5" drive slot, supports 2.5" SATA HDD
- One M.2 2280 PCIe Gen 3x4 slot, supports M.2 2242/2280 SSD

### Card Reader

4-in-1 Card Reader

### Optical

None

### Audio Chip

High Definition (HD) Audio

### Speakers

Stereo speakers, 1.5W x2, Dolby® Audio™

### Camera

HD 720p with Privacy Shutter

### Microphone

2x, Array

### Battery

Integrated 35Wh

### Max Battery Life

MobileMark® 2014: 5.5 hr (35Wh)

### Power Adapter

65W Round Tip (2-pin, Wall-mount)

## DESIGN

### Display

15.6" HD (1366x768) TN 220nits Anti-glare, Touch

### Touchscreen

10-point Multi-touch

### Keyboard

Non-backlit, English

### Case Color

Almond

### Surface Treatment

IMR (In-Mold Decoration by Roller)

### Case Material

PC + ABS (Top), PC + ABS (Bottom)

### Dimensions (WxDxH)

362.2 x 253.4 x 19.9 mm (14.26 x 9.98 x 0.78 inches)

### Weight

Around 1.7 kg (3.75 lbs)

## SOFTWARE

### Operating System

Windows® 11 Home in S mode, English

### Bundled Software

Office Trial

## CONNECTIVITY

### Ethernet

None

### WLAN + Bluetooth®

Wi-Fi® 6 11ax, 2x2 + BT5.0

### Standard Ports

- 1x USB 2.0
- 2x USB 3.2 Gen 1
- 1x HDMI® 1.4
- 1x Card reader
- 1x Headphone / microphone combo jack (3.5mm)
- 1x Power connector

## SECURITY & PRIVACY

### Security Chip

Firmware TPM 2.0

### Fingerprint Reader

None

### Other Security

Camera privacy shutter

## SERVICE

### Base Warranty

1-year, Depot

### Included Upgrade

None

## CERTIFICATIONS

### Green Certifications

- ErP Lot 3
- RoHS compliant

## MODEL

TopSeller : No

Announce Date : 2021-11-15

EAN / UPC / JAN : 196378822709

End of Support : 2027-02-08



## Premium Care - Advanced Support from Real People. Real Fast.



### REAL PERSON

Choose how you want to reach us - through the phone, chat or email - our expert technicians will take care of you.



### REAL FAST

Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If needed, our team will schedule an onsite visit for the next business day.



### HASSLE FREE

'Getting started' and 'how-to' assistance for hardware and software. Easy solutions that are simple to reach - that's how Premium Care delivers you the ideal support experience.



### PC HEALTH CHECK

Free annual PC Health Check that allows our experts to spot issues before you do so they can resolve them quickly and help you avoid PC problems.

## Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

## Base Warranty – Included with the systems you purchase, default 1- or 3-year coverage window.

## Warranty Extensions & Upgrades – Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

## Recommended Accessories



### ThinkPad Hybrid USB-C with USB-A Dock (American Standard Plug Type B)

40AF0135US

The ThinkPad Hybrid USB-C with USB-A Dock expands the capabilities of most any laptop, new or old, making it perfect for enterprise customers with mixed-PC or shared-desk environments. Featuring enterprise-class manag...

## Recommended Services

BEST	3Y Premium Care with Onsite upgrade from 1Y Courier/Carry-in (5WS0T73714)
GOOD	3Y Courier/Carry-in upgrade from 1Y Courier/Carry-in (5WS0K75663)

For a full list of accessories and services, please visit: <https://smartfind.Lenovo.com>

**Lenovo**

**PSREF**  
Product Specifications  
Reference