



## World's first 16" 4K OLED HDR 16:10 display

Your creations demand visual perfection, and ProArt Studiobook 16 OLED delivers it with a 4K OLED HDR display that's in a class of its own. This display delivers truly photorealistic visuals that are VESA DisplayHDR™ 500 True Black certified for ultra-high contrast and deep blacks, and the 100% DCI-P3 industry-standard color gamut ensures you're seeing as many vivid, true-to-life colors as possible. For delivering precise color accuracy, this remarkable display is Calman verified, PANTONE® Validated, and has a Delta-E color-accuracy value of less than 2.



## Fire up your imagination

ProArt Studiobook 16 OLED is powered by up to an Intel® Core™ i9 11900H processor, an eight-core processor that takes your creativity to another level, with the fastest ever performance that enables super-smooth and responsive multitasking. ProArt Studiobook 16 OLED can easily handle complex multithreaded applications, multi-layered video editing, and 3D rendering.

## Fast graphics, stable drivers

Professional-level 3D graphics processing power is provided by NVIDIA® GeForce® RTX™ 3060 graphics, which is based on Ampere, NVIDIA®'s second-generation RTX™ architecture. Whether you're working on complex 3D scenes, 8K video, or high-quality livestreaming, ProArt Studiobook 16 OLED is more than equal to the task thanks to the GPU's enhanced core architecture and fast GDDR6 memory. For outstanding driver stability, we use NVIDIA® Studio Drivers to ensure maximum performance, rock-solid reliability, and wide software compatibility.



## Make magic happen with ASUS Dial

Discover new ways to work with the brand-new and exclusive ASUS Dial, an intuitive physical controller that gives you instant and precise fingertip control over parameters in your creative apps. You can easily change brush size, change saturation, adjust layer opacity, or rapidly undo actions. You can also adjust screen brightness and volume, or vertical scroll to make your creative workflow smoother. There are over 70 functions available to help smooth your creative workflow. ASUS Dial is currently compatible with four Adobe apps: Photoshop, Premiere Pro, Photoshop Lightroom Classic, and After Effects. It's fully customizable — and there are more compatible apps on the way!



## ProArt Studiobook 16 OLED (H7600HM)

- Windows 11 Pro
- Up to Intel® Core™ i9 11900H
- NVIDIA® GeForce® RTX™ 3060
- 1 x PCIe® 4.0 x4 NVMe M.2 slots +1 x PCIe® 3.0 x4 NVMe M.2 slots support up to 4 TB capacity
- 2 x SO-DIMM slots, support for up to 64GB 3200 MHz DDR4 memory
- 16" 4K OLED HDR 16:10 display
- ASUS Dial for intuitive and precise control
- Touchpad with 3 function buttons and support for 1024-level stylus
- Next-gen technology: Thunderbolt™ 4, WiFi 6, HDMI 2.1, SD Express 7.0
- ProArt Creator Hub enables full creative potential to be achieved

## ProArt Studiobook 16 OLED



H7600

CPU	Intel® Core™ i9 11900H processor Intel® Core™ i7 11800H processor
Operating System	Windows 11 Pro (ASUS recommends Windows 11 Pro for business) Windows 11 Home
On board Memory	32GB / 64GB 3200 MHz DDR4 memory, with 2 x SO-DIMM slots
Memory Max.	64GB
Storage	1 x PCIe® 4.0 x4 NVMe M.2 slots +1 x PCIe® 3.0 x4 NVMe M.2 slots support up to 2+2TB capacity, CPU attached Gen 4 SSD with up to 7000 MB transfer speed
EMMC / ISSD	N/A
Display	16" 4K OLED HDR (3840x2400) slim-bezel NanoEdge 16:10 display 16" 120Hz 2.5K (2560x1600) IPS wide-view 16:10 display
Touchpad	Precision touchpad (PTP) technology supports up to four-finger gestures
External Video Display Modes	HDMI 2.1
GPU	NVIDIA® GeForce® RTX™ 3060 graphics
Video Memory	N/A
Video Camera	HD IR Web Camera with webcam shield
Fingerprint Sensor	Yes
Wireless	Intel® WiFi 6 (802.11ax) & Bluetooth® 5.2
LAN	RJ45 LAN port
Card Reader	SD Express 7.0 card reader
Interface	1 x Thunderbolt™ 4 USB-C® (up to 40Gbps) 1 x Type-C® USB 3.2 Gen 2 (up to 10Gbps) 2 x USB 3.2 Gen 2 (up to 10Gbps) 1 x HDMI 2.1 1 x SD Express 7.0 card reader 1 x 3.5mm combo audio jack 1 x Gigabit RJ45 LAN port
Audio	Certified by Harman Kardon, Premium ESS® Sabre HiFi DAC with hi-res audio, smart amplifier technology, 4 built-in microphones
Weight (Kg)	Approx. 2.4kg
Dimension (cm)	36.2(W) x 26.4(D) x 19.6(H) cm
AC Adapter	240W AC adapter (Output: 20V DC, 12A, 240W) (Input: 100-240V AC, 50/60Hz universal)
Battery	90Whs, 4-cell lithium-polymer battery
Replaceable Battery	No
Keyboard Type	Full-size backlit keyboard with Num-key 1.4mm key-travel
Security	HDD User Password Protection and Security BIOS Booting User Password Protection Trusted Platform Module (TPM) 2.0 BIOS setup user password Security Lock McAfee LiveSafe™ 30-day trial Fingerprint sensor integrated with Power Key IR webcam with Windows Hello support
Warranty	2 years (depends on countries)
Price	Starting at \$2199

## ProArt Studiobook 16 OLED (H7600)

### Born for Creative Pros



Up to Intel® Core™ i9 processor



NVIDIA® GeForce® RTX™ 3060



16" 4K OLED HDR 16:10 display



ASUS Dial

Turn your creative vision into reality with the ProArt Studiobook 16 OLED studio laptop. With a certified color-accurate 16-inch 4K OLED HDR 16:10 display, up to a breathtakingly powerful Intel® Core™ i9 processor, pro-grade NVIDIA® GeForce® RTX™ 3060 graphics, huge amounts of memory, advanced ultrafast storage, superb I/O connectivity, and ultra-precise fingertip control over your creative apps with the groundbreaking new ASUS Dial, ProArt Studiobook 16 OLED is simply the best creator laptop we've ever made.



Your content, curated.