

# ZU920TST

Ultra bright professional installation laser projector



- **9800 lumen DuraCore laser projector - Ultra bright for immersive installations**
- **Full motorized lens shift - Ideal for a simple set up**
- **Large zoom range - Motorized zoom expands placement opportunities**
- **Long life - Delivers 30,000 hours of virtually maintenance-free operation**



At 9800 lumens with 4K and HDR compatibility, the ZU920TST features a dust-resistant IP5X certified optical engine for 24/7 operation capabilities, offering true maintenance-free projection for up to 30,000 hours of powerful performance in Eco mode. Other features include a motorized zoom and focus, full motorized lens shift, and built-in dual 10W speakers.

High brightness, color precision and quiet operation, along with a short throw lens make this projector the ideal solution for a variety of end-user scenarios and professional environments, such as short throw digital signage, edge-blending and projection mapping, simulation and immersive installations.

## Specifications

UPC: 796435 44 590 4, EAN: 5055387666047, Colour: black

<b>Display/image</b>	
Display technology	DLP
Resolution	WUXGA (1920x1200)
Brightness	9,800 lumens
ANSI brightness	8,200
Contrast ratio	3,000,000:1
Contrast ratio - full on/off	1,100:1
Native aspect ratio	16:10
Aspect ratio - compatible	4:3,16:9,16:10
Keystone correction - horizontal	30°
Keystone correction - vertical	30°
Uniformity	95%
Screen size	1.27m ~ 7.62m (50" ~ 300") diagonal
<b>Lamp info</b>	
Light source type	DuraCore Laser
LASER life	30,000 hours
<b>Optical</b>	
Throw ratio	0.65:1 ~ 0.75:1
Projection distance (m)	0.7m - 16.6m
Zoom	1.15
Zoom type	Motorised
Focal length (mm)	9.69-11.19
Lens shift	Vertical: +/-55%, Horizontal: +/-25%
Native offset	50%
Lens shift	Yes - <a href="#">{{downloads_link}}</a>
<b>Connectivity</b>	
Connections	<p><b>Inputs</b> 1 x HDBaseT, 1 x HDMI 2.0, 1 x HDMI 2.0, 1 x VGA, 1 x 3D sync, 1 x Audio 3.5mm</p> <p><b>Outputs</b> 1 x HDMI 2.0, 1 x 3D sync, 1 x USB-A power 1.5A, 1 x Audio 3.5mm</p> <p><b>Control</b> 1 x 12V trigger, 1 x Wired remote, 1 x RJ45, 1 x RS232</p>
LAN - wireless networking	No
<b>General</b>	
Noise level (typical)	36dB
Noise level (max)	38dB
Security	Security bar, Kensington Lock
OSD / display languages	10 languages: English, French, German, Italian, Portuguese, Russian, Chinese (simplified), Spanish, Chinese (traditional)
24/7 operation	Yes
360° operation	Yes
Remote control	Backlit ProAV remote
Speaker count	2
Watts per speaker	10W
<b>Networking</b>	
LAN - wireless networking	No
LAN	Yes
<b>Power</b>	
Power supply	AC 90 - 264V 50/60 Hz
Power consumption (min)	260W
Power consumption (max)	505W
<b>Weight and dimensions</b>	
Dimensions (W x D x H) mm	480 x 376 x 144
Gross weight	17.5 kg
Net weight	14 kg

