

ZU920T

Ultra bright professional laser projector



- **9800 lumen DuraCore laser projector - Ultra bright for immersive installations**
- **Full motorized lens shift - Ideal for a simple set-up**
- **Large zoom range - Motorized zoom expands placement opportunities**
- **Long life - Delivers 30,000 hours of virtually maintenance-free operation**



At 9,800 lumens with 4K and HDR compatibility, the ZU920T features a dust-resistant IP5X certified optical engine for 24/7 operation capabilities, offering true maintenance-free projection for up to 30,000 hours of powerful performance in Eco mode. Other features include a motorized zoom and focus, full motorized lens shift and built-in dual 10W speakers.

High brightness, color precision and quiet operation make this projector the ideal solution for a variety of end-user scenarios and professional environments, such as edge-blending and projection mapping, simulation, and immersive installations.

Specifications

UPC: 796435 44 589 8, EAN: 5055387666030, Colour: Black

Display/image	
Display technology	DLP
Resolution	WUXGA (1920x1200)
Brightness	9,800 lumens
ANSI brightness	8,200
Contrast ratio	3,000,000:1
Contrast ratio - full on/off	1,100:1
Native aspect ratio	16:10
Aspect ratio - compatible	4:3,16:9,16:10
Keystone correction - horizontal	30°
Keystone correction - vertical	30°
Uniformity	95%
Screen size	50" ~ 300" diagonal
Lamp info	
Light source type	DuraCore Laser
LASER life	30,000 hours
Optical	
Throw ratio	1.25:1 ~ 2:1
Projection distance	52.36" - 514.17"
Zoom	1.6
Zoom type	Motorised
Focal length (mm)	18.72-29.59
Lens shift	Vertical: +/-55%, Horizontal: +/-25%
Native offset	50%
Lens shift	Yes - {{downloads_link}}
Connectivity	
Connections	Inputs 1 x HDBaseT, 2 x HDMI 2.0, 1 x VGA, 1 x 3D sync, 1 x Audio 3.5mm Outputs 1 x HDMI 2.0, 1 x 3D sync, 1 x USB-A power 1.5A, 1 x Audio 3.5mm Control 1 x 12V trigger, 1 x Wired remote, 1 x RJ45, 1 x RS232
LAN - wireless networking	No
General	
Noise level (typical)	36dB
Noise level (max)	38dB
Security	Security bar, Kensington Lock
OSD / display languages	10 languages: English, French, German, Italian, Portuguese, Russian, Chinese (simplified), Spanish, Chinese (traditional)
24/7 operation	Yes
360° operation	Yes
Remote control	Backlit ProAV remote
Speaker count	2
Watts per speaker	10W
Networking	
LAN - wireless networking	No
LAN	Yes
Power	
Power supply	AC 90 – 264V 50/60 Hz
Power consumption (min)	260W
Power consumption (max)	505W
Weight and dimensions	
Dimensions (W x D x H)	19.13" x 17.03" x 6.93"
Gross weight	38.58 lbs
Net weight	30.86 lbs

