

CLEANWIPE PRO WATERPROOF & ERGONOMIC KEYBOARDS

Model: SSWKSV101PRO

State-of-the-art Cleanwipe Pro Waterproof Keyboards from Seal Shield™, with a compact footprint perfect for any workspace. Washable, waterproof & dishwasher-safe keyboard is IPx8-certified & compatible with industrial-grade cleaners & disinfectants. Three Ergonomic Tilt Positions allows keyboard angle for optimal comfort, reducing wrist strain and repetitive strain injury. Two choices of Cleanwipe Pro latex-free silicone covers are available for purchase.

FEATURES:



100% Waterproof & Washable



Three Ergonomic Keyboard Tilt Positions - Inclined, Declined and Flat



IPx8-Certified



MagSeal™ Magnetic USB Connector for Convenient Connection and Cleaning



Supports USB 3.0 Connectivity



Easy Clean Key Lock Function (ALT+F12) for Easy Cleaning While Still Connected



LED Key Illumination on Caps Lock, Number Lock, Scroll Lock, and Key Lock



Designed to withstand Industrial-Grade Disinfectants



Compact footprint perfect for tight applications including mobile carts and exam rooms



SSWKSV101Pro

Silicone Cover Options



SSxKSV101PRO-FFSC



SSxKSV101PRO-KFSC

ADVANCED CLEANING CAPABILITIES

- Dishwasher-Safe
- Compatible with Spray & Wipe Disinfectant Products:
 - Clorox Healthcare®
 - Lysol®
 - PDI Products
 - Bleach, Ethanol, IPA, Quats, Citric Acid, & Hydrogen Peroxide, and Other Industrial-Grade Cleaners and Disinfectants



CLEANWIPE PRO WATERPROOF & ERGONOMIC KEYBOARDS**Model: SSWKSV101PRO****TECHNICAL DATA:**

Compatibility:	Windows 10 Version 1607 x64 (USB Models)
Construction:	ABS Plastic (Chiclet Style with Silicone Cover)
Net Dimensions L x W x H:	13.94 x 5.12 x 0.886in (354 x 130 x 22.5 mm)
Gross Dimensions:	14.25 x 5.6 x 1.2in (362 x 142 x 30.5 mm)
Key Layout:	99 Keys including 10 Keypad
Net Weight:	.66lb (.299kg)
Gross Weight:	.73lb (.331kg)
Connection Type:	6ft (1.83m) Long USB Cable with Magnetic Connector to Keyboard
Key Switch Force:	60 ± 15 gf
Key Switch Life Cycle:	8,000,000 keystrokes
Key Switch Type:	Chiclet Style with Scissor Mechanism
Keycaps Imaging Type:	Laser-Etched Keys
Key Illumination:	Caps Lock, Num. Lock, Keyboard Lock, Scroll Lock Keys,
Total Key Travel:	.08 in (2mm)
Operating Voltage:	+ 5VDC ± 5%
Storage Temperature:	-5° to 55° C
EMI - RFI:	Conforms to FCC Rules for Class B Computing Device
Waterproof/Dustproof Ratings:	IPx8, NEMA 4X
Safety, Regulatory and Environmental Compliance:	IPx8, FCC Class B, CE, RoHS, WEEE, WHQL, Industrie Canada (IC) ICES-003, RSS-210
RF Frequency:	13.56MHz and 125kHz and 134.2kHz2
Read Range:	Up to 5cm
Mount Compatibility:	VESA Mount 200 x 100mm Hold Pattern



Copyright© 2020, Seal Shield, LLC. All rights reserved. All other trademarks and trade names are those of their respective owners.