



5MP HD-TVI IR Bullet Camera with Included Junction Box

V5B1

2.8mm fixed lens, white housing



Features


- Supports up to 5MP @ 20FPS
- IR Distance: 98' (depending on scene reflection)
- DWDR
- 12VDC Operation (power supply not included)
- IP67 weather resistance
- NDAA Compliant*
- 5 year warranty



Camera Specifications	
Image Sensor	Progressive scan 1/2.7" CMOS
Resolution	5MP 2560 x 1936
Video Output	AHD/TVI/CVI/CVBS (*camera comes defaulted to HD-TVI)
Image System	PAL/NTSC
Electronic Shutter Speed	Auto; 1/50s~1/100000s(PAL);1/60s~1/100000s (NTSC)
Minimum Illumination	Color: 0.01lux @ F1.2(AGC ON); B/W: 0 lux @ IR ON
S/N Ratio	≥ 52dB (AGC OFF)
Function Control	OSD (UTC Control)
Day/Night	Yes
WDR	Yes
DNR	Yes
Gain Control	Auto
White Balance	ATW
Defog	No
BLC	Yes
LSC	Yes
Mirror	Yes
Sharpness	Yes
Smart IR	Yes
Image Setting	Yes
Defect Correction	Auto

Operating & Unit Specifications	
Power	12VDC (power supply not included)
Power Consumption	IR OFF ≤ 1W; IR ON ≤ 4W
Operating Temperature	-22°F - 122°F
Relative Humidity	10% ~ 90%
Unit Dimensions	6.6"(L) x 2.9"(W) x 2.9"(H)
Unit Weight	1.87lbs


Optional Accessories




PSW5
12VDC
Power Supply




PMT1
Pole Mount




CMT1
Corner Mount



CLTX1
Ceiling Mount
4" Extension



O5VLWMJ
Wall Mount



CLT2J
Ceiling Mount

NDAA COMPLIANT

*Products are in compliance with NDAA Section 889 Part B Guidelines