

### PERFORMANCE

#### Display Size

27"

#### View Area

596.7x335.7 mm

#### Panel

Vertical Alignment

#### Aspect Ratio

16:9

#### Resolution

1920x1080

#### Pixel Pitch

0.311x0.311 mm

#### Dot / Pixel Per Inch

81.72 dpi

#### View Angle (H / V)

178 / 178

#### Response Time

1 ms (MPRT) / 7 ms (Level 1) / 6 ms (Level 2) / 5 ms (Level 3) / 4 ms (Level 4)

#### Color Support

16.7 Million

#### Refresh Rate

165 Hz

#### Brightness

350 nits

#### Contrast Ratio

3000:1

#### Color Gamut

99% sRGB, 90% DCI-P3

#### Anti-glare

Yes

#### Curvature

None

#### Camera

None

#### Microphone

None

#### Speakers

3Wx2

#### Power Consumption (Typical / Maximum)

21W / 52W

#### Power Adapter

Integrated

#### Touchscreen

None

#### Smart System

None

### DESIGN

#### Stand

Tilt, Height Adjust Stand

#### Case Color

Raven Black

#### Side Bezel Width

2 mm

#### Dimensions with Stand (HxWxD)

529x614.1x239.2 mm / 20.83x24.18x9.42 inches

#### Weight (Including Stand)

5.8 kg / 12.8 lbs.

#### ThinkCentre® M Series Support

None

### CONNECTIVITY

#### USB Port

None

#### Video Connector

2x HDMI® 2.0, 1x DP 1.4

#### Network Connectivity

None

### SERVICE

#### Base Warranty

1-year

### CERTIFICATIONS

#### Environmental Certification

RoHS

#### Ergonomic Certification

Eyesafe® Display, TÜV Low Blue Light (Hardware solution), TÜV Rheinland® Eye Comfort

#### Sync Technology

AMD Radeon™ FreeSync™ Premium

### SOFTWARE

#### Operating System

Support Windows® 10, Windows 11

### ACCESSORIES

#### Video Cables

DP cable

### MODEL

#### Announce Date

: 2022-02-14

#### EAN /

UPC / : 0196119803929 / 196119803929 / None

#### JAN



## Premium Care - Advanced Support from Real People. Real Fast.



### REAL PERSON

Choose how you want to reach us - through the phone, chat or email - our expert technicians will take care of you.



### REAL FAST

Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If needed, our team will schedule an onsite visit for the next business day.



### HASSLE FREE

'Getting started' and 'how-to' assistance for hardware and software. Easy solutions that are simple to reach - that's how Premium Care delivers you the ideal support experience.



### PC HEALTH CHECK

Free annual PC Health Check that allows our experts to spot issues before you do so they can resolve them quickly and help you avoid PC problems.

## Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

**Base Warranty** – Included with the systems you purchase, default 1- or 3-year coverage window.

**Warranty Extensions & Upgrades** – Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.



**Lenovo**

**PSREF**  
Product Specifications  
Reference