



Lexmark CX730de

Color and Performance



Lexmark CX730de

The Lexmark CX730de is designed for performance, security, and ease of use for mid-to-large workgroups at speeds up to 42 pages per minute*. Single-pass two-sided scanning and a 7-inch (17.8 cm) tablet-like touchscreen make handling your tasks easy. Replacement cartridges with Unison™ Toner yield up to 22,000/10,500 black/color pages** to keep you going.

Robust, enduring quality

- ▶ Enjoy high-quality color output in a wide variety of environments—from back-office to retail to harsh manufacturing conditions.
- ▶ Intentionally engineered to last seven years or more with durable steel frames and long-life components.
- ▶ Unison™ Toner replacement cartridges yield up to 22,000/10,500 black/color pages**.

Make a statement with professional color

Enjoy the benefits of vibrant, professional-quality output allowing you to do more color printing in-house—saves time and money. Match corporate colors on marketing collateral and brand-sensitive text and graphics with PANTONE® calibration and Lexmark Named Color Replacement.



Always easy. Always intuitive.

- ▶ Large, tablet-like, button-free touchscreens help you intuitively complete every task, from the basic to the complex.

- ▶ Get into the flow with standard access to built-in MFP workflow solutions like Scan Center, an easy-to-use app that simplifies routing to multiple destinations simultaneously.
- ▶ Plus, you can add other Lexmark or third-party partner solutions that meet your specific business needs.

Secure by design

- ▶ Lexmark security features help keep your information safe—in the document, on the device, over the network and at all points in between.
- ▶ Always improving security, we now include a standard Trusted Platform Module***, which delivers authentication, system integrity checks, and cryptographic capabilities to create a unique digital system fingerprint.

Sustainability matters

- ▶ Designed for the circular economy.
- ▶ Automatic two-sided printing is standard, along with built-in energy-saving modes that help support ratings of EPEAT® Silver and ENERGY STAR® certified.
- ▶ The award-winning Lexmark Cartridge Collection Program (LCCP) and Lexmark Equipment Collection Program (LECP) minimize waste and support recycling (availability varies by country).

Power up with IoT

- ▶ Sophisticated, IoT-enabled printers are loaded with sensors that continuously monitor hundreds of data points.
- ▶ When you connect your device to Lexmark Cloud Services, you can optimize performance and uptime with additional features like predictive service and automatic supplies replenishment.


This is a Class A device according to international electromagnetic emissions standards (i.e. FCC Rules, EN 55022/EN 55032, etc.). Class A products are intended for use in non-residential/non-domestic environments. Use of a Class A product in residential/domestic environments may cause interference to radio communications and require corrective measures.

* Print speeds measured in accordance with ISO/IEC 24734 (ESAT). For more information see: www.lexmark.com/ISOspeeds.

** Average continuous black or continuous composite color (CMY) declared yield in one-sided (simplex) mode up to this number of pages in accordance with ISO/IEC 19798. Actual yield will vary considerably based upon many factors. See www.lexmark.com/yields for more information. In demonstration of circular economy principles, genuine Lexmark supplies with Unison™ Toner may contain components recovered from the Lexmark Cartridge Collection Program (LCCP).

*** The Trusted Platform Module (TPM) is not available in some countries.

Lexmark CX730de



- 1** Multifunction product with 7-inch (17.8 cm) touch screen
24.44 x 18.85 x 20.9 in.
621 x 479 x 533 mm
- 2** 550-Sheet tray with 100-sheet multipurpose feeder
Dimensions included as part of base model
- 3** 550-Sheet Tray
4.7 x 18.23 x 19 in.
119 x 463 x 483 mm
- 4** 550-Sheet Tray
4.7 x 18.23 x 19 in.
119 x 463 x 483 mm

- 5** 550-Sheet Tray
4.7 x 18.23 x 19 in.
119 x 463 x 483 mm
- 6** 550-Sheet Tray
4.7 x 18.23 x 19 in.
119 x 463 x 483 mm
- 7** Adjustable Stand
20.5 x 25.7 x 24.6 in.
521 x 653 x 625 mm
- 8** Convenience Stapler LV
3.23 x 4.29 x 4.77 in.

Standard
 Optional

P/N 47C9500	Hardware Lexmark CX730de
P/N 71C0H10	Supplies Lexmark CS730, 735, CX730 Black 22K Toner Cartridge
71C0H20	Lexmark CS/CX730 Cyan 10.5K Toner Cartridge
71C0H30	Lexmark CS/CX730 Magenta 10.5K Toner Cartridge
71C0H40	Lexmark CS/CX730 Yellow 10.5K Toner Cartridge
71C0W00	Lexmark CS/CX730, 735, C/XC4342, C4352 170K Waste Container
71C0Z10	Lexmark CS/CX730, 735, C/XC4342, C/XC4352 Black 150K Imaging Unit
71C0Z50	Lexmark CS/CX730, 735, C/XC4342, C/XC4352 Color (CMY) 150K Imaging Unit
71C10C0	Lexmark CS/CX730, 735 Cyan Return Program 5K Toner Cartridge
71C10K0	Lexmark CS/CX730, 735 Black Return Program 5K Toner Cartridge
71C10M0	Lexmark CS/CX730, 735 Magenta Return Program 5K Toner Cartridge
71C10Y0	Lexmark CS/CX730, 735 Yellow Return Program 5K Toner Cartridge
71C1HC0	Lexmark CS/CX730 Cyan Return Program 10.5K Toner Cartridge
71C1HK0	Lexmark CS730, 735, CX730 Black Return Program 22K Toner Cartridge
71C1HM0	Lexmark CS/CX730 Magenta Return Program 10.5K Toner Cartridge
71C1HY0	Lexmark CS/CX730 Yellow Return Program 10.5K Toner Cartridge

P/N 40C2100	Paper Handling 550-Sheet Tray
47C4500	Convenience Stapler
P/N 27X0400	Memory Options 500+ GB Hard Disk
57X0070	Removable Hard Disk Enclosure Kit
57X9528	Intelligent Storage Device (ISD)

P/N 57X0300	Application Solutions Contact Authentication Device
57X0301	Contactless Authentication Device
82S1203	IPDS License
82S1204	Bar Code License

P/N 1021294	Connectivity USB Cable (2-meter)
27X0823	MarkNet N8370 Wireless for CS720, CS725, CX725
27X6410	Lexmark MarkNet N8372 802.11 a/b/g/n/ac Wireless Print Server
37X6350	Analog Fax Card
57X7020	English Keyboard Kit
SPD0001	Surge Protective Device, 110-120V

P/N 40C2300	Furniture Adjustable Stand
-----------------------	--------------------------------------

Supports up to four optional 550-sheet trays.
 All measurements are shown as height x width x depth. For more information about supported configurations, refer to the Printer, Option and Stand Compatibility Guide at http://www.lexmark.com/publications/furniture_safety/
 IPDS License and Bar Code License require an Intelligent Storage Drive.

Product Specifications		Lexmark CX730de
Printing		
Display	Lexmark e-Task 7-inch (17.8 cm) color touch screen	
Print Speed	Up to: Black: 42 ppm ¹ (Letter) / Color: 42 ppm ¹ (Letter)	
Time to First Page	As fast as: Black: 6.4 seconds / Color: 7.0 seconds	
Print Resolution	Black: 1200 x 1200 dpi, 4800 CQ (2400 x 600 dpi) / Color: 4800 CQ (2400 x 600 dpi), 1200 x 1200 dpi	
Memory	Standard: 2048 MB / Maximum: 2048 MB	
Hard Disk	Intelligent Storage Drive available; Magnetic Hard Disk available	
Recommended Monthly Page Volume	1500 - 15000 pages ²	
Maximum Monthly Duty Cycle	Up to: 120000 pages per month ³	
Copying		
Copy Speed	Up to: Black: 42 cpm ¹ (Letter) / Color: 42 cpm ¹ (Letter)	
Time to First Copy	As fast as: Black: 6.7 seconds / Color: 7.3 seconds	
Scanning		
Scanner Type / ADF Scan	Flatbed scanner with ADF / DADF (single pass Duplex)	
A4/Ltr Duplex Scan Speed	Up to: Black: 80 / 84 sides per minute / Color: 80 / 84 sides per minute	
A4/Ltr Simplex Scan Speed	Up to: Black: 40 / 42 sides per minute / Color: 40 / 42 sides per minute	
ADF Paper Input Capacity	Up to: 100 pages 20 lb or 75 gsm bond	
Supplies⁴		
Laser Cartridge Yields	up to: 10,500 ⁵ -page Color (CMY) High Yield Cartridges / up to: 22,000 ⁵ -page Black High Yield Cartridge	
Imaging Unit Estimated Yield	Up to: 150000 pages, based on 3 average letter/A4-size pages per print job and ~ 5% coverage ⁶	
Cartridge(s) Shipping with Product	5,000 ⁵ -page (CMYK) Return Program Toner Cartridges ⁵	
Paper Handling		
Included Paper Handling	100-Sheet Multipurpose Feeder, Integrated Duplex, 300-Sheet Output Bin, 550-Sheet Input	
Optional Paper Handling	550-Sheet Tray	
Paper Input Capacity	Up to: Standard: 650 pages 20 lb or 75 gsm bond / Maximum: 2850 pages 20 lb or 75 gsm bond	
Paper Output Capacity	Up to: Standard: 300 pages 20 lb or 75 gsm bond / Maximum: 300 pages 20 lb or 75 gsm bond	
Media Types Supported	Vinyl Labels, Banner Paper, Paper Labels, Card Stock, Plain Paper, Envelopes, Refer to the Paper & Specialty Media Guide	
Media Sizes Supported	A6, Oficio, 7 3/4 Envelope, 9 Envelope, JIS-B5, A4, Legal, A5, Letter, B5 Envelope, Statement, C5 Envelope, Executive, Universal, DL Envelope, Folio, 10 Envelope	
General Information⁷		
Standard Ports	Gigabit Ethernet (10/100/1000), Front USB 2.0 Specification Hi-Speed Certified port (Type A), Rear Hi-Speed USB Port Compatible with USB 2.0 Specification (Type A), USB 2.0 Specification Hi-Speed Certified (Type B), One Internal Card Slot	
Optional Network Ports	Internal MarkNet N8370 802.11b/g/n/a Wireless, NFC	
Noise Level	Operating: 52 dBA (Print) / 55 dBA (Copy) / 51 dBA (Scan)	
Specified Operating Environment	Humidity: 8 to 80% Relative Humidity / Temperature: 10 to 32°C (50 to 90°F) / Altitude: 0 - 2896 Meters (9,500 Feet)	
Limited Warranty	See Statement of Limited Warranty: 1-Year Onsite Service, Next Business Day	
Size / Weight	H x W x D: 24.44 x 18.85 x 20.9 in. / 85.98 lb.	
ENERGY STAR Typical Electricity Consumption	TEC: 0.55 kilowatt-hours per week	

All information is subject to change without notice. Lexmark is not liable for any errors or omissions.

¹ Print and copy speeds measured in accordance with ISO/IEC 24734 and ISO/IEC 24735 respectively (ESAT). For more information see: www.lexmark.com/ISOspeeds.

² "Recommended Monthly Page Volume" is a range of pages that helps customers evaluate Lexmark's product offerings based on the average number of pages customers plan to print on the device each month. Lexmark recommends that the number of pages per month be within the stated range for optimum device performance, based on factors including: supplies replacement intervals, paper loading intervals, speed, and typical customer usage. ³ "Maximum Monthly Duty Cycle" is defined as the maximum number of pages a device could deliver in a month using a multishift operation. This metric provides a comparison of robustness in relation to other Lexmark printers and MFPs. ⁴ Product functions only with replacement cartridges designed for use in a specific geographical region. See www.lexmark.com/regions for more details. ⁵ Average continuous black or continuous composite CMY declared cartridge yield up to this number of standard pages in accordance with ISO/IEC 19798. ⁶ Actual Yield may vary based on other factors such as device speed, paper size and feed orientation, toner coverage, tray source, percentage of black-only printing and average print job complexity. ⁷ Printers are sold subject to certain license/agreement conditions. See www.lexmark.com/printerlicense for details.

This is a Class A device according to international electromagnetic emissions standards (i.e. FCC Rules, EN 55022/EN 55032, etc.). Class A products are intended for use in non-residential/non-domestic environments. Use of a Class A product in residential/domestic environments may cause interference to radio communications and require corrective measures.

© 2022 Lexmark. All rights reserved.

Lexmark, the Lexmark logo and Unison are trademarks of Lexmark International, Inc., registered in the United States and/or other countries.

Apple and AirPrint are trademarks of Apple Inc., registered in the U.S. and other countries and regions. MOPRIA®, the Mopria® Logo, and the Mopria Alliance™ word mark and logo are registered and/or unregistered trademarks and service marks of Mopria Alliance, Inc. in the United States and other countries. Unauthorized use is strictly prohibited. ENERGY STAR and the ENERGY STAR mark are registered trademarks owned by the U.S. Environmental Protection Agency. EPEAT is a trademark of the Green Electronics Council in the United States and other countries. PANTONE® is the property of Pantone LLC. All other trademarks are the property of their respective owners.

This product includes software developed by the OpenSSL Project for use in the Open SSL Toolkit (<http://www.openssl.org/>).

