

GCS82DPC

# 2-port 4K KVM Switch with DisplayPort, USB-C and Audio




- Superior video quality - 4096 x 2160 @60Hz True 4K resolution
- Access one DisplayPort and one USB-C™ computer
- 2.1 audio support
- Multi-platform support - Windows®, Mac®, Linux® and other USB-supported systems
- Easy installation, just plug and play
- Built-in cables
- Port switching via remote switch button
- DisplayPort 1.2 compliant
- USB-powered - no external power adapter required
- 3-year warranty
- Free lifetime US-based technical support

- One USB keyboard, mouse and one DisplayPort monitor control one DisplayPort and one USB-C computer
- Superior video quality – up to 4K (4096 x 2160 @ 60Hz)
- Computer selection via remote port selector
- DisplayPort v1.2 and HDCP compliant
- Supports USB hot-plugging
- The console USB ports can be used for USB peripheral sharing

- Multiplatform support – Windows, Mac and Linux
- Plug and play
- Bus-powered – no external power adapter required<sup>1</sup>

Note: 1. The GCS82DPC may require an external power supply via the USB Micro-B Power Port. For the USB Micro-B cable connecting to the USB Micro-B Power Port, it requires a separate purchase based on the type of the power supply you use.





**Requirements**

**Package Contents**

**Console**

- DisplayPort monitor
- Standard 104-key wired USB keyboard
- Standard 2 or 3 button wired USB mouse
- Speakers and Microphones (optional)

- 1 x GCS82DPC DisplayPort/USB-C KVM
- 1 x Manual

**Computers**

- DisplayPort port and USB-A port
- USB Type-C port with DisplayPort Alt Mode enables USB-C connection to carry DisplayPort signals
- Audio ports (optional)
- Operating Systems
  - Windows®7, 8.1, 10, 11
  - Mac OS X 9.0+
  - Oracle® Solaris
  - Linux®, UNIX, and other USB supported systems

## Specifications

Function	GCS82DPC
<b>Computer Connections</b>	
Direct	2
<b>Port Selection</b>	
	Remote Port Selector
<b>Console Connectors</b>	
Monitor	1 x DisplayPort
Keyboard	1 x USB Type A
Mouse	1 x USB Type A
Audio	1 x 3.5mm Mini Stereo Jack (Green)
Microphone	1 x 3.5mm Mini Stereo Jack (Pink)
<b>CPU Connectors</b>	
Monitor	1x DisplayPort (CPU 1)
Keyboard & Mouse	1x USB Type A (CPU 1)
Audio	2 x 3.5mm Mini Stereo Jack
Microphone	2 x 3.5mm Mini Stereo Jack
Keyboard, Mouse, and Monitor	1x USB Type-C (CPU 2)
<b>LEDs</b>	
KVM	2 x White
<b>Emulation</b>	
Keyboard	Pass Through
Mouse	Pass Through
<b>Video Resolution</b>	
	up to 4096 x 2160 @60Hz
<b>Environment</b>	
Operation Temperature	32~122 F(0~50C)
Storage Temperature	-4~140F (-20~60C)
Humidity	0~80% RH, Non-condensing
<b>Housing</b>	
Case	Plastic
<b>Cable Length</b>	
	KVM cables: 4 ft. (120cm); Remote Switch: 6ft.(180cm)

Dimensions	GCS82DPC
<b>Unit Package Dimensions</b>	
Height	8.75 in. (22.3cm)
Length	2.25 in. (5.7cm)
Width	6 in.(15.3cm)
<b>Master Carton</b>	
Height	7 in. (17.8cm)
Length	15 in. (38 cm)
Width	8 in. (20.3cm)
Master Carton Qty.	6
<b>Weight</b>	
Master Carton Wt.	6.4 lb. (2.9 kg)
Unit Pack Wt.	0.95 lb. (0.43 kg)