




# Planar UC Complete 21:9 153" P0.9 LED Video Wall

The Planar® UC Complete™ 21:9 153" P0.9 LED video wall virtually brings remote meeting participants into medium-sized hybrid unified communication rooms. The 153-inch display features a wide, 21:9 aspect ratio, 0.9mm pixel pitch and 3840 x 1440 resolution to beautifully display the most popular video collaboration platforms such as Microsoft Teams® with front row layout.



SPECIFICATION	DETAIL
<b>Model</b>	UC Complete 21:9 153in P0.9
<b>Video Controller Model</b>	VC4-L-F
<b>Display Technology</b>	Direct View LED
<b>Resolution</b>	3840 x 1440
<b>Display Size Diagonal</b>	153"
<b>Display Size (W x H x D)</b>	11.91 W x 4.49 H x 0.35 D (ft)
<b>Pixel Pitch</b>	0.9mm
<b>Brightness Max (cd / sq m)</b>	600 nits
<b>Contrast Ratio</b>	7000:1
<b>Brightness Uniformity</b>	97%
<b>Color Uniformity</b>	97%
<b>LED Refresh Rate</b>	3000
<b>Color Temperature Range (k)</b>	3,000-10,000
<b>Viewing Angle, Horizontal</b>	160°
<b>Viewing Angle, Vertical</b>	140°
<b>Video Input Resolution Maximum</b>	3840 x 2160 @ 60hz
<b>Frame Rate</b>	50, 60 hz
<b>Video Inputs</b>	4x HDMI 2.0 (HDCP 2.2)
<b>Control</b>	RS232, Network
<b>Service Access</b>	Front

<b>Runtime Duty Cycle (Hours/Day)</b>	24 x 7
<b>LED Lifetime (Half Brightness)</b>	100,000hrs
<b>Power Supply</b>	Single Power
<b>Line Voltage</b>	100-240V AC, 50/60hz
<b>Power Consumption, Maximum (watts)</b>	3770
<b>Display Weight</b>	182.28kg   401.85lbs
<b>Environmental</b>	Indoor
<b>Storage Temperature/Humidity (degrees F/C, relative humidity)</b>	-20° to 60° C   -4° to 140° F 10-85% relative humidity, non-condensing
<b>Operating Temperature/Humidity (degrees F/C, relative humidity)</b>	-10° to 40° C   14° to 104° F 10-80% relative humidity, non-condensing

For more information, please visit [www.planar.com](http://www.planar.com)

*Specifications are subject to change without notice.*

*Specification Report Date: 9/13/2023*

*© Copyright 2023 Planar Systems, Inc. All rights reserved*