




Planar UC Complete 21:9 153" P0.9 LED Video Wall

The Planar® UC Complete™ 21:9 153" P0.9 LED video wall virtually brings remote meeting participants into medium-sized hybrid unified communication rooms. The 153-inch display features a wide, 21:9 aspect ratio, 0.9mm pixel pitch and 3840 x 1440 resolution to beautifully display the most popular video collaboration platforms such as Microsoft Teams® with front row layout.



SPECIFICATION	DETAIL
Model	UC Complete 21:9 153in P0.9
Video Controller Model	VC4-L-F
Display Technology	Direct View LED
Resolution	3840 x 1440
Display Size Diagonal	153"
Display Size (W x H x D)	11.91 W x 4.49 H x 0.35 D (ft)
Pixel Pitch	0.9mm
Brightness Max (cd / sq m)	600 nits
Contrast Ratio	7000:1
Brightness Uniformity	97%
Color Uniformity	97%
LED Refresh Rate	3000
Color Temperature Range (k)	3,000-10,000
Viewing Angle, Horizontal	160°
Viewing Angle, Vertical	140°
Video Input Resolution Maximum	3840 x 2160 @ 60hz
Frame Rate	50, 60 hz
Video Inputs	4x HDMI 2.0 (HDCP 2.2)
Control	RS232, Network
Service Access	Front

Runtime Duty Cycle (Hours/Day)	24 x 7
LED Lifetime (Half Brightness)	100,000hrs
Power Supply	Single Power
Line Voltage	100-240V AC, 50/60hz
Power Consumption, Maximum (watts)	3770
Display Weight	182.28kg 401.85lbs
Environmental	Indoor
Storage Temperature/Humidity (degrees F/C, relative humidity)	-20° to 60° C -4° to 140° F 10-85% relative humidity, non-condensing
Operating Temperature/Humidity (degrees F/C, relative humidity)	-10° to 40° C 14° to 104° F 10-80% relative humidity, non-condensing

For more information, please visit www.planar.com

Specifications are subject to change without notice.

Specification Report Date: 9/13/2023

© Copyright 2023 Planar Systems, Inc. All rights reserved