

ThinkVision T27p-30 63A9GAR1US

Product

ThinkVision T27p-30

Machine Type

63A9

Region

LA, NA

Display Size

27"

View Area

596.7x335.7 mm

Panel

In-Plane Switching

Aspect Ratio

16:9

Resolution

3840x2160

Pixel Pitch

0.155x0.155 mm

Dot / Pixel Per Inch

163 DPI

View Angle (H / V)

178 / 178

Response Time

4 ms (Extreme mode) / 6 ms (Typical mode) / 14 ms (Off mode)

Color Support

1.07 Billion

Refresh Rate

60 Hz

Brightness

180 nits (Typical) / 350 nits (Peak)

Contrast Ratio

1300:1

Color Gamut

99% sRGB

Curvature

None

Anti-glare

Yes

Video Connector

1x HDMI 2.0, 1x DP 1.4, 1x USB-C 3.2 Gen 2 (DP 1.4 Alt Mode)

USB Port

3x USB 3.2 Gen 1 (1x BC)

Camera

Modular Camera Support

Microphone

None

Speakers

Modular Soundbar support

Power Consumption (Typical / Maximum)

35W / 165W

Power Adapter

Integrated

Stand

Tilt, Swivel, Pivot, Height Adjust Stand

Color

Black

Side Bezel Width

2 mm

Dimensions with Stand (HxWxD)

545.4x613.6x204.5 mm / 21.47x24.16x8.05 inches

Weight (Including Stand)

10.39 kg / 22.91 lbs.

Cables Included

USB-C cable, DP cable (NA, Brazil only), USB-C to USB-A cable (NA, Brazil only)

Environmental Certification

Energy Star Certified, TCO 9.0, TCO Edge 2.0, EPEAT Gold, RoHS

Ergonomic Certification

Eyesafe Display, TÜV Low Blue Light (Hardware solution), TÜV Rheinland Low Blue Light, TÜV Rheinland Flicker Free, TÜV Rheinland Eye Comfort

Base Warranty

3-year

Operating System Support

Support Windows 10, Windows 11

Sync Technology

None

Tiny Support / CPU / Platform

None / None / None

Ethernet / Bluetooth / Wireless

1x RJ 45, Ethernet (10M/100M/1000M) / None / None

Touch Screen / Digitizer Pen / Controller

None / None / None

Display Ram / Storage / Card Slot

None / None / None

EAN / UPC / JAN

0196380977459 / 196380977459 / None

Announce Date

2022-08-01

 WWW.LENOVO.COM

Lenovo may not offer the products, services or features discussed in this document in other countries. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area.

Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors.

Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.



<https://psref.lenovo.com>

Visit psref website for the latest version of Product specifications Reference.

© Lenovo, 2022. All rights reserved.



Lenovo™

ThinkVision T27p-30

DISPLAY

Panel Size
27-inch

Screen Dimensions
608.8 mm x 355.3 mm

Panel Type
3-side NearEdgeless In-Plane Switching

Active Area
596.7 mm x 335.7 mm

Curvature
Flat Panel

Backlight
WLED

Aspect Ratio
16:9

Resolution
3840 x 2160

Pixel Pitch
0.155 mm x 0.155 mm

Dot/Pixel Per Inch (DPI/PPI)
163 DPI

Viewing Angle (H x V @ CR 10:1)
178° / 178°

Response Time
6ms (normal mode)
4ms (extreme mode)

Refresh Rate
60 Hz

Brightness (Typical)
350 cd/m²

Contrast Ratio (Typical)
1300:1

Dynamic Contrast Ratio (Typical)
3M:1

Color Gamut (Coverage Ratio)
99% sRGB

Color Gamut (Color Area Ratio)
112% sRGB

Color Support (Typical)
1.07 Billion colors

Color Depth
10 Bit (8 Bit + A-FRC)

Anti-Glare
Yes

CONNECTIVITY

Video Signal
1 x USB Type-C (DP1.4 32.4 Gbps for 4 lanes Alt mode)
1 x HDMI 2.0
1 x DP 1.4

Audio Signal
1 x Audio Out (3.5 mm)

USB Hub
Yes

Ethernet
Yes (10M/100M/1000M)
1 X RJ45

USB Upstream
1 x USB3.2 Gen1 Type-C

USB Downstream
3 x USB3.2 Gen1 Type-A
1 x USB3.2 Gen1 Type-A (1 x BC1.2)

MULTI-MEDIA

Modular Camera/Speaker Support
Yes (Optional Support*)

POWER

Power Consumption (Typ. / Max)
35W / 165W

Power Consumption (Sleep / O Mode)
<0.5W

Power Consumption (Switch - O Mode)
<0.3W

EnergyStar® Power Consumption (Pon / E^{TEC})
29W / 91kWh

Power Supply
Internal

USB Type-C (DP Alt Mode) Power Delivery
Up to 90W[Ⓞ]

Smart Power
Yes

Voltage Required
AC 100 to 240 V (50-60 Hz)

MECHANICAL

Tilt Angle (Front / Back)
-5° / 23.5°

Swivel Angle (Left / Right)
-45° / 45°

Lift (Max. Range)
155 mm

Pivot
-90° / 90°

VESA Mount Capability
Yes (100 x 100 mm)

Kensington™ Lock Slot
Yes

Cable Management
Yes

Bezel Color
Raven Black

Bezel Width (Side)
2.0 mm

Bezel Width (Top/Bottom)
2.0 mm / 18.0 mm

DIMENSIONS

Size Packed (D x H x W) (mm/inch)
148.0 x 525.0 x 690.0 mm
5.83 x 20.67 x 27.17 inches

Size Unpacked w/stand (D x H x W) (mm/inch) (Highest Position)
204.5 x 545.4 x 613.6 mm
8.05 x 21.47 x 24.16 inches

Size Unpacked w/stand (D x H x W) (mm/inch) (Lowest Position)
204.5 x 390.4 x 613.6 mm
8.05 x 15.37 x 24.16 inches

Size Unpacked w/o Stand (Head Only) (D x H x W) (mm/inch)
50.0 x 363.5 x 613.6 mm
1.97 x 14.31 x 24.16 inches

Weight Packed (kg / lbs.)
10.4 kg / 22.9 lbs.

Weight Unpacked (kg / lbs.)
7.3 kg / 16.2 lbs.

Unpacked Weight (Monitor Head Only; kg / lbs.)
5.3 kg / 11.7 lbs.

WHAT'S IN THE BOX

Monitor with Stand
Yes

Power Cable (Cable Length)
1 x Power cable (1.8m)

DisplayPort Cable (Cable Length)
1 x DP cable (1.8m) for NA: North America, Brazil & PRC Workstation

HDMI
1 X HDMI cable for PRC Standalone only

USB Cable (Cable Length)
1 x USB Type-C to Type-A cable (1.8m) for NA: North America & Brazil
1 x USB Type-C cable (1m)

CERTIFICATION

Energy Star®
Energy Star® 8.0

CCC
Yes

TCO
TCO 9.0

TCO Edge
TCO Edge 2.0

EPEAT™
EPEAT™ Gold

RoHS (EU 2011/65/EU)
Yes

Windows Certification
Windows 10, Windows 11


China Energy Efficiency Standard
Tier 2

TÜV Rheinland Eye Comfort
Yes

TÜV Rheinland Low Blue Light (Hardware Solution)
Yes

TÜV Rheinland Flicker Free
Yes

Eyesafe® Display Certifications
Yes



Ⓞ Listed as maximum capacity of power delivery. Actual capacity of power delivery may vary depending upon devices connected or monitor configuration, and may decline with downstream USB ports connected or higher brightness setting.

*Compatible with ThinkVision VoIP Stack MC60 Monitor Webcam and MS30 Monitor Soundbar.

© 2022 Lenovo. All rights reserved. These products are available while supplies last. Prices shown are subject to change without notice. For any questions concerning price, please contact your Lenovo Account Executive. Lenovo is not responsible for photographic or typographic errors. Warranty: For a copy of applicable warranties, write to: Warranty Information, 500 Park Offices Drive, RTP, NC 27709, U.S.A. Attn: Dept. ZPYA/B600. Lenovo makes no representation or warranty regarding third-party products or services. Trademarks: Lenovo, the Lenovo logo, Rescue and Recovery, ThinkPad, ThinkCentre, ThinkStation, ThinkVantage, and ThinkVision are trademarks or registered trademarks of Lenovo. Microsoft, Windows, and Vista are registered trademarks of Microsoft Corporation. Other company, product, and service names may be trademarks or service marks of others.

Specifications may vary depending upon region.

ThinkVision T27p-30

