

See beyond the Game. Visualize your victory.

Inspired by the rigorous quality testing in the production of MSI MAG series, MSI MAG series' design is full of symbols of sturdiness and durability. Additionally, to provide quality user experience, MAG series has really simple installation process and a friendly user interface, and will be the best choice for entry level gamers to step into the game world.




Selling Points

- Curved Gaming display (1500R) - The best gameplay immersion.
- UWQHD High Resolution - Game titles will even look better, displaying more details due to the UWQHD resolution.
- 144Hz Refresh Rate - Real smooth gaming.
- 1ms response time - eliminate screen tearing and choppy frame rates.
- Night Vision: See every detail clearly in the dark, helping you find and attack enemies before they notice.
- Adaptive-Sync Technology - Tear free, stutter free, fluid gaming.
- Anti-Flicker and Less Blue Light - game even longer and prevent eye strain and fatigue.
- Frameless design - Ultimate gameplay experience.
- 178° wide view angle.



Picture and logos

System I/O-Ports



1. 1x HDMI 2.0
2. 1x HDMI 2.0
3. 1x Display Port 1.2a
4. 1x DC Jack
5. 1x Earphone out

Specification

Screen Size	34" (86.36 cm)
Active Display Area (mm)	797.22(H) x 333.72(V)mm
Curvature	Curve 1500R
Panel Type	VA
Resolution	3440x1440 (UWQHD)
Aspect Ratio	21:9
Dynamic Refresh Rate technology	Adaptive-Sync
HDR (High dynamic range)	HDR Ready
SDR Brightness (nits)	300
HDR Brightness (Peak nits)	N/A
Contrast Ratio	4000:1
DCR (Dynamic Contrast Ratio)	100000000:1
Signal Frequency	30~160 KHz(H) / 60~144 Hz(V)
Refresh Rate	144HZ
Response Time (MPRT)	1ms(MPRT)
Response Time (GTG)	4ms
Response Time (Tr + Tf)	14ms
View Angles	178°(H)/178°(V)
Surface Treatment	Anti-glare
NTSC (CIE1976 area percentageoverlap)	105.76%/93.23%
NTSC (CIE1931 area percentageoverlap)	95.98%/90.30%
sRGB (CIE1976 area percentageoverlap)	118.25%/97.10%
sRGB (CIE1931 area percentageoverlap)	135.51%/99.26%
Adobe RGB (CIE1976 area percentageoverlap)	103.81%/94.64%
Adobe RGB (CIE1931 area percentageoverlap)	100.46%/92.57%
DCI-P3 (CIE1976 area percentageoverlap)	96.67%/92.57%
DCI-P3 (CIE1931 area percentageoverlap)	99.89%/94.63%
Rec.709 (CIE1976 area percentageoverlap)	NA
Rec.709 (CIE1931 area percentageoverlap)	NA
Rec.2020 (CIE1976 area percentageoverlap)	N/A
Rec.2020 (CIE1931 area percentageoverlap)	N/A
Display Colors	1.07B
Color bit	10 bits (8 bits + FRC)
Note_DP	3440 x1440 (Up to 144Hz)
Note_HDMI	3440 x 1440 (Up to 100Hz)
Note_DVI	N/A
HDMI	2
HDMI version	2.0
HDMI HDCP version	2.2
DisplayPort	1
DisplayPort version	1.4
DisplayPort HDCP version	2.2
Thunderbolt version	NA
Thunderbolt HDCP version	NA
USB Type C (DisplayPort Alternate)	NA
DVI	NA
D-Sub	NA
Mic-in	NA
Mic-in upstream	N/A
Headphone-out	1
Audio Combo	NA
Lock type	Kensington Lock
Speaker	N/A
USB 2.0 Type B	NA
USB 3.2 Gen 1 Type B	NA
Thunderbolt	NA
USB 2.0 Type A	NA
USB 2.0 Type C	NA
USB 3.2 Gen 1 Type A	NA
USB 3.2 Gen 1 Type C	NA
USB 3.2 Gen 2x2 Type C	NA
USB 3.2 Gen 2x2 Type A	NA
Card Reader	NA



MONITOR
Optix MAG342CQ
OPTIX MAG342CQ

Power Type	External Adaptor 19V 3.42A
Power Input	100~240V, 50/60Hz
Adapter's KC safety Number	NA
Power Cord Type	C13
QC Output	NA
QC Output Power	NA
PD Output	NA
PD Output Power	NA
DisplayPort Cable	1
HDMI Cable	0
DVI Cable	0
USB Type A to Type B Cable	0
USB Type C to Type A Cable	0
USB Type C to Type C Cable	0
Thunderbolt Cable	0
VGA Cable	0
3.5mm audio Cable	0
3.5mm combo audio Cable	0
Mouse Bungee Unit	N/A
VESA Screw	N/A
Power Cord	1
AC Adaptor	1
Warranty Card	1
Quick Guide	1
WebCam	N/A
Adjustment (Tilt)	-5° ~ 20°
Adjustment (Swivel)	-30° ~ 30°
Adjustment (Height)	0 ~ 90 mm
Adjustment (Pivot)	-5° ~ 5°
VESA Mounting	75x75mm
Frameless Design	Yes
Outer Carton Dimension (WxDxH) (mm)	929 x 223 x 505
Outer Carton Dimension (WxDxH) (inch)	36.57 x 8.78 x 19.88
Product Dimension with Stand (WxDxH) (mm)	810 x 270 x 510
Product Dimension with Stand (WxDxH) (inch)	31.89 x 10.63 x 20.08
Product Dimension without Stand (WxDxH) (mm)	810 x 119 x 362
Product Dimension without Stand (WxDxH) (inch)	31.89 x 4.69 x 14.25
Stand Dimension (WxDxH) (mm)	524 x 286 x 375
Stand Dimension (WxDxH) (inch)	20.63 x 11.26 x 14.76
Inside Carton Dimension (WxDxH) (mm)	910 x 210 x 485
Inside Carton Dimension (WxDxH) (inch)	35.83 x 8.27 x 19.09
Weight (Net kg)	6.91
Weight (Gross kg)	9.36
Weight Without Stand (kg)	N/A
Warranty	36M
Color	ID1/Black-Black
EAN	4719072940102