

# Smart IP Access - Extend KVM control over IP

MODEL NUMBER: 0SU51068



## Description

Add remote IP access to existing servers. Smart IP Access is an IP device that provides remote KVM access to servers and network devices. It provides access via LAN, WAN or Internet connection to either a single server or to mixed server environments. Smart IP Access is ideal for data centers, high-density server environments and medium-to-large businesses that are managed by legacy KVM switches. Smart IP Access can be attached to almost any switch or server, making it the perfect add-on device and preserving your existing investment. It comes with configuration definitions for most KVM switches. Smart IP Access provides built-in remote control to two serial devices. For example, serial control of power management enables you to reboot remotely and to power servers on and off from any location. Smart IP Access offers industry standard, 128-bit SSL encryption to prevent security breaches. In addition, the dual IP connection provides redundancy and security.

## Features

- Adds remote KVM control servers, computers, and KVM switches
- Features two ports for remote control of serial devices
- Features dual NIC ports for network redundancy and security
- Able to utilize a standard 56Kbps analog modem connection, while allowing adaptive and configurable bandwidth consumption when accessed via LAN
- SNMP traps for monitoring Smart IP Access events and operation
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

## Highlights

- Adds remote KVM control servers, computers, and KVM switches
- Features two ports for remote control of serial devices
- Features dual NIC ports for network redundancy and security
- Able to utilize a standard 56Kbps analog modem connection, while allowing adaptive and configurable bandwidth consumption when accessed via LAN
- SNMP traps for monitoring Smart IP Access events and operation
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

## System Requirements

### Operating System

- Host Computer - DOS, Windows, Novell, Linux
- Client Computer - Windows with IE 6.0 or higher

### Resolution

- Host Computer: Up to 1600 x 1200 @ 85Hz
- Client Computer: Recommended - client computer resolution should be higher than resolution on the host computer

### Package Includes

- Smart Access Unit
- KVM Cable Kit
- RS232 Cable
- Rackmount Kit

# Specifications

OVERVIEW	
UPC Code	654518206241
Accessory Type	Remote Management



Powering Business Worldwide



Accessory Class	KVM Switch Accessories
<b>PHYSICAL</b>	
Color	Black
Shipping Dimensions (hwd / in.)	2.80 x 6.80 x 3.50
Shipping Dimensions (hwd / cm)	7.11 x 17.27 x 8.89
Shipping Weight (lbs.)	0.90
Shipping Weight (kg)	0.41
<b>ENVIRONMENTAL</b>	
Storage Temperature Range	-40° to 158°F (-40° to 70°C)
Relative Humidity	80% Non-Condensing
Operating Temperature	0 to 40 C / 32 to 104 F
<b>CONNECTIONS</b>	
PC/Server Connections	VGA; PS/2
<b>FEATURES &amp; SPECIFICATIONS</b>	
Number of Users	1
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	Trade Agreements Act (TAA)
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.