



HRX-1634

16CH Pentabrid DVR



Key Features

- 5-in-1 16CH Pentabrid DVR
- AHD/HDTVI/HDCVI/CVBS/IP inputs
- Total 18CH(Analog Maximum 16CH and Network Maximum 18CH), up to 8MP
- H.265, H.264, MJPEG
- 8fps@8MP, 12fps@5MP, 15/12fps@4MP, 30/25fps@2MP recording
- Coaxial control
- Smart search(only Network camera)
- Up to 2 SATA HDDs(6TB/HDD)
- HDMI/VGA Dual monitor (Expand mode)
- P2P service(QR code connect)

HRX-1634

16CH Pentabrid DVR



Specifications

Display

Analog camera	Inputs	16CH(1Vp-p 75ohm, BNC)
	Signal Type	- AHD(8MP, 5MP, 4MP, 1080p, 720p) - HDTVI(8MP, 5MP, 4MP, 1080p, 720p) - HDCVI(8MP, 5MP, 4MP, 1080p, 720p) - NTSC/PAL
Network camera	Inputs	2CH (Up to 18CH)
	Resolution	8MP ~ CIF
	Protocols	SUNAPI(Wisenet), ONVIF
Live	Local Display	1x HDMI, 1x VGA (Dual monitor) HDMI: 3840 x 2160, 2560x1440, 1920x1080, 1280x1024, 1280x720 VGA: 1920x1080, 1280x1024, 1280x720, 1024x768
	Resolution	[Analog Camera(NTSC/PAL)] - 8MP(15/12fps), 5MP(20/12fps), 4MP(30/25fps), 2MP(30/25fps), 1MP(30/25fps), 960H(or 720H)(30/25fps) * per CH [Network Camera] - Typ. 2MP(480fps)

Performance

Record	Compression	H.265, H.264, MJPEG
	Record Rate(Analog)	(Main Stream, NT/PAL) 8M 8/8fps, 5M 12/12fps, 4M 15/12fps, 2M 30/25fps, 720p 30/25fps, Under 960H 30/25fps/CH (Sub Stream) 720p/CH or Higher : 640x368 Full fps, SD : upto SD Full fps * The maximum recording frame rate depends on the frame rate of the input camera.
	Recording Bandwidth	Max. 128Mbps
	Resolution	8MP ~ CIF
	Mode	Normal, Dual Stream, Schedule(Continuous/Event), Event (Pre/Post), Bookmark
	Event Trigger	Alarm Input, Video Loss Analog Camera : Video Loss, Motion Detection, Tampering Network Camera : Camera Event(Sensor, MD, Video Analytics, Defocus, Audio), Dynamic Event, User Event
Search & Playback	Event Action	e-Mail, Event Push, PTZ Preset, Alarm Out, Buzzer, Monitor Out, FTP, SUNAPI Command, Shutdown
	Playback Bandwidth	Max. 32Mbps (18CH simultaneously)
	User	Max. 4 users (Set 1, Remote 3)
	Simultaneous playback	18CH(Local Monitor), 18Ch (CMS), 4Ch (Wisenet Mobile), 1Ch(Web)
Storage	Fisheye Dewarping	CMS (only N/W Camera)
	Supported HDD	Up to 6TB
Backup	HDD Slot	SATA 2ea(Max. 12TB)
	File backup	Set : Recorder, SEC, AVI Webviewer : AVI
	Function	Max. 16 CH play, Date-time/title display

Functions

PTZ	Control	Via GUI, Webviewer, SSM, SmartViewer, Wisenet Mobile Viewer, System Controller
Smart phone	Support Model	iOS, Android
	Protocol Support	RTP, RTSP, HTTP, CGI(SUNAPI)
	Control	Live(16ch) : Multi-Profile Support Playback(4Ch Multi Playback, Max 2MP) Event push
	Max. Remote Users	Search(3), Live Unicast(10)

Redundancy	ARB	Support
Easy configuration		Setup Wizard (Language Date/Time, Password, Network, Auto Camera Configuration), P2P (QR code)
Coaxial Control		CVBS(Pelco-C)/AHD/CVI/TVI

Interface

HDMI	1EA
VGA	1EA
BNC	16CH In / 1CH Out(Spot Output)
Audio	Out(1EA, RCA, Line)
Ethernet	RJ-45(10/100/1000BASE-T)
Alarm	In 16EA, Out 4EA - Relay Out1(NO/NC/COM) - Relay Out2~4(NO/COM)
USB	3EA(Front 2ea USB2.0, Rear USB 3.0))
Serial(Protocols)	RS-485 (Samsung-T/Pelco-D/Pelco-p) * for PTZ
Power inlet	1EA AC (AC100V)

System

System Control	Mouse, Webviewer, System Controller(SPC-7000, SPC-6000, SPC-2000)
Language	English, French, German, Italian, Spanish, Russian, Turkish, Polish, Dutch, Swedish, Czech, Portuguese, Danish, Rumanian, Serbian, Croatian, Hungarian, Greek, Norwegian, Finnish, Korean, Chinese, Japanese, Thai

Environmental

Operating Temperature	0°C to +40°C(+32°F to +104°F)
Operating Humidity	20% ~ 85% RH
Certification	UL, CE, FCC, KC, UKCA

Electrical

Power Input	DC12V
Power Consumption	Max. 40W (6T HDD 2ea)

Mechanical

Color / Material	Black / Metal
Dimension (WxHxD)	W370.0x H44.0 xD320(14.57" x 1.73" x12.6")
Weight	Approx. 4.5Kg (9.9 lb, 4TB HDD 1ea)

Network

Protocol		TCP/IP, UDP/IP, RTP (UDP), RTP (TCP), RTSP, NTP, HTTP, DHCP (Server, Client), PPPoE, SMTP, ICMP, IGMP, ARP, DNS, DDNS, uPnP, HTTPS, SNMP, ONVIF (Profile-S), SUNAPI(Server, Client)
DDNS		Wisenet DDNS
Transmission speed		- Analog Camera(NTSC/PAL) (Main Stream) 8MP 8/8fps CH, 5M 12/12fps CH, 4M 15/12fps CH, 2M 30/25fps CH, 720p 30/25fps/CH, SD 30/25fps/CH (Sub Stream) 720p or higher : 640x368 full fps/CH, SD signal : upto CIF full fps/CH * The maximum recording frame rate depends on the frame rate of the input camera.
Transmission Bandwidth		Max. 100Mbps
Audio	Input/Output	4 Line in / 1 Line out
	Compression	G.711 (N/W Camera G.711, 726)
	Audio Communication	2-Way
Max Remote Users		Search(3), Live Unicast(10), Multicast(20)
Security		IP address filtering, User access log, 802.1x Authentication, Encryption (ID/PW, Recording, Transmission, Backup) Device Certificate(Hanwha Techwin Root CA)
Viewer Software		SSM, Webviewer, SmartViewer, Wisenet Mobile Viewer, Wisenet Viewer Support SDK/CGI(SUNAPI) for integration to 3'rd party VMS

HRX-1634


16CH Pentabrid DVR



CAD

Unit: mm [inch]

This parts should not contain any substances which are specified in A800-0032K



Appearance drawing HRX-1634
Unit : mm[inches]