



PRN-6400DB4

64CH AI NVR



Key Features

- Up to 8K (32MP) Resolution
- AI search (BestShot, Attribute)
- Object detection and classification
- SATA 16ea (Up to 160TB)
- Easy Channel/Event/Alarm configuration
- Video preview support
- Dynamic Event support
- Bookmark management (Up to 100 set)
- Simple connection with mobile phone through QR code
- Dual SMPS

PRN-6400DB4

64CH AI NVR



Specifications

Display

Network camera	Inputs	Max. 64CH
	Resolution	32MP ~ CIF
	Protocols	Wisenet, ONVIF
Decoding	Local Display	[Dual Display] HDMI 1: 3840 x 2160 (30Hz) HDMI 2: 1920x1080 (60Hz)
	Multi Screen Display	[Local Monitor] - Dynamic layout, Virtual channel view - Clone Mode : Up to 64 Division - Expand Mode : HDMI1 up to 36 Div. HDMI2 up to 16 Div. [Web] 1/ 2H/ 2V/ 3V/ 4/ 6/ 8/ 9
	Resolution	32M(15fps, H.265 Only), 12M(30fps, H.265 Only), 8.3M(120fps), 1080p(480fps), 720P(960fps), D1(1920fps)

Performance

Operating System	Embedded	Linux
Record	Compression	H.265, H.264, MJPEG, WiseStream(H.265, H.264)
	Recording Bandwidth	Distributed mode : Up to 400 Mbps Normal mode : Up to 150 Mbps {RAID mode} Normal : Up to 400 Mbps Degradate/ Rebuild : Up to 320 Mbps
	Resolution	32MP ~ CIF
	Mode	Normal, Dual Stream, Schedule(Continuous/Event), Event (Pre/Post), Bookmark
	Event Trigger	Alarm Input, Video Loss, Camera Event(Sensor, MD, Video Analytics, Defocus, Audio), Dynamic Event, User Event
	Event Action	e-Mail, Event Push, PTZ Preset, Alarm Out, Buzzer, Monitor Out, FTP, SUNAPI Command, Shutdown
Search & Play	Playback Bandwidth	Max. 64Mbps(64CH simultaneously)
	User	Max. 4 Users (Local 1, Remote 3)
	Simultaneous playback	Max. 112CH(Local 64CH, Remote 16CH per user)
	Fisheye Dewarping	Support (Local 1CH), CMS
	Mode	Date & Time(Calendar), Event list, Text Search, Smart Search
	Resolution	CIF ~ 32MP (Up to H.264 9MP, H.265 32MP)
	Playback Control	Fast/Slow Forward / Backward, Move one step Up / Down
Storage	Supported HDD	Up to 10TB
	HDD Slot	SATA 16ea(Max. 160TB, Non-RAID mode), Hot swap
	External	iSCSI storage
	RAID	RAID-5/6(Array Size : 8 HDD x 2 Array)
Backup	File backup	BU/Exe/AVI(GUI), JPG/AVI(Network)
	Function	Multi channel(Up to 16CH) Play, Date-Time/Title display

Network

Protocol	IPv4, IPv6, TCP/IP, UDP/IP, RTP (UDP), RTP (TCP), RTSP, NTP, HTTP, DHCP (Server, Client), SMTP, ICMP, IGMP, ARP, DNS, DDNS, uPnP, HTTPS, SNMP, ONVIF (Profile-S), SUNAPI(Server, Client)	
DDNS	Hanwha DDNS	
Transmission Bandwidth	Max. 400Mbps	
Audio	GUI	64 CH(network)
	Web	G.711, G.726, AAC(16/48KHz)

Audio Communication		2-Way
Max Remote Users	Search(3), Live Unicast(10), Multicast(20)	
Security	IP address filtering, User access Log, 802.1x, Encryption Device certificate(Hanwha Techwin Root CA), Signed firmware	
Web viewer	Supported OS	Windows 10, macOS 10.13
	Supported browser	Google Chrome, Microsoft Edge, Mac Safari
Viewer Software	SSM, Webviewer, Smart Viewer, Wisenet mobile Support CGI(SUNAPI) for integration to 3'rd party VMS	

Functions

Camera Setup	Register	Auto, Manual
	Item	IP address, Add profile edit, Bitrate, Compression, GOP, Quality, Camera MD setup (4, 8 point polygon) Camera video setup (Simple focus, Brightness/Contrast, Flip/Mirror, IRIS, WDR, D&N, SSNR, Shutter, SSDR, DIS), Fisheye Dewarping Mode, Hallway View Setup, Camera Webpage
PTZ	Control	Via GUI, Webviewer, SPC-2000
	Preset	300 Presets
Smart phone	Support Model	iOS, Android
	Protocol Support	RTP, RTSP, HTTP, CGI(SUNAPI)
	Control	Live 16CH(Multi-Profile Support), Playback 4CH
	Max. Remote Users	Search(3), Live Unicast(10)
Redundancy	Failover	N+1
	ARB	Support
Easy configuration	P2P(QR code)	

Interface

Front	Indicator	HDD, Alarm, Power, Record, Backup, Network, RAID
Storage	OK	
Reset	Power button	
HDD Key Lock	OK	
HDMI	2EA	
Audio	Out 1EA (3.5mm Audio Jack)	
Ethernet	RJ-45 3EA (LAN/WAN, 1Gbps)	
Alarm	In 8EA, Out 4EA	
USB	4EA(Front 2 x USB 2.0, Rear 2 x USB 3.0)	
Power inlet	AC 2EA	

System

Log	Log List	Max. 100,000 (System Log, Event Log each)
System Control	Mouse, Keyboard, Web, Controller (SPC-2000)	
Language	English, French, German, Italian, Spanish, Russian, Turkish, Polish, Dutch, Czech, Portuguese, Danish, Rumanian, Serbian, Croatian, Hungarian, Greek, Norwegian, Finnish, Korean, Chinese, Japanese, Thai, Vietnamese	

Environmental

Operating Temperature	0°C to +40°C(32°F to 104°F)
Operating Humidity	20% ~ 85% RH

Electrical

Power Input	100 ~ 240 VAC ±10%; 50/60 Hz (Dual SMPS)
Power Consumption	Max. 285W (972.5 BTU with HDD 16ea)

Mechanical

Color / Material	Black / Metal
Dimension (WxHxD)	440.0 x 132.0 x 571.1mm
Weight	Approx. 14.3Kg(31.5 lb, HDD not included)

Intelligent Analysis

AI Search	Object Attribute	Person, Face(with Wisenet AI camera), Vehicle, Liscence plate
	LPR	English, Number (Wisenet AI, P/X Camera)

PRN-6400DB4


64CH AI NVR



CAD

Unit: mm [inch]

This parts should not contain any substances which are specified in AMS-00000



Appearance Drawing
PRN-6410DB4, XRN-6410DB4, PRN-6400DB4
Unit : mm[inches]