

HD39HDRx

Exceptional home entertainment and gaming performance



- **Lights on viewing - Incredible 4,000 lumens for use any time of day**
- **4K UHD and HDR compatible - Enhanced detail for an immersive viewing experience**
- **Enhanced Gaming Mode - Delivers up to 8.4ms response time at 1080p, 120Hz**
- **Easy connectivity - 2x HDMI, USB power and built-in 10W speaker**



Experience incredible HDR technology on a massive screen with the 1080p, 4,000 lumens HD39HDRx home entertainment projector. Gamers can take advantage of the Enhanced Gaming Mode, combined with a 120Hz refresh rate for lightning-fast, 8.4ms response times for lag-free gaming.

The 1.3x zoom and keystone correction deliver flexible installation options. Powerful 10-watt audio fills a room with loud and crisp audio to further enhance media and presentations.

Specifications

Display/image	
Display technology	DLP™
Resolution	1080p Full HD (1920x1080)
Brightness	4,000 lumens
Contrast ratio	50,000:1
Native aspect ratio	16:9
Aspect ratio - compatible	4:3
Keystone correction - vertical	+/-40°
Horizontal scan rate	15.38 ~ 91.15Khz
Vertical scan rate	50 ~ 85(120 for 3D)Hz
Uniformity	70%
Screen size	30.8" ~ 301.4" diagonal
Lamp info	
Light source type	Lamp
Lamp watts	240
Lamp life hours (up to)	4000 (Bright), 12000 (Dynamic), 10000 (Eco), 15000 (Eco+)
Optical	
Throw ratio	1.12:1 ~ 1.47:1
Projection distance	39.37" - 295.28"
Zoom	1.3
Zoom type	Manual
Focal length (mm)	16.9mm~21.6mm/0.665"~0.85"
Native offset	116%
Connectivity	
Connections	Inputs 1 x HDMI 2.0, 1 x HDMI 1.4a 3D support Outputs 1 x Audio 3.5mm, 1 x USB-A power 1.5A Control 1 x RS232
General	
Noise level (typical)	26dB
Noise level (max)	28dB
PC compatibility	UHD, WUXGA, FHD, UXGA, SXGA, WXGA, HD, XGA, SVGA, VGA, Mac
2D compatibility	NTSC M/J, 3.58MHz, 4.43MHz PAL B/D/G/H/I/M/N, 4.43MHz SECAM B/D/G/K/K1/L, 4.25/4.4MHz 480i/p, 576i/p, 720p(50/60Hz), 1080i(50/60Hz), 1080p(50/60Hz)
3D compatibility	Side-by-Side:1080i50 / 60, 720p50 / 60 Frame-pack: 1080p24, 720p50 / 60 Over-Under: 1080p24, 720p50 / 60
3D	Full 3D
Security	Security bar, Kensington Lock, Password protected interface
OSD / display languages	25 languages: Arabic, Czech, Danish, Dutch, English, Farsi, Finnish, French, German, Greek, Hungarian, Indonesian, Italian, Japanese, Norwegian, Polish, Portuguese, Romanian, Russian, Chinese (simplified), Spanish, Swedish, Chinese (traditional), Turkish, Vietnamese
Operating conditions	5°C~40°C/41°F~104°F, max altitude 3000M/9843ft, max humidity 85%
Remote control	Data remote with laser and mouse function
Speaker count	1
Watts per speaker	10W
In the box	AC power cord Remote control 2x AAA batteries Basic user manual
Optional wireless models	WHD200
Power	
Power supply	100 ~ 240V, 50 ~ 60Hz
Power consumption (standby)	0.5W
Power consumption (min)	200W
Power consumption (max)	285W
Weight and dimensions	
Dimensions (W x D x H)	12.44" x 9.61" x 4.25"
Gross weight	8.47 lbs
Net weight	6.42 lbs

