

ProductSheet

HP Pro mt440 G3 Mobile Thin Client (73U46UT)



Secure, stylish, and affordable cloud productivity.

Drive productivity and performance on-the-go with the 12th Gen Intel® Celeron® processor[2], long battery life with HP Fast Charge[8], WLAN[3], and essential ports in the HP Pro mt440 Mobile Thin Client. Confidently move through your day with a device built with aluminum materials for durability.



Business-class cloud productivity

Power through your day with the latest Intel® Celeron® processor[2] and a mix of modern and legacy ports.

Protect your data and device

Rest easy with a mobile thin client that helps keep your cloud computing experience safe with a self-healing BIOS.

Built to be seen, built to last

Get an eye-catching device that features a durable chassis built with aluminum materials that can withstand daily wear and tear.

Specifications

Operating system	HP ThinPro
Processor family	Intel® Celeron® processor
Processor	Intel® Celeron® 7305 (1.1 GHz base frequency, 8 MB L3 cache, 5 cores, 5 threads)
Chipset	SoC
Memory	8 GB DDR4-3200 MHz RAM (2 x 4 GB)
Memory Slots	2 SODIMM
Internal Storage	128 GB PCIe® NVMe™ SSD
Graphics	Integrated
Graphics (integrated)	Intel® UHD Graphics
Display	35.6 cm (14") diagonal, HD (1366 x 768), narrow bezel, anti-glare, 250 nits, 45% NTSC
Display	14" diagonal, HD (1366 x 768), narrow bezel, anti-glare, 250 nits, 45% NTSC ^[17,20,21,22]
Display size (diagonal)	35.6 cm (14")
Display size (diagonal)	14"
Audio	Dual stereo speakers, dual array microphones
Minimum dimensions (W x D x H)	32.19 x 21.39 x 1.99 cm
Minimum dimensions (W x D x H)	12.67 x 8.42 x 0.78 in
Weight	Starting at 1.48 kg <i>(Weight will vary by configuration.)</i>
Weight	Starting at 3.26 lb <i>(Weight will vary by configuration.)</i>
Keyboard	HP Premium Keyboard – spill-resistant, backlit keyboard with drain
Pointing device	Clickpad with multi-touch gesture support, taps enabled as default
Camera	720p HD camera
Ports	1 AC power; 1 headphone/microphone combo; 1 RJ-45; 1 SuperSpeed USB Type-C® 10Gbps signaling rate (USB Power Delivery, DisplayPort™ 2.1); 1 HDMI 2.1b; 3 SuperSpeed USB Type-A 5Gbps signaling rate (1 charging, 1 USB Power Delivery) <i>(HDMI cable sold separately.)</i>
Wireless	Intel® Wi-Fi 6E AX211 (2x2) and Bluetooth® 5.2 combo (supporting gigabit data rate)
Protocols	Citrix® ICA/HDX; Microsoft RFX/RDP; VMware Horizon® View™ through RDP/PCoIP, and Blast Extreme (Protocols are dependent on operating system installed.); Azure Virtual Desktop add-on; Microsoft 365
Power	HP Smart 65 W External AC power adapter ^[27]
Battery type	HP Long Life 3-cell, 42 Wh Li-ion
Management features	HP ThinUpdate; HP Cloud Endpoint Manager; HP Write Filter; Windows Defender; HP BIOS Configuration Utility; HP Device Manager ^[19]
Sustainable impact specifications	Low Halogen
Security management	USB enable/disable (via BIOS); Power-on password (via BIOS); Setup password (via BIOS); Support for chassis padlocks and cable lock devices; HP Secure Erase; BIOS Update via Network; HP BIOSphere Gen6; HP Sure Start Gen7; HP Tamper Lock; HP DriveLock and Automatic DriveLock ^[23,24,34]
Software included	HP Connection Optimizer; HP Hotkey Support
Browser supported	Mozilla Firefox; Microsoft Edge ^[35,36]
UPC number	197029159427

Top Recommended Displays, Accessories and Services

Personal Systems Commercial Care Pack Services

HP 3 year Pickup and Return Notebook Hardware Support	UK707E
HP 3 year Pickup and Return w/Accidental Damage Protection Notebook Hardware Support	UK712E

Personal Systems Hardware Support Onsite Service

HP 3 year Next Business Day Response Onsite w/Accidental Damage Protection NB HW Supp	UK726E
---	--------

Messaging Footnotes

[2] Multicore is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. Intel's numbering, branding and/or naming is not a measurement of higher performance.

[3] Wireless access point and Internet service required and sold separately. Availability of public wireless access points limited.

[8] Recharges your battery up to 50% within 30 minutes when the system is off or in standby mode. Power adapter with a minimum capacity of 65 watts is required. After charging has reached 50% capacity, charging will return to normal. Charging time may vary +/-10% due to System tolerance.

Technical Specifications Footnotes

[17] FHD/HD content required to view FHD/HD images.

[19] Resolutions are dependent upon monitor capability, and resolution and color depth settings.

[21] Actual brightness will be lower with touchscreen or Sure View.

[22] Touchscreen not available with ThinPro.

[23] HP BIOSphere Gen6 features may vary depending on the platform and configuration.

[24] HP Sure Start Gen7 is available on select HP PCs and requires Windows 10 and higher.

[27] Availability may vary by country.

[34] HP Tamper Lock is an optional feature that must be configured at the factory and requires a supervisor password be established prior to use.

[35] Microsoft Edge available for Windows only.

[36] Firefox available for ThinPro only.

© Copyright 2022 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Intel, Celeron, and XMM are trademarks or registered trademarks of Intel Corporation or its subsidiaries in the United States and other countries. Bluetooth is a trademark owned by its proprietor and used by HP Inc. under license. USB Type-C® and USB-C® are registered trademarks of USB Implementers Forum. DisplayPort™ and the DisplayPort™ logo are trademarks owned by the Video Electronics Standards Association (VESA®) in the United States and other countries. ENERGY STAR is a registered trademark of the U.S. Environmental Protection Agency. All other trademarks are the property of their respective owners.

