

## Meraki Go Outdoor WiFi 6 Access Point - GR62 Datasheet

### Meraki Go Outdoor WiFi 6 Access Point

GR62: Dual-band, 802.11ax Wifi 6 2x2:2 MU MIMO



## Technical Specifications

### Radios

- 2.4 GHz 802.11b/g/n/ax client access radio
- 5 GHz 802.11a/n/ac/ax client access radio
- Supported frequency bands (country-specific restrictions apply):
  - 2.412-2.484 GHz
  - 5.150-5.250 GHz (UNII-1)
  - 5.250-5.350 GHz (UNII-2)

### 802.11ac/ax and 802.11n Capabilities

- 2 x 2 multiple input, multiple output (MIMO) with two spatial streams
- SU-MIMO and MU-MIMO support
- Maximal ratio combining (MRC) & Beamforming
- 20 and 40 MHz channels (802.11n), 20, 40, and 80 MHz channels (802.11ac/ax)

- 5.470-5.600, 5.660-5.725 GHz (UNII-2e)
- 5.725 -5.825 GHz (UNII-3)

- Up to 1024-QAM on both 2.4 GHz and 5 GHz bands
- Packet aggregation
- OFDMA, BSS coloring, and TWT support

---

## Antenna

---

- Integrated omni-directional antennas (5.6 dBi gain at 2.4 GHz, 5.3 dBi gain at 5 GHz)

---

## Interfaces

---

- 1x 10/100/1000 BASE-T Ethernet (RJ45)
- 1x DC power connector (5.5 mm x 2.5 mm, center positive)

---

## Power

---

- Power over Ethernet: 37 - 57 V (802.3af compatible)
- Alternative 12 V DC input
- Power consumption: 11W max (802.3af)
- Power over Ethernet injector sold separately

---

## Environment

---

- Operating temperature: -4 °F to 131 °F (-20 °C to 55 °C)
- Humidity: 5 to 95% non-condensing
- IP67 rated (glands not included)

---

## Physical Dimensions

---

- 9.57" x 4.53" x 1.26" (243 mm x 115 mm x 32 mm), not including mount plate.
- Product Weight: 1.06 lb | 0.48 kg
- Package Weight: 1.94 lb | 0.88 kg

---

## Mobility

---

- PMK and OKC for fast Layer 2 roaming

---

## LED Indicators

---

- 2 Ethernet status
- 1 power/booting/firmware upgrade status

---

## Compliance

---

- RoHS
- DFS

---

## In the Box

---

- GR62-HW: Meraki Go Outdoor Access Point
- Wall mount and screw kit
- Quick start guide
- PSU and ethernet cable

---

## Warranty

---

- 1 year hardware warranty

