

G27C6P E2

SEE BEYOND THE GAME. VISUALIZE YOUR VICTORY.





SPECIFICATIONS

Panel Size	27" (69cm)
Panel Resolution	1920 x 1080 (FHD)
Refresh Rate	170Hz
Response time	1ms (MPRT)
Panel Type	VA
Brightness (nits)	250
Viewing Angle	178° (H) / 178° (V)
Aspect Ratio	16:9
Curvature	1500R
Contrast Ratio	3000:1
Active Display Area (mm)	596.736(H) x 335.664(V)
Pixel Pitch (H x V)	0.3108(H)x0.3108(V)
Surface Treatment	Anti-glare
Display Colors	16.7M
Adobe RGB / DCI-P3 / sRGB	90% / 93% / 117%
Video ports	1x DP(1.2a) 2x HDMI (1.4b)
Audio ports	1x Earphone out
Kensington Lock	Yes
VESA Mounting	100 x 100 mm
Power Type	External Adaptor 20V 2.25A
Power Input	100~240V, 50~60Hz
DYNAMIC REFRESH RATE TECHNOLOGY	FreeSync Premium
ACTIVATED RANGE	48Hz-170Hz
DCR	100000000:1
Signal Frequency	53~183 KHz(H) / 48~170 Hz(V)
Adjustment (Tilt)	-5° ~ 20°
Adjustment (Height)	0 ~ 130 mm
Dimension (W x D x H)	611.5 x 266.5 x 567.1 mm 611.5 x 86 x 372.8mm (without stand)
Carton Dimension (W X D X H)	WW carton: 790 x 168 x 488mm Outer:805 x 183 x 513mm
Weight (NW / GW)	5.7 kg / 7.9 kg
Frameless Design	Yes
Compatibility	PC, Mac, PS5™, PS4™, Xbox, Mobile, Notebook * All trademarks and the registered trademarks are the property of their respective owners.

FEATURES



Enjoy the most immersive gameplay with 1500R curvature rate.



1ms Fast Response Time

Eliminate screen tearing and choppy frame rates with 1ms response time.



170Hz High Refresh Rate

170 Hz Experience smooth gaming with 170Hz refresh rate, that gives you the upperhand in fast moving games.



Console Mode

Best solution for console users: FHD@120Hz, 2K Resolution PS5™ Optimization.



Night Vision

Get the jump on enemies before they even notice you. The Night Vision is built to be easy on the eyes.



Wide Color Gamut

Wide Color Game colors and details will look more realistic and refined, to | IGamut push game immersion to its limits.



Frameless Design

With the narrow bezel, you will not even notice the monitor at all in the heat of the moment.



MONITOR

G27C6P E2

SEE BEYOND THE GAME. VISUALIZE YOUR VICTORY.

Note

Display Port: 1920 x 1080 (Up to 170Hz by DP overclocking) HDMI1.4: 1920 x 1080 (Up to 144Hz) Adobe RGB, sRGB and DCI-P3 follow CIE1976 standard

CONNECTIONS



- 1. 5-way joystick navigator
- 2. 1x DC Jack
- 3. 2x HDMI (1.4b)
- 4. 1x Display Port (1.2a)
- 5. 1x Earphone out
- 6. 1x Kensington lock