



## QHora-322

Number of Ethernet Ports	9
10GbE BASE-T (RJ45)	3 x 10GBASE-T (10G/5G/2.5G/1G/100M)
2.5GbE (RJ45)	6
CPU	Marvell CN9130 Quad Core Armv8 Cortex-A72
Memory	4GB DDR4
Flash Memory	4MB SPI NOR Flash 4GB eMMC
USB 3.2 Gen 1 port	1
Button	Reset
Power	12V DC
Power consumption	36W
Dimensions	226 x 140 x 44.4mm
Weight	1.08Kg
Packing weight	1.61Kg
Operating Temperature	0°C ~ +40°C
Operating Humidity	5% to 95% non-condensing
Certifications	CE / FCC / VCCI / BSMI / RCM / CCC / UKCA
QNAP SD-WAN solution, QuWAN	Yes

Note: Use only QNAP memory modules to maintain system performance and stability. For NAS devices with more than one memory slot, use QNAP modules with identical specifications.

Warning: Using unsupported modules may degrade performance, cause errors, or prevent the operating system from starting. The terms HDMI, HDMI High-Definition Multimedia Interface, HDMI trade dress and the HDMI Logos are trademarks or registered trademarks of HDMI Licensing Administrator, Inc.

Product images are for illustrative purposes only and may differ from the actual product. Due to differences in monitors, colors of products may also appear different to those shown on the site.

Designs and specifications are subject to change without notice.