



Modern 15 B12M-093CA

OS	Windows 11 Home (MSI recommends Windows 11 Pro for business.)
CPU/Processor	Core i5-1235U
Graphics	Intel Iris Xe
Screen Size / Type	15.6" FHD, IPS-Level 60Hz 45%NTSCThin Bezel
System Memroy	Onboard DDR IV 16GB
Color	Black
SSD	1x M.2 SSD NVMe PCIe Gen3x4
Resolution/ Ratio	1920x1080 16:9
CPU Frequency	0.9 - 4.4Ghz
Keyboard	White backlight 99 Key
Speaker	Speakers 2W * 2
AC Adapter	65W
SoDimm	On board with Dual channel design
Unit weight	3.85 lbs
HDD Capacity	512GB NVMe PCIe SSD
Unit Dimension	14.13" x 9.49" x 0.78"
HDD Interface	NVMe
WLAN	Intel Wi-Fi 6 AX201(2*2 ax)
BT	BT 5.2
Card Reader	Micro SD
Webcam	720p HD Webcam
USB	USB 3.2Gen 2 *1; USB 2.0 *2
HDMI-out	4K @ 30Hz
USB Type C	USB 3.2 Gen 2 Type C *1
Battery Pack	3 cell (39Whr) Li-Polymer
Touch Pad	Silky Glass Multi Touch with Finger print reader
Mic-in/ Headphone-out	Mic-in/Headphone-out Combo
UPC	824142297049
UCC-14	10824142297046
Warranty	1 year Limited warranty (Include 1 Year Global)