

ThinkVision T32h-30 63D3GAR1US

Product

ThinkVision T32h-30

Machine Type

63D3

Region

LA, NA

Display Size

31.5"

View Area

698.1x392.7 mm

Panel

In-Plane Switching

Aspect Ratio

16:9

Resolution

2560x1440

Pixel Pitch

0.273x0.273 mm

Dot / Pixel Per Inch

93 dpi

View Angle (H / V)

178 / 178

Response Time

4 ms (Extreme mode) / 6 ms (Typical mode)

Color Support

1.07 Billion

Refresh Rate

60 Hz

Brightness

350 nits

Contrast Ratio

1000:1

Color Gamut

99% sRGB

Curvature

None

Anti-glare

Yes

Video Connector

1x HDMI 2.0, 1x DP 1.4, 1x USB-C 3.2 Gen 1 (DP 1.4 Alt mode)

USB Port

4x USB-A 3.2 Gen 1 (1x BC 1.2)

Network Connectivity

1x RJ45, Ethernet (10M/100M/1000M)

Camera

Modular Camera Support

Microphone

None

Speakers

Modular Speaker Support

Power Consumption (Typical / Maximum)

32W / 153W

Power Adapter

Integrated

Stand

Tilt, Swivel, Pivot, Height Adjust Stand

Color

Raven Black

Side Bezel Width

2 mm

Dimensions with Stand (HxWxD)

444.5x714.2x234.9 mm / 17.5x28.12x9.25 inches

Weight (Including Stand)

9.9 kg / 21.8 lbs.

Cables Included

USB-C cable

Environmental Certification

Energy Star Certified, TCO 9.0, TCO Edge 2.0, EPEAT Gold, RoHS

Ergonomic Certification

Eyesafe Display, TÜV Low Blue Light (Hardware solution), TÜV Rheinland Eye Comfort

Base Warranty

3-year

Operating System Support

Support Windows 10, Windows 11

Sync Technology

None

ThinkCentre M Series Support

None

Processor

None

Touch Screen

None

Controller

None

Display Ram / Storage / Card Slot

None / None / None

EAN / UPC / JAN

0196801200654 / 196801200654 / None

Announce Date

2022-10-10

 WWW.LENOVO.COM

Lenovo may not offer the products, services or features discussed in this document in other countries. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area.

Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors.

Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.



<https://psref.lenovo.com>

Visit psref website for the latest version of Product specifications Reference.

© Lenovo, 2022. All rights reserved.



Lenovo™

ThinkVision T32h-30 Monitor

Display

Panel Size
31.5-inch

Screen Dimensions
709.4 mm x 412.0 mm

Panel Type
3-side NearEdgeless
In-Plane Switching

Active Area
698.1 mm x 392.7 mm

Backlight
WLED

Aspect Ratio
16:9

Resolution
2560 x 1440

Pixel Pitch
0.273 mm x 0.273 mm

Dot/Pixel Per Inch (DPI/PPI)
93

Viewing Angle (H x V @ CR 10:1)
178° / 178°

Response Time
4ms (Extreme Mode),
6ms (Normal Mode)

Refresh Rate
60Hz

Brightness (Typical)
350 cd/m²

Contrast Ratio (Typical)
1000:1

Dynamic Contrast Ratio (Typical)
3M:1

Color Gamut (Coverage Ratio)
99% sRGB

Color Gamut (Color Area Ratio)
130% sRGB

Color Support (Typical)
1.07 Billion

Color Depth
10-bit (8+FRC)

Anti-Glare
Yes

Connectivity

Video Signal
1 x USB Type-C¹ (DP 1.4 Alt Mode)
1 x HDMI 2.0
1 x DP 1.4 (HBR2)

Audio Signal
1 x Audio Out (3.5 mm)

USB Hub
Yes

Ethernet
Yes (10M/100M/1000M)

USB Upstream
1 x USB 3.2 Gen 1² Type-C¹

USB Downstream
4 x USB 3.2 Gen 1² Type-A (1 x BC1.2)

Multimedia

Modular Camera/Speaker Support
Yes (Optional Support³)

Special Features

Software
Lenovo ThinkColour (Lenovo Display Control Center)⁴

Natural Low Blue Light
Yes

Power

Power Consumption (Typ. / Max.)
32.0W / 153.0W

Power Consumption Sleep/Off Mode
< 0.5W

Power Consumption Switch-Off Mode
< 0.3W

ENERGY STAR Power Consumption (Pon/E_{TREC})
26.0W / 82.6kWh

Power Supply
Internal

USB Type-C¹ (DP Alt Mode) Power Delivery⁵
Up to 90.0W

Smart Power
Yes

Voltage Required
AC 100 to 240 V (50-60Hz)

Mechanical

Tilt Angle (Front / Back)
-5° / 23.5°

Swivel Angle (Left / Right)
-45° / 45°

Lift (Max. Range)
155 mm

Pivot
-90° / 90°

VESA Mount Capability
Yes (100 x 100 mm)

Kensington Lock Slot
Yes

Cable Management
Yes

Bezel Color
Raven Black

Bezel Width (Side)
2.0 mm

Bezel Width (Top / Bottom)
2.0 / 18.6 mm

Dimension

Size Packed (D x H x W) (mm/inch)
525.0 x 148.0 x 95.0 mm
20.67 x 5.83 x 37.40 inches

Size Unpacked w/ Stand (Lowest Position) (D x H x W) (mm/inch)
234.9 x 599.5 x 714.2 mm
9.25 x 23.60 x 28.12 inches

Size Unpacked w/ Stand (Highest Position) (D x H x W) (mm/inch)
234.9 x 444.5 x 714.2 mm
9.25 x 17.50 x 28.12 inches

Size Unpacked w/o Stand (Head Only) (D x H x W) (mm/inch)
59.5 x 420.9 x 714.2 mm
2.34 x 16.57 x 28.12 inches

Weight Packed (kg / lbs.)
14.0 kg / 30.9 lbs.

Weight Unpacked (kg / lbs.)
9.9 kg / 21.8 lbs.

Weight (Monitor Head Only) (kg / lbs.)
7.2 kg / 15.9 lbs.

What's in the Box

Monitor with Stand
Yes

Power Cable (Cable Length)
1 x Power Cable (1.8 m)

USB Cable (Cable Length)
1 x USB Type-C¹ to Type-C¹ Cable (1.8 m)

Quick Setup Guide
Yes

Warranty Booklet
Yes

Certification

ENERGY STAR Certification
Yes

CCC
Yes

TCO
9.0

TCO Edge
2.0

EPEAT
Gold

Volatile Organic Compound Certification
Yes

RoHS (2011/65/EU)
Yes

Windows Certification
Windows 10, Windows 11

China Energy Efficiency Standard
Tier 1

TÜV Rheinland Eye Comfort
Yes

TÜV Low Blue Light (Hardware Solution)
Yes

Eyesafe Display Certification
Yes



¹ USB Type-C[®] and USB-C[®] are registered trademarks of USB Implementers Forum. | ² Depending on many factors such as the processing capability of peripheral devices, file attributes, and other factors related to system configuration and operating environments, the actual transfer rate using the various USB connectors on this device will vary and is typically slower than the data rates as defined by the respective USB specifications: 5 Gbit/s for USB 3.2 Gen 1; 10 Gbit/s for USB 3.2 Gen 2 & 20 Gbit/s for USB 3.2 Gen2x2. | ³ Compatible with ThinkVision VoIP Stack MC60 Monitor Webcam and MS30 Monitor Soundbar. | ⁴ This software can only be used with Windows 10 & Windows 11. | ⁵ Listed as maximum capacity of power delivery. Actual capacity of power delivery may vary depending upon devices connected or monitor configuration, and may decline with downstream USB ports connected or higher brightness setting.

© 2022 Lenovo. All rights reserved. These products are available while supplies last. Prices shown are subject to change without notice. For any questions concerning price, please contact your Lenovo Account Executive. Lenovo is not responsible for photographic or typographic errors. Warranty: For a copy of applicable warranties, write to: Warranty Information, 500 Park Offices Drive, RTP, NC 27709, U.S.A., Attn: Dept. ZPYA/B600. Lenovo makes no representation or warranty regarding third-party products or services. Trademarks: Lenovo, the Lenovo logo, Rescue and Recovery, ThinkPad, ThinkCentre, ThinkStation, ThinkVantage, ThinkVision, and ThinkColour are trademarks or registered trademarks of Lenovo. Microsoft, Windows, and Vista are registered trademarks of Microsoft Corporation. Intel, the Intel logo, Intel Inside, Intel Core, and Core Inside are trademarks of Intel Corporation in the U.S. and/or other countries. Other company, product, and service names may be trademarks or service marks of others. Specifications may vary depending upon region.

Smarter
technology
for all

Lenovo

ThinkVision T32h-30

