


EP1052T-A - 10.1" SCHEDULING PANEL, MEETING ROOM TOUCH CONTROLLER, POE+, NFC, RFID, WI-FI, CAMERA, MIC, GPIO

## Key Features

---


- Simple Scheduling
- Easy and Secure Cabling
- Interactive On-Demand Messaging
- Content Management Software
- Door Lock Control
- Enterprise Secured Solution
- Two-Way Communication
- Simple Yet Powerful
- 1-year Limited Warranty



10  
DISPLAY



IPS-Type  
PANEL



RESOLUTION



## Product Description

---


The ViewSonic® EP1052T-A is a 10.1" all-in-one interactive digital ePoster that can be used as a video conferencing touch controller, meeting room scheduler and communication signage display. For video conferencing, the EP1052T-A provides one-touch join, easy content-sharing, and a seamless meeting experience across all rooms. When used with certified room scheduling software such as EMS, PLANON, APPSPACE, PRONESTOR and more, the EP1052T-A simplifies meeting room scheduling. The EP1052T-A is also ideal for interactive signage, information kiosks and other on-demand messaging. Filled with user-friendly features like Signage Manager Express software, Power over Ethernet one-wire installation, door lock access control - and so much more - it makes loading, playing and managing content easy and reliable.

## Specifications

---

|                                    |                                  |
|------------------------------------|----------------------------------|
| <b>Screen Size</b>                 | 10                               |
| <b>Viewable Area (in.)</b>         | 10.1                             |
| <b>Display Resolution</b>          | 1280 x 800                       |
| <b>Light Source</b>                | LED                              |
| <b>Orientation</b>                 | Landscape / Portrait             |
| <b>Static Contrast Ratio</b>       | 1,000:1                          |
| <b>Brightness</b>                  | 350 cd/m2                        |
| <b>Colors</b>                      | 16.7M                            |
| <b>Viewing Angles</b>              | 160° horizontal, 160° vertical   |
| <b>Backlight Life (Hours)</b>      | 10,000                           |
| <b>Response Time (Typical GTG)</b> | 16ms                             |
| <b>Panel Surface</b>               | Anti-glare, Hard coating (3H)    |
| <b>Panel Type</b>                  | IPS-Type                         |
| <b>Operation Rating</b>            | 16/7                             |
| <b>Microphone</b>                  | Yes                              |
| <b>Internal Speakers</b>           | 2W (x2)                          |
| <b>3.5mm Audio Out</b>             | 1                                |
| <b>3.5mm Mic In</b>                | 1                                |
| <b>Ethernet LAN (RJ45)</b>         | 1                                |
| <b>USB 2.0 Type A</b>              | 2                                |
| <b>Micro USB</b>                   | 1                                |
| <b>Micro SD Card Slot</b>          | 1                                |
| <b>DC Jack (12V/4A)</b>            | 1                                |
| <b>GPIO</b>                        | 1                                |
| <b>Media Player Type</b>           | Yes                              |
| <b>CPU</b>                         | Octa-core ARM Cortex-A53         |
| <b>Operating System</b>            | Android™ 9.0                     |
| <b>RAM</b>                         | 2GB                              |
| <b>Storage Capacity</b>            | 16GB                             |
| <b>Storage Type</b>                | eMMC                             |
| <b>Touch Technology</b>            | Capacitive                       |
| <b>Touch Points</b>                | 10-Point Touch                   |
| <b>Voltage</b>                     | AC 100-240V (universal), 50-60Hz |
| <b>Consumption (max)</b>           | 20W                              |
| <b>Consumption (typical)</b>       | 16W                              |
| <b>Stand-by</b>                    | <2W                              |

|                                  |  |
|----------------------------------|--|
| <b>Temperature</b>               | 32-104° F (0 - 40° C)  |
| <b>Humidity (non-condensing)</b> | 10-85%   |
| <b>Ethernet LAN</b>              | 10/100/1000 Mbps   |
| <b>Wifi</b>                      | 802.11ac (2.4GHz/5GHz)   |
| <b>VESA Compatible</b>           | 75 x 75 mm   |
| <b>Gross (lbs)</b>               | 3.2  |
| <b>Net (lbs)</b>                 | 2.3  |
| <b>Gross (kg)</b>                | 1.45   |
| <b>Net (kg)</b>                  | 0.92   |
| <b>Packaging (in.)</b>           | 18.9 x 11.0 x 13.8   |
| <b>Physical (in.)</b>            | 10.28 x 7.12 x 1.14  |
| <b>Packaging (mm)</b>            | 480 x 280 x 350  |
| <b>Physical (mm)</b>             | 261 x 181 x 29   |
| <b>Regulations</b>               | CE / FCC / RoHS  |
| <b>PACKAGE CONTENTS</b>          | EP1052T-A, Quick Start Guide, Flush Wall Mount Bracket, Glass Mount 3M Tape, Mounting Sheet, Cover Sheet, Screws |
| <b>Recycle/Disposal</b>          | Please dispose of in accordance with local, state or federal laws.   |
| <b>Warranty</b>                  | One-year limited warranty on parts and labor   |



**Contact Sales**  
[ViewSonic.com](http://ViewSonic.com)  
 888.881.8781  
 email:  
[salesinfo@viewsonic.com](mailto:salesinfo@viewsonic.com)