



# HP DesignJet SD Pro 2 44-in MFP (1GY94E)



## Overview

### Highly productive 44-in MFP for fast and detailed document reproduction

Quickly print and scan documents, maps, and drawings with the HP DesignJet SD Pro 2 MFP. See high-quality results at fast speeds. Accelerate workflows and handle even the most complex files with this reliable, secure printer.

#### Detailed document reproduction with CIS technology

Scan and copy everyday documents and maps at high speeds without fringing, using advanced CIS technology.

#### Reliable dual-roll 44-in PostScript® printer

Print on different paper types and sizes seamlessly, and save time using two rolls with smart switching.

#### A fast SD scanner designed to streamline workflows

Scan fast—up to 9 inches/sec (22.8 cm/sec) in color and 18 inches/sec (45.7 cm/sec) in grayscale.

---

## Specifications

<b>Print quality color (best)</b>	Up to 2400 x 1200 optimized dpi
<b>Functions</b>	Print, copy, scan
<b>Connectivity, standard</b>	Printer: Gigabit Ethernet (1000Base-T) (802.3, 802.3u, 802.3ab), USB Type-A host port; Scanner: Gigabit Ethernet (1000Base-T), USB 3.1 gen 1 (3+1) and USB 2.0 (1) rear
<b>Connectivity, optional</b>	Printer: HP USB 3.0 to Gigabit LAN Adapter
<b>Software included</b>	HP Click, HP Utility for Mac and Windows, HP WebJet Admin, HP Embedded Web Server, HP JetAdvantage Security Manager, HP Partner Link, HP MPS, integrated software with scan and copy enhancement features
<b>Energy star certified</b>	No
<b>Scan file format</b>	PDF, PDF/A, TIFF, JPEG, JPEG2000, DWF, multi-page PDF generation
<b>Scan input modes</b>	File, email, USB, HDD, network folder, FTP, print
<b>Scanner type</b>	CIS scanning technology
<b>Minimum dimensions (W x D x H)</b>	Printer: 1802 x 695 x 998 mm; Scanner: 1530 x 930 x 1660 mm
<b>Minimum dimensions (W x D x H)</b>	Printer: 70.9 x 27.4 x 39.3 in; Scanner: 60 x 37 x 65 in
<b>Weight</b>	Printer: 74 kg; Scanner: 60 kg
<b>Weight</b>	Printer: 163 lb; Scanner: 132 lb
<b>Power consumption</b>	Printer: <100 W (printing); <24 W (ready); <6.5 W (sleep); 0.1 W (off); Scanner: 47 W (scanning); 32 W (ready); 1.8 W (sleep)
<b>Environmental certification</b>	Printer: ENERGY STAR; WEEE; RoHS (EU, China, Korea, India); REACH; EPEAT; Scanner: ENERGY STAR; WEEE; RoHS (EU, China, Korea, India); REACH; EPEAT
<b>What's in the box</b>	Printer: HP DesignJet T1700dr 44-in PostScript Printer, printheads, ink cartridges, printer stand, spindles (x2), setup poster, introductory information, warranty, power cords, label kits; Scanner: HP SD Pro 2 44-in Scanner, stand, touchscreen (panel PC), quick reference guide, media guides, setup poster, maintenance sheet, copy/scan software, documentation software, Ethernet cable, USB cable, power cords
<b>Manufacturer Warranty</b>	One-year limited hardware warranty

## Additional specifications

<b>Acoustic power emissions (active, printing)</b>	Printer: 6.1 B(A) (operating), 5.0 B(A) (idle), <3.1 B(A)(sleep); Scanner: 6.4 B(A) (operating), <3.3 B(A) (idle), <3.3 B(A) (sleep)
<b>Acoustic pressure emissions</b>	Printer: 45 dB(A) (operating), 32 dB(A) (idle), <15 dB(A)(sleep); Scanner: 62 dB(A) (operating), <30 dB(A) (idle), <30 dB(A) (sleep)
<b>Color(s) of printing supplies</b>	Cyan, magenta, yellow, photo black, matte black, gray
<b>Copier settings</b>	Print mode, output size, paper type, copies, page order, collate, printer output destination (folder, stacker, bin), folding style selection (only available when folder accessory is available and supported by the HP large-format printer), paneling, tiling, nesting, reprint
<b>Copy reduce / enlarge settings</b>	1 to 10000%
<b>Dynamic security</b>	Dynamic security enabled printer
<b>Electromagnetic compatibility</b>	Printer: Compliant with Class B requirements, including: USA (FCC rules), Canada (ICES), EU (EMC Directive), Australia (ACMA), New Zealand (RSM), China (CCC), Japan (VCCI), Korea (KCC), South Africa (SABS); Scanner: Compliance for Class A ITE products: EU (EMC Directive), USA (FCC Rules), Canada (ICES), Australia (ACMA), New Zealand (RSM), China (CCC), Japan (VCCI), Korea (MSIP), Russia (EAC)
<b>Finished output handling</b>	Printer: Sheet feed, two automatic roll feeds, automatic roll-switching, media bin, automatic horizontal cutter; Scanner: Straight-through scan paper path for sheet and cardboard originals. Face-up, front entry, rear exit, rewind to front, use document return guide for front-return.
<b>HP ePrint capability</b>	Yes
<b>Ink drop</b>	6 pl
<b>Ink types</b>	Dye-based (C, M, Y, PK, G); pigment-based (MK)
<b>Interface</b>	15.6" (396-mm) large touchscreen to preview and enhance images
<b>Internal Storage</b>	Printer: 500 GB self-encrypting; Scanner: 256 GB SSD
<b>Line accuracy</b>	±0.1%[2]
<b>Linear scan speed</b>	Color: up to 9 in/sec; Grayscale: up to 18 in/sec[3]
<b>Linear scan speed</b>	Color: up to 22.8 cm/sec; Grayscale: up to 45.7 cm/sec[3]
<b>Maximum media thickness</b>	2 mm
<b>Maximum optical density (black)</b>	2.15 maximum black optical density (6 L*min)
<b>Media sizes standard (metric rolls)</b>	279 to 1118 mm
<b>Media sizes standard (sheets, rolls)</b>	11 to 44 in
<b>Media sizes supported</b>	A, B, C, D, E
<b>Media sizes supported</b>	A4, A3, A2, A1, A0
<b>Media sizes, custom</b>	8.3 x 11 to 44 x 66 in
<b>Media sizes, custom</b>	210 x 279 to 1118 x 1676 mm

<b>Media thickness</b>	0.08 in
<b>Media thickness</b>	Up to 31.5 mil
<b>Media thickness (metric)</b>	Up to 0.8 mm
<b>Media types</b>	Printer: Bond and coated paper (bond, coated, heavyweight coated, super heavyweight plus matte), technical paper (natural tracing, translucent bond), film (clear, matte), photographic paper (satin, gloss, semi-gloss, matte, high-gloss), backlit, self-adhesive (polypropylene, vinyl); Scanner: Non-abrasive paper, sepia, blueprints, plastic, plastic laminate, foam board, cardboard, newspaper (no plywood, stone plates, metal plates or abrasive, dirty, rough, sharp edged, metal clamped, or burned surfaces or transparencies)
<b>Media weight, recommended</b>	60 to 328 g/m <sup>2</sup>
<b>Media width, maximum</b>	44 in
<b>Media width, maximum</b>	1118 mm
<b>Memory</b>	Printer: 128 GB file processing (based on 4 GB RAM); Scanner: 8 GB DDR4
<b>Model size</b>	44 in
<b>Model size</b>	1118 mm
<b>Network ready</b>	Standard
<b>Non-Operating Humidity Range</b>	0 to 90% RH
<b>Number of print cartridges</b>	6 (C, M, Y, G, pK, mK)
<b>Operating humidity range</b>	20 to 80% RH
<b>Operating temperature range</b>	5 to 40°C
<b>Operating temperature range</b>	41 to 104°F
<b>Package dimensions (W x D x H)</b>	77.8 x 30.2 x 49.6 in
<b>Package dimensions (W x D x H)</b>	1950 x 766 x 1260 mm
<b>Package weight</b>	470 lb
<b>Package weight</b>	213 kg
<b>Playbook TS icon dimensions</b> AiO	<a href="https://h10003.www1.hp.com/digmedialib/prodimg/lowres/c08192862.png">https://h10003.www1.hp.com/digmedialib/prodimg/lowres/c08192862.png</a>
<b>Power</b>	Printer: Input voltage (auto ranging) 100-240 V (±10%), 50/60 Hz (±3 Hz), 2 A max; Scanner: Input voltage (auto ranging): 100-240 V (±10%), 50/60 Hz, 5 A max
<b>Print Technology</b>	Ink
<b>Print cartridge volume delivered</b>	300 ml (C, M, Y, G, pK, mK); 130 ml (C, M, Y, G, pK, mK)
<b>Print head nozzles</b>	2112 each color
<b>Print heads</b>	3 universal printheads, 2 colors each
<b>Print languages</b>	Adobe PostScript 3, Adobe PDF 1.7 ext 3, HP-GL/2, TIFF, JPEG, URF, CALS G4
<b>Print speed</b>	116 A1/hr, 26 sec/A1[1]
<b>Print speed</b>	116 D/hr, 26 sec/D[1]
<b>Print technology</b>	HP Thermal Inkjet

<b>Printer drivers included</b>	Printer: Raster drivers for Windows and macOS, PostScript and PDF Windows drivers and macOS PostScript driver; Scanner: Windows drivers for compatible HP PageWide XL and HP DesignJet Printers
<b>Printing path</b>	Direct printing from USB flash drive, email printing, HP driver for Windows, HP Print Service for Android, Apple AirPrint for MacOS and for iOS, HP Print for Chrome OS, HP Click, HP Smart App for iOS and Android
<b>Product logos</b>	Adobe PDF Print Engine 4; Adobe PostScript 3; ENERGY STAR; EPEAT; Gold IPv6 Ready; Intel Inside Core i5; Mac; PANTONE® Digital Color; Windows 10 Compatible
<b>Recommended media</b>	HP Bright White Inkjet Paper (FSC® certified)[4] (Recyclable)[5];HP Heavyweight Coated Paper (Recyclable)[5];HP Universal Instant-dry Satin Photo Paper (FSC® certified)[4] (Recyclable)[5];HP Universal Coated Paper (FSC® certified)[4] (Recyclable)[5]
<b>Roll external diameter</b>	135 mm
<b>Roll external diameter</b>	5.3 in
<b>Roll maximum input</b>	2
<b>Roll maximum weight</b>	26.3 lb
<b>Roll maximum weight</b>	11.9 kg
<b>Safety</b>	Printer: USA and Canada (CSA certified); EU (LVD and EN 60950-1 compliant); Russia, Belarus, Kazakhstan (EAC); Singapore (PSB); China (CCC); Argentina (IRAM); India (BIS); Scanner: USA and Canada (UL certified), EU (LVD and EN 60950-1 compliant), Russia (EAC), Singapore (PSB), China (CCC), Argentina (IRAM), Mexico (NYCE), Korea (KC)
<b>Scan resolution, optical</b>	1200 dpi
<b>Scan size, maximum</b>	44 in
<b>Scan size, maximum</b>	1118 mm
<b>Scan size, minimum</b>	6 x 4.5 in
<b>Scan size, minimum</b>	152 x 114 mm
<b>Security features</b>	HP Secure Boot, Whitelisting, Role Based Access Control, SNMPv3, HTTPS, Secure-IPP, IPsec/Firewall, Certificates management, 802.1X, TLS 1.0/1.1/1.2, HP Web Jetadmin compatible, HP JetAdvantage Security Manager compatible, Secure Disk erase (DoD 5220.22-M), Secure File erase, self-encrypting HDD, PIN printing
<b>Storage temperature range</b>	-25 to 55°C
<b>Storage temperature range</b>	-13 to 131°F
<b>Supported Primary Applications</b>	Line drawings; Maps; Orthophotos; Presentations; Renderings
<b>Theoretical minimum line width</b>	0.02 mm (PDF addressable @ 1200 dpi)
<b>Theoretical minimum line width</b>	0.0008 in (PDF addressable @ 1200 dpi)
<b>UNSPSC code</b>	43212104
<b>UPC number</b>	(ABG) 196786156304; (ACJ) 196786156328; (B1K) 196786156342; (BCD) 196786156366
<b>Web address for additional information</b>	<a href="http://www.hp.com/go/DesignJet-SD-Pro-2-MFP">http://www.hp.com/go/DesignJet-SD-Pro-2-MFP</a>

# Ink/Toner/Paper/Printer Supplies

## Ink Supplies

★ : Recommended

### HP Graphic Arts Inks/Printheads

HP 730 130-ml Cyan DesignJet Ink Cartridge	P2V62A
HP 730 130-ml Gray DesignJet Ink Cartridge	P2V66A
HP 730 130-ml Magenta DesignJet Ink Cartridge	P2V63A
HP 730 130-ml Matte Black DesignJet Ink Cartridge	P2V65A
HP 730 130-ml Photo Black DesignJet Ink Cartridge	P2V67A
HP 730 130-ml Yellow DesignJet Ink Cartridge	P2V64A
HP 730 300-ml Cyan DesignJet Ink Cartridge	P2V68A
HP 730 300-ml Gray DesignJet Ink Cartridge	P2V72A
HP 730 300-ml Magenta DesignJet Ink Cartridge	P2V69A
HP 730 300-ml Matte Black DesignJet Ink Cartridge	P2V71A
HP 730 300-ml Photo Black DesignJet Ink Cartridge	P2V73A
HP 730 300-ml Yellow DesignJet Ink Cartridge	P2V70A
HP 730B 130-ml Cyan DesignJet Ink Cartridge	3ED42A
HP 730B 130-ml Gray DesignJet Ink Cartridge	3ED44A
HP 730B 130-ml Magenta DesignJet Ink Cartridge	3ED41A
HP 730B 130-ml Matte Black DesignJet Ink Cartridge	3ED45A
HP 730B 130-ml Photo Black DesignJet Ink Cartridge	3ED43A
HP 730B 130-ml Yellow DesignJet Ink Cartridge	3ED40A
HP 730B 300-ml Cyan DesignJet Ink Cartridge	3ED48A
HP 730B 300-ml Gray DesignJet Ink Cartridge	3ED50A
HP 730B 300-ml Magenta DesignJet Ink Cartridge	3ED47A
HP 730B 300-ml Matte Black DesignJet Ink Cartridge	3ED51A
HP 730B 300-ml Photo Black DesignJet Ink Cartridge	3ED49A
HP 730B 300-ml Yellow DesignJet Ink Cartridge	3ED46A
HP 730F 300-ml Cyan DesignJet Ink Cartridge	1XB27A
HP 730F 300-ml Gray DesignJet Ink Cartridge	1XB29A
HP 730F 300-ml Magenta DesignJet Ink Cartridge	1XB26A
HP 730F 300-ml Matte Black DesignJet Ink Cartridge	1XB30A
HP 730F 300-ml Photo Black DesignJet Ink Cartridge	1XB28A
HP 730F 300-ml Yellow DesignJet Ink Cartridge	1XB25A

HP 731 DesignJet Printhead

P2V27A

## Accessories

### Paper Handling

★ : Recommended

#### Roll Core Adapters

HP DesignJet 3-in Core Adapter

CN538A

#### Spindles

HP DesignJet 44-in Spindle

Q6709A

#### Output Trays and Stackers

HP Pro Scanner Output Delivery Tray

P7V13A

### Network Print Servers

#### External Print Servers

HP Jetdirect 3100w BLE/NFC/Wireless Accessory

3JN69A

## Software

### Printing and Imaging Software

★ : Recommended

#### Printer Management Software

HP SmartStream Preflight Manager	8SW00AAE
HP SmartStream Print Controller USB for HP DesignJet Printers	8SW01A
HP SmartStream Print Controller for HP DesignJet Printers	8SW01AAE
HP SmartStream USB Preflight Manager	8SW00A
HP SmartTracker USB for DesignJet	8SW11A
HP SmartTracker for DesignJet	8SW11AAE

---

### Disclaimer — Copyright

© Copyright 2024 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Generated by Dynamic Collateral Tool – (ww-en) – Aug 28, 2024 5:08 AM UTC+0000