




SPECIFICATIONS

Size:	23.8" FHD Flat Monitor
Display Size:	21.02" (H) x 12.13" (V)
Display Mode:	VA Mode
Brightness (Typ):	250cd/m2
Contrast (Typ):	3000:1 (Typical)
Resolution (H x V):	1920 x 1080
Aspect Ratio:	16:9
Display Colors:	16.7M Colors
Max. Display Frequency (Resolution H*V/Fv)	1920 x 1080 / 75Hz

Ports:	1 x HDMI Port
	1 x VGA Port
	1 x Audio Jack 3.5mm
	1 x Speaker
Consumption (Typical):	On: Type 17W; Max: 22W Standby<=0.5W
AC Power Range:	DC: 12V-3A
Multi-Language:	English, Spanish, French, Portuguese, Dutch
Temperature:	0°C ~ 35°C
Humidity:	20% ~ 85%, non-condensing
VESA Mountable:	75mm x 75mm
Cable:	1 x HDMI, 1 x VGA



HDMI Cable
Included



VGA Port



Aspect Ratio



3000:1