

ProductSheet
HP P24v G5 FHD Monitor (64W18A6)



Everyday Productivity

Expand your view and your productivity with this 23.8-inch diagonal, FHD monitor when you're working from home or at the office. This sleek monitor makes hybrid work easy and complete via a crisp, smooth screen and simple design, so you can do more everyday.

In Full View

Enjoy a productive, hybrid work experience with excellent front-of-screen views. This monitor boasts FHD resolution and 75Hz refresh rate^[1] for sharp images and fluid motion.

Modern Design. Functional Fit.

Clear your mind and your desk with a monitor designed to work in any space. Keep the focus on your screen through the sleek 3-sided micro-edge bezel, neat cable management, and slim stand with adjustable tilt for your perfect view.

Easy Control. Easy Management.

Make your workspace as simple as possible, so you can concentrate on what you do best. Easily setup your monitor by customizing your settings with the intuitive Joypad OSD button or manage settings and updates directly from the screen with HP Display Center^[2] and Display Manager^[3].

Featuring

75 Hz Refresh Rate

Experience smooth, life-like video and clear detail with a 75 Hz refresh rate that provides fluid movement from frame to frame. ^[1]

3-Sided Micro-Edge Bezel

See and do more on your screen with a 3-sided micro-edge bezel that maximizes your viewing area for a sleek design and seamless dual-monitor setups.

Easy Joypad OSD Button

It's never been easier to configure your display with the Joypad OSD button to adjust brightness, resolution, and volume.

Low Blue Light Mode

Keep your eyes comfortable with subtly warmer display colors onscreen.

With the Environment in Mind

Meeting the latest standards with EPEAT[®] registered, ENERGY STAR[®] and TCO certifications. ^[4]

Specifications

Display size (diagonal)	23.8"
Panel technology	VA
Display size (diagonal)	60.5 cm (23.8")
Aspect ratio	16:9 ^[1]
Native resolution	FHD (1920 x 1080) ^[1,2]
Resolutions supported	640 x 480; 720 x 400; 800 x 600; 1024 x 768; 1280 x 720; 1280 x 800; 1280 x 1024; 1440 x 900; 1600 x 900; 1680 x 1050; 1920 x 1080
Pixel pitch	0.27 x 0.27 mm
Brightness	250 nits ^[1]
Contrast ratio	3000:1 ^[1]
Response time (typical)	5ms GtG (with overdrive) ^[1]
Minimum dimensions (W x D x H)	53.89 x 5.14 x 32.36 cm (Without stand.)
Minimum dimensions (W x D x H)	21.22 x 2.02 x 12.74 in (Without stand.)
Dimensions With Stand (W x D x H)	53.89 x 18.05 x 39.78 cm
Weight	3.57 kg (With stand.)
Weight	7.86 lb (With stand.)
Display features	On-screen controls; Low blue light mode; Anti-glare
Onscreen controls	Brightness; Input control; Management; Information; Exit; Color control; Image control; Power control; Menu control
Display colors	Up to 16.7 million colors supported ^[3]
Display scan frequency (horizontal)	55.6-90.8 kHz
Display scan frequency (vertical)	48-75 Hz
Camera	No integrated camera
Power	100 - 240 VAC 50/60 Hz
Power consumption	30 W (maximum), 20 W (typical), 0.5 W (standby)
Operating temperature range	5 to 35°C
Operating humidity range	20 to 80% RH
Sustainable impact specifications	Molded paper pulp cushion inside box is 100% sustainably sourced and recyclable; 85% ITE-derived closed loop plastic; Low Halogen
Certifications and compliances	Australian-New Zealand MEPS; BIS; BSMI; CB; CCC; CE; CECP; CEL; CSA; EAC; ENERGY STAR®; FCC; ISO 9241-307; KC/KCC; Microsoft WHQL Certification; NOM; PSB; RoHS; SEPA; TCO Certified; TCO Certified Edge; TUV Bauart; TUV LBL; VCCI; Vietnam MEPS; WEEE; ISC; China Energy Label (CEL) Grade 2; California Energy Commission (CEC); WW application; ICE; UAE; Ukraine certificates; NRCS of South Africa; TÜV Flicker free certified
Physical security	Security lock-ready ^[10]
Management Software	HP Display Center; HP Display Manager
UPC number	196548685561
Manufacturer Warranty	3 years limited warranty
What's in the box	Monitor; HDMI cable; Warranty card; Quick Setup Poster; Doc-kit; AC power cord ^[9]

Top Recommended Displays, Accessories and Services

Personal Systems Commercial Care Pack Services

HP 4y Next Business Day Response Advanced Exchange Large DisplayHardware Support	U0J12E
HP 5y Next Business Day Response Advanced Exchange Large DisplayHardware Support	U0J13E

Messaging Footnotes

[1] All performance specifications represent the typical specifications provided by HP's component manufacturers; actual performance may vary either higher or lower.

[2] Host PC requires Windows 10 or higher. HP Display Center is available on the Microsoft store.

[3] HP Display Manager software agent must be running on a web server and host PC. Some limitations may apply to legacy monitors.

[4] Based on US EPEAT® registration according to IEEE 1680.1-2018 EPEAT®. EPEAT® status varies by country. Visit www.epeat.net for more information.

Technical Specifications Footnotes

[1] All specifications represent the typical specifications provided by HP's component manufacturers; actual performance may vary either higher or lower.

[2] HDMI 1.4 or VGA required to drive panel at its native resolution. The video card of the connected PC must be capable of supporting 1920 x 1080 at 60 Hz with 8-bit color using one HDMI or VGA. The video card of the connected PC must be capable of supporting 1920 x 1080 and include one HDMI or one VGA outputs to drive the monitor at the Preferred Mode.

[3] Number of colors through A-FRC technology.

[9] Included cables may vary by country.

[10] Lock sold separately.

Learn more at
hp.com

© Copyright 2023 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

EPEAT® is a registered trademark of Green Electronics Council. ENERGY STAR® is a registered mark owned by the U.S. government.

