

UHD35x

Bright, True 4K UHD gaming and home entertainment projector



- **True 4K UHD resolution - HDR and HLG compatible**
- **Lights on viewing - 3600 lumens for use any time of day**
- **Lightning fast gaming projector - Delivers 1080p 240Hz with an ultra-low input lag of 4.2ms**
- **Full 3D compatible - Experience life-like big-screen entertainment**



Immerse yourself in a world of Ultra HD gaming, live sports, TV shows and movies. The lightning-fast, low latency 4K UHD UHD35x delivers impressive cinema-quality images, an ultra-low input lag of 4.2ms and a high refresh rate of 240Hz - perfect for a competitive gaming advantage.

TV and movie fans can also enjoy excellent colour depth, crystal clear detail, and sparkling contrast for a stunningly immersive experience.

Specifications

Display/image	
Display technology	DLP™
Resolution	UHD (3840x2160)
Brightness	3,600 lumens
Contrast ratio	1,000,000:1
Native aspect ratio	16:9
Aspect ratio - compatible	4:3
Keystone correction - horizontal	+/-40°
Keystone correction - vertical	+/-40°
Horizontal scan rate	31 ~ 135Khz
Vertical scan rate	24 ~ 120Hz
Uniformity	80%
Screen size	0.84m ~ 7.62m (33" ~ 300") diagonal
Lamp info	
Light source type	Lamp
Lamp watts	240
Lamp life hours (up to)	4000 (Bright), 15000 (Dynamic), 10000 (Eco)
Optical	
Throw ratio	1.5:1 ~ 1.66:1
Projection distance (m)	1.21m - 9.9m
Zoom	1.1
Zoom type	Manual
Focal length (mm)	15.84 mm~17.42mm/0.624"~0.686"
Lens shift	Vertical +0%
Native offset	105%
Connectivity	
Connections	Inputs 2 x HDMI 2.0 Outputs 1 x Audio 3.5mm, 1 x S/PDIF, 1 x USB-A power 1.5A Control 1 x RS232, 1 x 12V trigger
General	
Noise level (typical)	26dB
Noise level (max)	28dB
PC compatibility	UHD, WQHD, WUXGA, FHD, UXGA, SXGA, WXGA, HD, XGA, SVGA, VGA, Mac
2D compatibility	480i/p, 576i/p, 720p(50/60Hz), 1080i(50/60Hz), 1080p(50/60Hz), 2160p(50/60Hz)
3D compatibility	Frame-pack: 1080p24, 720p50 / 60
3D	Full 3D
Security	Security bar, Kensington Lock, Password protected interface
OSD / display languages	10 languages: English, French, German, Italian, Japanese, Portuguese, Russian, Chinese (simplified), Spanish
Operating conditions	5°C~40°C/41°F~104°F, max altitude 3000M/9843ft, max humidity 85%
Remote control	Backlit home remote
Speaker count	1
Watts per speaker	10W
In the box	AC power cord Remote control 2x AAA batteries Basic user manual
Input lag	4.20ms
Power	
Power supply	100 ~ 240V, 50 ~ 60Hz
Power consumption (standby)	0.5W
Power consumption (min)	220W
Power consumption (max)	305W
Weight and dimensions	
Dimensions (W x D x H) mm	315 x 270 x 118
Gross weight	4.68 kg
Net weight	3.98 kg

