



## USB Drive | C175



Team Group releases the rounded C175 USB drives with black color. C175 looks like mysterious, luxury black pearl born from the deep blue ocean. The streamlined unibody design is able to offer users a well-rounded and comfortable hand held feeling.

### Main Feature

- Rounded and streamlined appearance
- Ingenious seamless design
- Thoughtful cap-loss free design for easy storage
- Plug and play interface
- Support hot swap
- Support power saving mode
- Lifetime warranty with free technical support service

### Specification

Interface	USB 3.2 Gen 1
Capacity	16GB / 32GB / 64GB / 128GB / 256GB / 512GB / 1TB <sup>[1]</sup>
Color	Black
Voltage	DC +5V
Weight	9g
Dimensions	54.9(L) x 20.5(W) x 9.5(H) mm
Operating System	Windows XP or later, Mac OS, Linux 2.6 or later
Transmission rate	16GB-32GB: Read speed up to 75MB/s 64GB-1TB: Read speed up to 100MB/s
Warranty	Lifetime warranty

### Ordering Information

Capacity	Team P/N
16GB	TC175316GB01
32GB	TC175332GB01
64GB	TC175364GB01
128GB	TC1753128GB01
256GB	TC1753256GB01
512GB	TC1753512GB01
1TB	TC17531TBB01



[1] Part of the capacity of FLASH storage products will be used for formatting or other functions, and the displayed capacity in the operating system will be less than the actual storage capacity due to unit conversion. It is recommended to calculate the actual storage capacity based on this equation: total bytes/1024/1024/1024.  
 ※We reserve the right to modify product specifications without prior notice.