



## Low printing costs, high-quality output, productivity enhancing features

### Business Color Laser All-in-One Printer

The Brother MFC-L8905CDW is designed for how work now works - providing fast speeds, Triple Layer Security features, and expandable paper handling ideal for small to mid-sized workgroups with higher print volumes.

- Fast printing up to 33ppm color / black<sup>1</sup>
- 9,000-page black, 8,000-page color replacement toner cartridges help reduce operating costs<sup>18</sup>
- 7" color touchscreen display enables creating up to 64 customized shortcuts
- 70-page capacity auto document feeder<sup>14</sup> offers scan speeds up to 58ipm<sup>4</sup>
- Built-in wireless and Gigabit Ethernet interfaces plus mobile device printing and scanning<sup>9</sup>

# MFC-L8905CDW

Color Laser All-in-One Printer with Duplex Print/Copy/Scan and Wireless Networking

**brother**  
at your side

## Specifications:

Print	
Print Technology	Electrophotographic Laser
Print Speeds (max.) <sup>1</sup>	Up to 33ppm color / black
Time to First Page <sup>2</sup>	Less than 15 seconds color / black
Print Resolution (max.) <sup>3</sup>	Up to 2400 x 600 dpi class
Print Emulations	PCL6 (PCL XL Class 3.0), BR-Script <sup>3</sup> , PDF Version 1.7, XPS Version 1.0
Pantone Calibrated <sup>®</sup>	Yes
Scan	
Scan Speeds (max.) <sup>4</sup>	Simplex: Up to 29ppm (black / color) Duplex: Up to 58ipm (black / color)
Scan Resolution (max.)	Optical: Up to 1200 x 2400 dpi Interpolated: Up to 19200 x 19200 dpi
Scan To Capability	PC (File, Image, Email, OCR), Email Server <sup>5</sup> , FTP, SSH Server (SFTP), USB memory stick <sup>6</sup> , SharePoint, Cloud Services (Web Connect) <sup>7</sup> , Network Folder <sup>8</sup> , Mobile Devices <sup>9</sup> , Easy Scan to Email <sup>10</sup>
Advanced Scanning Features	Continuous scan, Scan profiles, Auto deskew, Blank page skip, Setting lock, Base color removal, Multi-page to single-page
Copy	
Copy Speed / Copy Resolution (max.)	Up to 33ppm / Up to 1200 x 600 dpi
Copy Options	Sorting, N-in-1, Multi-copying (up to 99), ID Copy, Reduce / Enlarge 25 - 400% in 1% increments
Fax	
Fax Features	33.6K bps modem speed, Fax page memory: up to 500 pages <sup>11</sup> , Fax forward to: Network Folder and Email, Internet Fax <sup>10</sup> , PC Fax <sup>12</sup>
Connectivity & Compatibility	
Standard Interfaces	Wireless 802.11b/g/n, Gigabit Ethernet, Hi-Speed USB 2.0
USB Host	Front: Print from and scan to USB memory stick; external card reader Back: External card reader
Operating Systems Compatibility <sup>13</sup>	Windows 10 Home, 10 Pro, 10 Education, 10 Enterprise, 11 Home, 11 Pro, 11 Education, 11 Enterprise; Windows Server 2012, 2012 R2, 2016, 2019, 2022 macOS v10.10.5, v10.11.x, v10.12.x, v10.13.x, v10.14.x, v10.15.x, v11, v12 Linux, Windows Universal Print Driver
Mobile Device Compatibility <sup>9</sup>	AirPrint <sup>®</sup> , Brother iPrint&Scan, Mopria <sup>™</sup> , Wi-Fi Direct <sup>®</sup>
Cloud Services (Web Connect) <sup>7</sup>	Google Drive <sup>™</sup> , Evernote <sup>™</sup> , OneDrive, OneNote, Dropbox, Box, SharePoint Online
Brother Cloud Apps <sup>10</sup>	Easy Scan to Email, Scan to Mobile, Cloud Secure Print, Attach, Email and Print, Fax Forward to Cloud or Email, Scan to Word, Scan to Excel, Scan to PowerPoint, Scan to Searchable PDF, Enlarge Text Copy
Security	
Security Features	Integrated NFC Card Reader, Active Directory, External Card Reader Compatibility, LDAP, Secure Function Lock, Enterprise Security (802.1x), SMB v3, Syslog Reporting, SNMP v3, IP Filter, Secure Print, TLS/SSL, IPSec
Paper Handling	
Paper Input Capacity (max.) <sup>14</sup>	250-sheet capacity paper tray, 50-sheet capacity multipurpose tray
Optional Input Capacity (max.) <sup>14</sup>	1,300 sheets via optional trays
Output Capacity (max.) <sup>14</sup>	150 sheets (face down), 1 sheet (face up)
Document Glass Size	8.5" x 14" (Legal)
Auto Document Feeder Capacity <sup>14</sup>	70 pages
Paper Sizes	Paper Tray: Letter, Legal, Executive, A4, A5, A6 Multipurpose Tray: 3.0" - 8.5" (W) / 5.0" - 14" (L)
Media Types	Standard Paper Tray: 16 to 28 lbs. Multipurpose Tray: 16 to 43 lbs.
Media Weights	Standard Paper Tray: 16 to 28 lbs. Multipurpose Tray: 16 to 43 lbs.
General	
Automatic Duplex Capacity	Print (default setting), plus single-pass copy / scan / fax
Display	7" Color Touchscreen
Customizable Shortcuts	64
Processor	800 MHz
Memory (std. / max.)	512MB / 512MB
Included Software <sup>15</sup>	Kofax PaperPort <sup>™</sup> 14SE with OCR for Windows Brother iPrint&Scan (desktop) for Windows and Mac <sup>®</sup>
Maximum Monthly Duty Cycle <sup>16</sup>	Up to 60,000 pages
Recommended Monthly Volume <sup>17</sup>	Up to 4,000 pages
Warranty	1-year limited warranty

## Replacement Supplies & Optional Accessories:

TN431BK	Standard Yield Toner Cartridge (3,000 pages) <sup>18</sup>
TN431C/M/Y	Standard Yield Toner Cartridge (1,800 pages) <sup>18</sup>
TN433BK	High-Yield Toner Cartridge (4,500 pages) <sup>18</sup>
TN433C/M/Y	High-Yield Toner Cartridge (4,000 pages) <sup>18</sup>
TN436BK	Super High-Yield Toner (6,500 pages) <sup>18</sup>
TN436C/M/Y	Super High-Yield Toner (6,500 pages) <sup>18</sup>
TN437BK	Ultra High-Yield Toner (9,000 pages) <sup>18</sup>
TN437C/M/Y	Ultra High-Yield Toner (8,000 pages) <sup>18</sup>
DR431CL	Drum Unit (30,000 pages) <sup>19</sup>
BU330CL	Belt Unit (50,000 pages) <sup>20</sup>
WT320CL	Waste Toner Box (50,000 pages) <sup>21</sup>
LT-330CL	Optional 250-Sheet Capacity Paper Tray
LT-340CL	Optional 500-Sheet Capacity Paper Tray
CB-1010	Optional 15.7" Printer Cabinet / Stand
GH-1000	Optional Card Hold Reader

## Dimensions / Weights:

Unit Dimensions / Weight	19.5" (W) x 20.7" (D) x 21.6" (H) / 65.4 lbs.
Carton Dimensions / Weight	26.6" (W) x 25.7" (D) x 28.6" (H) / 79.7 lbs.

## Carton Contents:

Brother MFC-L8905CDW, Standard Yield Toner Cartridges (3,000 pages black / 1,800 pages color)<sup>18</sup>, DR431CL Drum Unit (30,000 pages)<sup>19</sup>, Belt Unit (50,000 pages)<sup>20</sup>, Waste Toner Box (50,000 pages)<sup>21</sup>, AC Power Cord, Telephone Line Cord, Quick Setup Guide, Installation CD-ROM



**At your side support.** One-year limited warranty with free online, live chat, or phone technical assistance for the life of your product.



### Working with you for a better environment

At Brother, our green initiative is simple. We strive to take responsibility, act respectfully and try to make a positive difference to help build a society where sustainable development can be achieved. We call this approach Brother Earth.

COMPATIBLE WITH  
**WINDOWS**



- Based on one-sided printing. Change from default setting required.
- From ready mode and standard tray.
- PostScript<sup>®</sup> 3<sup>™</sup> compatible.
- Color and monochrome scan speed with all advanced features turned off. Letter at 300dpi.
- Requires mail server support.
- PDF (up to ver. 1.7), JPEG, XPS files. Secure PDF / Signed PDF scan only.
- Requires an Internet connection and an account with desired service.
- Windows only.
- Requires connection to a wireless network.
- Requires an Internet connection.
- Using ITU-T Test Chart #1 with JBIG coding and standard resolution.
- Black/White only. PC Fax Receive not supported for Mac OS<sup>®</sup>.
- For the latest OS compatibility and to download drivers, visit support.brother.com. Printing or scanning via macOS requires the use of AirPrint. Mac printer drivers are not provided. Server 2012/2016/2019 network printing only.
- Maximum capacity based on using 20 lb. paper.
- Requires free download.
- Maximum number of printed pages per month can be used to compare designed durability between like Brother products. For maximum printer life, it is best to choose a printer with a duty cycle that far exceeds your print requirements.
- The recommended range of monthly printed pages to achieve the best possible performance and printer life. Printers are intended to handle occasional usage beyond this range with little or no effect. Consistently printing above the recommended print volume, however, may adversely affect the print quality or life of the machine. It is always best to choose a printer with an appropriate recommended print volume to allow for any anticipated increase in printing needs.
- Approximate toner cartridge yield in accordance with ISO/IEC 19798 (letter/A4).
- Drum yield is approximately 30,000 pages based on 1 page per job and 50,000 pages based on 3 pages per job [letter/A4 simplex pages]. The number of pages may be affected due to a variety of factors including but not limited to media type and media size.
- Yield is approximately 50,000 pages based on 1 page per job and 130,000 pages based on 3 pages per job [letter/A4 simplex pages]. The number of pages may be affected due to a variety of factors including but not limited to media type and media size.
- Approximate yield based on A4 or Letter size single-sided pages.