



HSM Classic 390.3 - 1/32" x 3/16" + external autom. oiler




HSM Classic 390.3 document shredder

The powerful document shredder with particle cut and 148 litres of collection volume. Recommended for the open-plan office for five to eight people.

Technical data

Order number:	16601430	Intake width:	15.75"
EAN	4026631032766	Container volume / collecting:	39.1 gal
Cutting type:	particle cut	Collection volume in sheets (80 g):	2722
Cutting size:	1/32" x 3/16"	Noise level (idle operation):	ca. 60 dB(A)
Security level (DIN 66399):	F-3 P-7	Width x Depth x Height:	23.43" x 20.08" x 36.02"
Cutting capacity in sheets 80g/m²:	6 - 7	Weight:	125.66 lb
Power consumption:	1400 W	Shredder material:	Paper
Voltage / Frequency:	120 V / 60 Hz		

Product information



The high quality materials and proven HSM "Made in Germany" quality guarantee you are receiving a safe and durable machine.

The induction-hardened, solid steel cutting rollers can easily cope with staples and paper clips and guarantee durability.

For a consistently high cutting performance, this low maintenance document shredder has an external automatic oiler.

HSM®



For continuous operation

The powerful motor ensures a high cutting capacity and reliable continuous operation.



Energy-saving

The stand-by feature ensures a high degree of energy saving when the shredder is not in use.



High level of user safety

The device automatically switches off if pressure is applied to the safety element.



Anti-paper jam function

The paper feed with overload protection reduces paper jams and sustains the high throughput of paper.



Mobile on castors

For convenience, there are castors on the document shredder so it is easy to move around.



Convenient emptying

Convenient emptying thanks to the high-quality wooden cabinet with door and pull-out reusable collecting bag.

