



HSM SECURIO B32 - 1/16" x 5/8"




HSM SECURIO B32 document shredder

High quality materials, proven quality – the reliable security partner in the workplace. With an intake width of 310 mm, the document shredder effortlessly shreds DIN A3 paper. It is the perfect device for working groups.

Technical data

Order number:	1822113	Intake width:	12.2"
EAN	4026631028158	Container volume / collecting:	21.7 gal
Cutting type:	particle cut	Collection volume in sheets (80 g):	1043
Cutting size:	1/16" x 5/8"	Noise level (idle operation):	ca. 56 dB(A)
Security level (DIN 66399):	E-4 F-2 P-5 T-5	Width x Depth x Height:	19.57" x 15.67" x 31.22"
Cutting capacity in sheets 80g/m²:	9 - 11	Weight:	59.52 lb
Power consumption:	500 W	Shredder material:	Paper, Staples and paper clips, Credit card
Voltage / Frequency:	120 V / 60 Hz		

Product information



The induction-hardened, solid steel cutting rollers guarantee durability.



The full bin is indicated via the display and the machine switches off automatically.



The device can be intuitively operated with the multifunction element.





For continuous operation

The powerful motor ensures a high cutting capacity and reliable continuous operation.



Energy-saving

In stand-by mode, intelligent control programme EcoSmart ensures there is an exceptionally low power consumption of 0.1 watts.



High level of user safety

The safety element prevents unintentional entry of materials into the machine and thereby increases the user safety.



Automatic start/stop

The operation is very easy: the device starts automatically when fed paper and automatically stops after shredding is complete.




Display bin full

The full bin is indicated via the display and the machine switches off automatically.



Filling level indication

The filling level of the waste container can be seen at all times through the inspection window.



Lifetime warranty on solid steel cutting rollers at security levels P-2 to P-5 (according to ISO/IEC 21964).



*HSM SECURIO B24, B26, B32

www.hsm.eu

