



HSM SECURIO B35 - 3/16" x 1 1/8"




HSM SECURIO B35 document shredder

For more data security in the workplace. The excellent document shredder with an intake width of 400 mm for professional data destruction in an open-plan office for up to eight people.

Technical data

Order number:	1923113	Intake width:	15.75"
EAN	4026631046398	Container volume / collecting:	34.3 gal
Cutting type:	particle cut	Collection volume in sheets (80 g):	1590
Cutting size:	3/16" x 1 1/8"	Noise level (idle operation):	ca. 56 dB(A)
Security level (DIN 66399):	E-3 F-1 O-3 P-4 T-4	Width x Depth x Height:	24.41" x 20.67" x 34.25"
Cutting capacity in sheets 80g/m²:	21 - 22	Weight:	119.93 lb
Power consumption:	700 W	Shredder material:	Paper, Staples and paper clips, Credit card, CD/DVD
Voltage / Frequency:	110-120 V / 60 Hz		

Product information



The induction-hardened, solid steel cutting rollers guarantee durability.



Reusable cardboard box as bin for shredded material.



The full bin is indicated via the display and the machine switches off automatically.

HSM®



For continuous operation

The powerful motor ensures a high cutting capacity and reliable continuous operation.



Energy-saving

In stand-by mode, intelligent control programme EcoSmart ensures there is an exceptionally low power consumption of 0.1 watts.



High level of user safety

The safety element prevents unintentional entry of materials into the machine and thereby increases the user safety.



Automatic start/stop

The operation is very easy: the device starts automatically when fed paper and automatically stops after shredding is complete.




Anti-paper jam function

The paper feed with overload protection reduces paper jams and sustains the high throughput of paper.



Convenient emptying

Robust wooden cabinet with castors. After opening the door, the reusable collecting bag can be easily removed and emptied.



Lifetime warranty on solid steel cutting rollers at security levels P-2 to P-5 (according to ISO/IEC 21964).

