

PERFORMANCE

Processor

Intel® Celeron® 7305, 5C (1P + 4E) / 6T, P-core 1.1GHz, E-core 0.9GHz, 8MB

Graphics

Integrated Intel UHD Graphics

Chipset

Intel SoC Platform

Memory

1x 8GB SO-DIMM DDR4-3200

Memory Slots

Two DDR4 SO-DIMM slots, dual-channel capable

Max Memory

Up to 32GB DDR4-3200

Storage

64G EMMC 5.1

Storage Support

One drive, up to 256GB M.2 2280 SSD or 64GB eMMC 5.1 on systemboard

Audio Chip

High Definition (HD) Audio, Realtek® ALC5682I codec

Power Supply

65W 89% Adapter

DESIGN

Keyboard

USB Chrome Keyboard, Black, English

Mouse

USB Calliope Mouse, Black

Expansion Slots

One M.2 slot (for WLAN, models with Celeron processor)

Case Color

Black

Stand

Vertical Stand

Adapter Cage

None

Dust Filter

None

Mounting

None

Form Factor

Tiny (1L)

Dimensions (WxDxH)

178 x 182 x 34 mm (7 x 7.16 x 1.33 inches)

Weight

Around 1.07 kg (2.35 lbs)

CONNECTIVITY

Ethernet

Integrated 100/1000M

WLAN + Bluetooth®

Intel AX211 Wi-Fi® 6E, 11ax 2x2 + BT5.1

Front Ports

- 2x USB 3.2 Gen 2
- 1x USB-C® 3.2 Gen 2 (with DP 1.4)
- 1x headphone / microphone combo jack (3.5mm)

Rear Ports

- 4x USB 3.2 Gen 1
- 1x Ethernet (GbE RJ-45)
- 1x HDMI® 2.1 TMDS
- 1x DisplayPort™ 1.4

Optional Rear Ports (configured)

1x HDMI 2.1 TMDS

Monitor Cable

None

SECURITY & PRIVACY

Security Chip

Google Security Chip H1

Physical Locks

Kensington® Security Slot™

Kensington Cable Lock

Kensington Cable Lock

MANAGEABILITY

System Management

Non-vPro®

SERVICE

Base Warranty

1-year, Courier or Carry-in

Included Upgrade

None

CERTIFICATIONS

Green Certifications

- EPEAT™ Gold
- ENERGY STAR® 8.0

Mil-Spec Test

MIL-STD-810H military test passed (Low Pressure [Altitude], High Temperature, Low Temperature, Temperature Shock, Humidity, Sand and Dust, Vibration, Shock, Fungus, Solar Radiation, Contamination by Fluids, Salt Fog)

SOFTWARE

Operating System

ChromeOS

Bundled Software

None

MODEL

TopSeller : Yes

Announce Date : 2022-12-13

EAN / UPC / JAN : 196803339895

End of Support : 2029-07-02



Premier Support - A direct 24x7x365 line to our most elite technicians.



Advanced technical support, 24x7x365, in more than 100 markets



Technical Account Managers for proactive relationship and escalation management



Comprehensive hardware & OEM software support



Priority on service delivery and repair parts



Single point of contact for simplified end-to-end case management



Lenovo Service Connect Portal for customized reporting and product support

Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty - Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades - Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.



Lenovo

PSREF
Product Specifications
Reference