

Safe-IT 5-Port Mobile Power Tower and USB Charging Station - USB-C 60W, 4x USB-A, 6x 5-15R, Wireless Charging, 1000 Joules, 10 ft. Cord, Antimicrobial Protection

MODEL NUMBER: TLM610CPAM



Features 5 USB charging ports, 6 AC outlets and 3 wireless pockets for keeping laptops, smartphones and other devices ready for use.

Features

Mobile USB Charging Station Powers and Charges up to 14 Devices at the Same Time

Move the power where you need it with this Mobile Power Tower and USB Charging Station. With its heavy-duty casters and flexible 10-foot power cord, the TLM610CPAM fits into any home or office workspace, as well as classrooms and conference rooms. It powers and charges up to 14 devices at the same time, including smartphones, tablets, laptops and e-readers. It doesn't require a computer, so you can take it anywhere AC power is available.

Provides Plenty of Power to Keep Your Devices at Capacity

Two USB-A ports provide a maximum of 5V 2.4A (12W) of power and two more USB-A ports provide up to 5A 2.1A (10.5W), enough for fast-charging most smartphones and tablets. One USB-C Quick Charge port provides up to 60W for battery-intensive devices like the MacBook Pro or Chromebook Pixel.

NEMA 5-15R Outlets Accept a Wide Range of Electronic Devices

Plug your computer, printer, wireless router, desk lamp or other home/office electronics into six NEMA 5-15R outlets to protect them against dangerous surges, spikes and line noise. A surge protection rating of 1000 joules defends your valuable electronic components. EMI/RFI filtering helps your connected equipment perform better and last longer.

Wireless Charging Pockets Deliver Power to Phones

Who wants to mess with tangled cables when you just want to charge your smartphone? Three Qi charging areas make the process easier by charging wirelessly. Just place your compatible phones and other devices inside the convenient pockets for rapid charging.

Antimicrobial Protection Helps Provide a Safer, Cleaner and Healthier Environment

The Safe-IT™ charging station features antimicrobial protection that helps resist the growth of bacteria, viruses, fungi, mold and mildew.

Highlights

- 5V USB-A ports (2x 2.4A, 2x 2.1A) provide charging power for smartphones and tablets
- USB-C Quick Charge port provides up to 60W of charging power to compatible devices
- 3 Qi wireless charging pockets avoid cable clutter when charging smartphones
- 1000 joules protect your valuable electronics against dangerous surges and spikes
- Antimicrobial protection helps resist the growth of bacteria, viruses, fungi, mold and mildew

Package Includes

- TLM610CPAM 5-Port Mobile Power Tower and USB Charging Station
- Owner's manual

Specifications

OVERVIEW	
UPC Code	037332271860
Product Type	Surge Protector
Charging Form Factor	Tower
Device Compatibility	Amazon Kindle; Laptop; Phone; Tablet
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Input Cord Gauge (AWG)	14
Maximum Surge Amps	1000
Input Plug Type	NEMA 5-15P
Input Cord Details	SJT
Input Cord Length (ft.)	10
Right-Angle Plug	No
Input Cord Length (m)	3.05
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	60 Hz
Output Receptacles	(6) 5-15R
Circuit Breaker (amps)	12
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	No
CHARGING	
Number of Charging Ports	4
Charging Method	USB
Charging Port Type	USB A (FEMALE)
Charging Ports / Amps	(2) 2.1A; (2) 2.4A; (3) 3.1A
Overcharge Protection	Yes
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	1000

AC Suppression Response Time	< 1ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression
UL1449 Let Through Rating	300,300,300
EMI / RFI Filtering	41.09dB
Immunity	Conforms to IEE 587/ANSI C62.41
Automatic Shut-Off	No
DATALINE SURGE SUPPRESSION	
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
Telephone/DSL Protection	No
PHYSICAL	
Material of Construction	steel
Power Cord Color	Black and White Braided Cord
Mounting Holes or Slots	Yes
Receptacle Color	Black
Shipping Dimensions (hwd / in.)	42.13 x 15.16 x 15.16
Shipping Dimensions (hwd / cm)	107.01 x 38.51 x 38.51
Shipping Weight (lbs.)	31.64
Shipping Weight (kg)	14.35
Unit Dimensions (hwd / in.)	39.700 x 12.900 x 12.990
Unit Dimensions (hwd / cm)	39.7 x 12.99 x 0.00
Unit Weight (lbs.)	1.8
Unit Weight (kg)	0.82
FEATURES & SPECIFICATIONS	
Antimicrobial	Yes
Rotatable Outlets	No
GaN Technology	No
STANDARDS & COMPLIANCE	
Product Certifications	CAN/CSA-C22.2 No. 60950-1 (Canada); NOM (Mexico); UL 60950-1
Product Compliance	FCC Part 15 Class B (USA); RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$50,000 Ultimate Lifetime Insurance
---	---