HSM Pure 320

Personal shredder

An asset for the office





- Personal/home office model designed for 1 to 3 users
- High quality materials and "Made in Germany" quality for security and durability
- Cutting rollers made of hardened steel with lifetime warranty
- Quiet operation minimizes noise development in the workplace
- Low power consumption in standby mode
- Paper feed with overload protection reduces paper jams
- Automatically switches off if pressure is applied to the safety element
- Light barrier for automatic start/stop
- Full bag indicator
- · Removable waste container for effortless emptying
- Timeless machine design in trendy white
- Uses an 11 gallon capacity shred bag; Part #HSM1310











| HSM Part# | HSM2331 | HSM2333 |
|------------------------------------|-----------------------|------------------------------|
| Cutting type | Strip cut | Cross cut |
| Cutting size | 1/4" | 1/8" x 1 1/8" |
| Security level DIN 32757-1 | 2 | 3 |
| Security level DIN 66399 | P-2 / O-2 / T-2 / E-2 | P-4 / T-4 / E-3 / F-1 |
| Cutting capacity per run in sheets | 16 - 18 | 8 - 9 |
| Cutting Speed | 9.8 ft / min | 9.8 ft / min |
| Throat opening | 9" | 9" |
| Motor power (horsepower) | 0.48 hp | 0.48 hp |
| Voltage | 115 V / 60Hz | 115 V / 60Hz |
| Dimensions (H x W x D) | 21.9" x 14.4" x 10" | 21.9" x 14.4" x 10" |
| Weight | 21.8 lbs | 24.25 lbs |
| Shred-bin volume | 6.6 gal | 6.6 gal |
| Cutting capabilities | MA TO THE CO | ^} <i>\phi</i> \mathred{\pi} |

All technical specifications are approximate values. Technical and design modifications reserved.

