


SmartRack Cable Entry Gland Plate for NEMA-Rated Enclosure Cabinets, 21-Port Membrane

MODEL NUMBER: **SRGP3RM**



Cable entry plate covers entry/exit cable cutouts on SmartRack NEMA 3R and NEMA 4 industrial enclosures.

Features

Gasketed Cable Entry Plate for NEMA-Rated Industrial Enclosures

This metal-reinforced gland plate covers cable entry and exit cutouts on SmartRack® NEMA 3R and NEMA 4 industrial enclosures, including the SRN and SRIN series. The SRGP3RM is sized to correspond to the enclosures' cable cutouts, making it quick and easy to install. Twenty-one ports accept a wide range of cable sizes, including 3 mm to 7 mm (14), 4 mm to 12 mm (six) and 16 mm to 27 mm (one). Membrane seals around non-terminated cables maintain the enclosure's NEMA 3R or NEMA 4 rating. Unused ports also are protected against dust and moisture.

Specifications

OVERVIEW	
UPC Code	037332262905
Accessory Type	Gland Plate
Accessory Class	Rack Accessories
PHYSICAL	
Total Number of Ports	21
Shipping Dimensions (hwd / in.)	2.87 x 8.37 x 15.75
Shipping Dimensions (hwd / cm)	7.30 x 21.27 x 40.00
Shipping Weight (lbs.)	2.43
Shipping Weight (kg)	1.11
Unit Dimensions (hwd / in.)	1.260 x 13.386 x 5.906

Highlights

- Rugged gasketed cable gland plate with metal reinforcement for long life
- Ideal for high-density cable installations and indoor or outdoor use
- Features 21 ports in various cable sizes ranging from 3 mm to 27 mm
- Membrane seals maintain NEMA rating of SmartRack industrial enclosure
- Unused ports are protected against dust and moisture

System Requirements

SmartRack NEMA 3R and NEMA 4 industrial enclosures

Package Includes

- SRGP3RM Cable Entry Plate
- (6) M5 screws
- Owner's manual

Unit Weight (lbs.)	2.00
Unit Weight (kg)	0.91
FEATURES & SPECIFICATIONS	
IP68 Rated	No
Outdoor Use	Yes
IP20 Rated	No
STANDARDS & COMPLIANCE	
Product Compliance	REACH; RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	2-year limited warranty