

NuScan 4300B Bluetooth/2.4GHz 2D Ring Wearable Barcode Scanner

www.adesso.com



■ Bluetooth® Wireless Technology

Connect the scanner to your iOS/Android device or PC with ease and enjoy scanning barcodes wirelessly up to 50 feet away.

■ Portable Ring Design

Weighing at less than 3 ounces, the NuScan 4300B is extremely light weight and portable, making it easily the perfect scanning solution wherever you go.

■ 2D Scanning Engine

The 2D scanning engine offers decoding capability for 2D barcodes like PDF417, Data Matrix, QR Code, MicroQR as well as common 1D barcodes.

■ Drop Protection

With its drop protection and rugged design, the NuScan 4300B can withstand accidental drops of up to 5 feet.

Superior Scanning Performance

Equipped with its CMOS sensor the device has a motion tolerance of 24 inches per second, offering fast and accurate scanning results.

Long Scanning Range

The 2D CMOS decoding engine is able to scan barcodes up to 12 inches scan depth.

Decoding Capabilities					
1D Barcodes	UPC/EAN/JAN, UPC/EAN with supplementary, JAN 8 & Jan 13, ISBN/ISSN, Code 39, ASCII, Codabar, Code 128, Code 93, Interleaved 2 of 5, Industrial 2 of 5, Standard 2 of 5, GS1 DataBar, Matrix 2 of 5.				
2D Barcodes	QR, Micro QR, PDF417, Datamatrix, Azetec, Matrix				







Portable



2D Scanning Engine



Specifications:

1280 x 800 CMOS Imager: **Light Source:** 650 ± 10 nm visible red LED & White Depth of Field: 0-12 inches (@20mil EAN-13, PC 100%) Roll: ±360°, Pitch: ±45°, Yaw: ±40° Scan Angle:

Motion Tolerance: 24 inches per second (IPS) Minimum Bar Width (1D): 5 mil/0.127 mm @ PCS 90%, Code 39 Minimum Bar Width (2D): 10 mil/0.254 mm @ PCS 80%, Data Matrix.

Print Contrast: PCS 30% EAN13 @10mil

15m / 50 ft. Wireless Range:

Bluetooth 5.0 Compliant Communication:

Indicators (LED):

Alert Operation: Programmable Beeper Tone

 $3.3 \pm 5\% \, VDC$ Input Voltage:

Operating Current: 132 ± 13 mA (at maximum)

Battery Capacity: Lithium Ion Battery Rated at 500mAH

EMC:

4.21 (L) x 1.89 (W) x 1.0 (H) in. (54 x 42 x 44 mm) Dimensions:

2.96 oz. (44 grams, excluding cable) Weight:

3'4" (1 meter)

Cable: Operating Temperature: -20°C to 50°C (-4°F to 122°F) Storage Temperature: -40°C to 70°C (-40°F to 158°F) Humidity: 5% to 95% (non-condensing)

Light Levels: Max 70.000 lux

Shock: Withstanding 1.5m freefall drops

Requirements:

Windows® 7 & above; Mac® OS X;iOS & Android Operating System: Bluetooth 4.2 or 2.4G Wireless (USB port required for Connectivity Interface: charging cable)

Includes:

Adesso NuScan 4300B Charging Cable Quick Start User Guide

Shipping Information:

ltem	UPC Code	Package Dimensions	Package Weight	Qty/ Carton
NuScan 4300B	783750012171	5.3" x 4.5" x 1.9"	0.17 lbs	10/40









