




**USE IT  
ANYWHERE,  
ANYTIME**



## **AVerVision A30**

All-Purpose Camera



The A30 is a multifunctional and all-in-one purpose camera. It's the first in the industry to feature a visualizer, microphone, and speaker in one device. At the same time, the A30 can be utilized as a webcam for video conferencing, and a document camera to visualize materials, providing the ultimate pleasure of hybrid/mobile teaching.



13 MP



4K Ultra HD



23X Digital Zoom



Microphone & Speaker



2nd Camera Support



Foldable Arm



HDMI & USB Outputs



AI Acoustics




AI Image Rotation



5-Year Warranty

## Absolute 4K Quality

The 13-megapixel camera delivers impressive resolution in 4K, making video capabilities impressive. Whether you take stills or videos, the A30 captures all the details perfectly.



## Diverse Camera Angles

A30's extendable arm can elongate and fold to capture people/document images via multiple angles. The adjustable camera head and rotatable base are also pluses, making the A30 even more video friendly.



## Dual Display Interface

The A30 has both HDMI and USB output ports for video streaming, moreover, teachers can connect to another USB camera for picture-in-picture image when using online teaching software.



## AI Acoustics

The integration of the camera, microphone and speaker efficiently provide teachers with an all-in-one teaching device. Teachers can enjoy the most peaceful teaching with the aid of AVer's AI Acoustics algorithm.



## AI Image Rotation

AVer's AI technology allows seamless experience in image capturing between people and document. Image flips automatically when uplifting the camera head, allowing teachers to always be seen in the correct direction.








## The Included AVerTouch Software Enhances Remote Teaching

Simply connect your A30 with one touch to immediately start sharing content and annotate as you go. With its easy and intuitive functions, as well as cloud sync to provide automatic backups of your annotations, captures, and recordings, this software will help enrich the overall teaching experience with unprecedented interactivity. You can take images and videos via Google Classroom by connecting A30 to the AVerTouch software.







With the A30, you can display...

-  Film slides / Filmstrips
-  Real-time movements
-  Documents
-  3D objects
-  X-rays



Show images to your audience through...

-  Interactive flat panel
-  TV monitor
-  Projection screen
-  Digital monitor

## Product Specifications

Image Sensor	1/3.06" CMOS	Built-in Mic	Yes
Total Pixels	13 Megapixels	Speaker	Yes
Output Resolution (via HDMI)	Up to 4K Ultra HD (3840 x 2160)	AI Acoustics	Yes (Acoustic Echo Cancellation (AEC) & Noise Suppression)
Output Resolution (via USB)	Up to 4K Ultra HD (3840 x 2160)	Security	Kensington Slot
TV Lines	1,200	Dimensions (W x D x H)	Operating: 96.9 x 239.0 x 348.4 mm Folded: 96.9 x 98.1 x 184.5 mm
Zoom	23X Digital Zoom	Net Weight	737 g (1.62 lbs)
Frame Rate	60fps (max.)	Power Source	DC 12V / 2A AC 100 to 240V, 50 / 60Hz
Focus	Auto / Manual (via AVerTouch)	Power Consumption	Lamp on: 15 Watts (max.) Lamp off: 14.5 Watts (max.)
Shooting Area	Larger than A3 Landscape	Warranty	Camera: 5 Years Accessories: 1 Year
Image Rotation	0° / 180°	Software	AVerTouch, Sphere Lite
AI Image Rotation	Yes (Automatic Flip)	Windows® OS	Windows® 7, 10, 11
Internal Storage	200 Pictures at XGA (1024 x 768)	Mac® OS	macOS® 10.15, 11, 12
External Storage	USB Thumb Drive (Up to FAT32 / 32 GB)	Chrome™ OS	Chrome™ OS 88 or Later (Available via the Sphere Lite App Only)
Image Effects	Color, B&W, Negative	Package Contents	AVerVision A30, USB Type-A to Type-C Cable, Power Adapter, Power Cord, Remote Control, QR Code Card
Image Adjustments (White Balance / Exposure)	Auto / Manual		
Display Modes	Normal, Motion, High Quality		
Light Source	Embedded LED Lamp		
HDMI I/O	1, HDMI out		
USB 2.0 Ports	Type-A x 1 (for USB Thumb Drive or 2 <sup>nd</sup> Camera Streaming Input) Type-C x 1 (for PC)		
Audio I/O	1, Line/Mic in (3.5 mm Stereo)		


\* Specifications may vary depending on location and are subject to change without notice.

## Product Appearance

Front



Left-Rear



Camera Head & Foldable Arm



©2023 AVer Information Inc. All rights reserved.  
All brand names and logos are trademarks of their respective companies.

www.aver.com



Learn More

Distributor/Dealer

202312