

Manufacturer Part #	TITANGT7713046
OS	Windows 11 Pro
CPU	Intel® Core™ i9-13980HX
CPU Speed	2.2-5.6 GHz
Chipset	-
Color	Core Black
Screen Size	17.3" UHD(3840x2160), 144Hz, Mini LED, HDR 1000, 100% DCI-P3, IPS-Level panel
Resolution	3840x2160 16:9
GPU	NVIDIA® GeForce RTX™ 4080 Laptop GPU
Video Memory	12G GDDR6
Keyboard	Cherry Mechanical KB SteelSeries per-Key RGB (99 Key)
Speaker	Sound by Dynaudio, 2x2 Speakers 2W x2W Woofer
Memory	64GB (32GB*2) DDR5 5600MHz
HDD Capacity	2TB NVMe SSD Gen4x4
HDD Interface	NVMe
LAN	Killer E3100G
WLAN	Killer WiFi 6E AX1690i
Bluetooth	BT 5.3
Card Reader	SD7.0
Webcam	IR 720p HD w/shutter
USB	3x USB 3.2 Gen 2
Type-C Port	2x Thunderbolt™ 4 w DP (1 also with PD)
Video Port	HDMI v2.1,
Audio Port	1 Audio Combo (1/8")
AC Power Adaptor	330W
Battery Pack	4 cell (99.9Whr) Li-Ion
Dimension	15.63"x 12.99"x 0.91"
Weight	7.28 lbs
Manufacturer Warranty	1 year Limited warranty (Include 1 Year Global)