

|                       |   |
|-----------------------|---|
| Manufacturer Part #   | RAIDERGE7813079   |
| OS                    | Windows 11 Pro  |
| CPU                   | Intel® Core™ i9-13980HX   |
| CPU Speed             | 2.2-5.6 GHz   |
| Chipset               | -   |
| Color                 | Dark Grey   |
| Screen Size           | 17" 16:10 QHD+(2560 x 1600), 240Hz, 100% DCI-P3, IPS-level panel  |
| Resolution            | 2560x1440<br>(16:10)  |
| GPU                   | NVIDIA® GeForce RTX™ 4090 Laptop GPU<br>Up to 2040MHz Boost Clock 175W Maximum Graphics Power with Dynamic Boost. *May vary by scenario<br><br>*Full-Power GPU Design |
| Video Memory          | 16G GDDR6   |
| Keyboard              | SteelSeries per-Key RGB with Anti-Ghost key (102 Key)   |
| Speaker               | Sound by Dynaudio, 2x2W Speaker, 4x2W Duo Wave Woofer   |
| Memory                | 32GB (16GB*2)<br>DDR5 4800MHz   |
| HDD Capacity          | 2TB NVMe SSD Gen4x4   |
| HDD Interface         | NVMe  |
| LAN                   | Killer E3100G   |
| WLAN                  | Killer WiFi 6E AX1690i  |
| Bluetooth             | BT 5.3  |
| Card Reader           | SD7.0   |
| Webcam                | 1080p FHD with shutter  |
| USB                   | 2x USB 3.2 Gen 2  |
| Type-C Port           | 1x Thunderbolt™ 4;<br>1x USB 3.2 Gen 2/DP;<br>1x USB 3.2 Gen 2/DP&PD  |
| Video Port            | HDMI v2.1,  |
| Audio Port            | 1 Audio Combo (1/8")  |
| AC Power Adaptor      | 330W  |
| Battery Pack          | 4 cell (99.9Whr) Li-Ion   |
| Dimension             | 14.97"x 11.73"x 1.13"   |
| Weight                | 6.83 lbs  |
| Manufacturer Warranty | 1 year Limited warranty (Include 1 Year Global)   |