

LED PICO+ Projector



New!!!




Wireless
Mirroring

Portable Mini Projector Watch Movie Anywhere, Anytime



RGB Vibrant
Color LEDs
30 Lumens



2 Hour
Battery (Eco)



720P Native
Resolution



Digital
Video Input



20,000 Hrs
LED Life



USB
Port



TF
Card



Ultra
Light Weight



PROJECTION SYSTEM:

Max Resolution:	1080P
Native Resolution:	1280 x 720 (720P)
Brightness (Boost Mode):	30 Lumens
Contrast Ratio:	1000 : 1
Projection Lens:	Manual Focus
Projection Image:	10 ~ 60 inches
Aspect Ratio:	16 : 9
Light Source:	RGB Vibrant Color LEDs 20,000 Hours

GENERAL SPECIFICATIONS:

Audio Output:	1W Speaker Stereo speaker / headphone mini-jack
Color:	White / Black
File Playback:	USB Memory Stick reader (up to 64GB) Micro SD/TF Card Reader (up to 32GB)
Menu Language:	English
Aspect Ratio Control:	16 : 9
Dimensions:	135mm x 70mm x 20mm
Weight:	0.5 lbs
Battery Size:	13 Watts
Battery Life (Eco Mode):	2 Hours
Supported Formats:	MP3 / WMA / OGG / WAV / AVI / JPG / GIF

INPUTS / OUTPUTS:

Video In:	Composite AV ,Mini-HDMI (Compatible);
Audio Out:	1080P
USB:	3.5mm Stereo Headphone Jack
USB Power Output:	Full Sized USB 2.0
SD Card:	5V 0.5A (2.5 Watts)

