



Redefining Focus

Intentionally crafted to deliver crisp visuals, personalized comfort, and true flexibility, the HP E24q G5 QHD Monitor redefines comfort, so there's nothing between you and your best. Stylishly designed with the planet in mind, this display is the perfect fit for both the office and home.



See it All, Do it All

When the difference is in the details, this 23.8-inch diagonal QHD monitor displays the clarity you need to stay focused on the task at hand. With rich 99% sRGB color depth and IPS technology^[1], you'll see clear, vivid colors across wide viewing angles^[2].

Bring Comfort to Work

When doing your best relies on feeling your best, it's easy to find all-day comfort with 4-way adjustability optimized by the step-by-step Ergonomic Setup Guide in HP Display Center^[3]. Help keep your eyes comfortable with a monitor that comes with flicker-free technology, a 75Hz refresh rate^[1] and HP Eye Ease, an always-on, built-in low-blue light filter.

Connect Intuitively

Work how you want with flexible connectivity and settings. Purposefully in reach, the accessible ports make connecting your devices quick and easy, while you effortlessly navigate your on-screen settings with the intuitive joystick OSD button.

Featuring

Ergonomic Setup Guide

Achieve all-day comfort when you apply the best practices from the Ergonomic Setup Guide. ^[3]

Enhanced Viewing Comfort with HP Eye Ease

Always-on, built-in, low-blue light filter that reduces blue light without the yellow color shift now enhanced with a 75Hz refresh rate. ^[1]

IPS Panel

No matter where you stand, IPS technology ensures image accuracy and consistency across wide, 178-degree horizontal and vertical viewing angles.

99% sRGB Color Space

Enjoy what you see on screen with 99% sRGB color space. This display provides ideal color reproduction for vibrant images and videos. ^[1]

Endless Adjustability

Work effortlessly with 4-way ergonomics that help keep your neck, shoulders, and back comfortable throughout the day. Customize pivot, tilt, 150 mm height adjust, and swivel settings to fit you, your desk, and your needs.

Specifications

Display size (diagonal)	23.8"
Panel technology	IPS
Aspect ratio	16:9 ^[1]
Native resolution	QHD (2560 x 1440) ^[1,2]
Resolutions supported	640 x 480; 720 x 400; 800 x 600; 1024 x 768; 1280 x 720; 1280 x 800; 1280 x 1024; 1440 x 900; 1600 x 900; 1600 x 1200; 1680 x 1050; 1920 x 1080; 1920 x 1200; 2560 x 1440
Pixel pitch	0.21 x 0.21 mm
Brightness	300 nits ^[1]
Contrast ratio	1000:1 ^[1]
Response time (typical)	5ms GtG (with overdrive) ^[1]
Minimum dimensions (W x D x H)	21.24 x 1.85 x 12.7 in (without hinge); 21.24 x 2.95 x 12.7 in (with hinge) (without stand)
Weight	12.83 lb (with stand)
Display features	On-screen controls; Anti-glare; Height Adjust/Tilt/Swivel/Pivot; HP Eye Ease
Onscreen controls	Management; Information; Exit; Input; Color; Image; Power; Menu; Brightness+
Display colors	Up to 16.7 million colors supported
Display scan frequency (horizontal)	30-115 kHz
Display scan frequency (vertical)	50-75 Hz
Power	100 - 240 VAC 50/60 Hz
Power consumption	56 W (maximum), 39 W (typical), 0.5 W (standby)
Operating temperature range	5 to 35°C
Operating humidity range	20 to 80% RH
Sustainable impact specifications	Low Halogen; Molded paper pulp cushion inside box is 100% sustainably sourced and recyclable; Outside box and corrugated cushions are 100% sustainably sourced and recyclable; Contains ocean-bound recycled plastic; 85% ITE-derived closed loop plastic; At least 25% recycled metal
Certifications and compliances	BIS; BSMI; CB; CCC; CE; CE Marking; CECP; CEL; CEL Grade 1; cTUVus; EAC; ENERGY STAR®; FCC; ISO 9241-307; KC/KCC; Microsoft WHQL Certification; NOM; PSB; SEPA; TCO Certified; TCO Certified Edge; TUV-S; VCCI; WEEE; ISC; eStandby; WW application; ICE; UAE; TGM; Ukraine certificates; NRCS; PSE; Hardware low blue light; GS
Physical security	Security lock-ready ^[11]
Management Software	HP Display Center; HP Display Manager
UPC number	196786298769
What's in the box	Monitor; DisplayPort™ cable; HDMI cable; Warranty card; USB Type-B to A cable; Quick Setup Poster; AC power cord ^[10]

Top Recommended Displays, Accessories and Services

No Top Recommended Displays, Accessories and Services

Messaging Footnotes

- [1] All performance specifications represent the typical specifications provided by HP's component manufacturers; actual performance may vary either higher or lower.
- [2] More accurate colors compared to 72% NTSC.
- [3] Ergonomic Setup Guide is available through HP Display Center. Host PC requires Windows 10 or higher. HP Display Center is available on the Microsoft store.

Technical Specifications Footnotes

- [1] All specifications represent the typical specifications provided by HP's component manufacturers; actual performance may vary either higher or lower.
- [2] DisplayPort™ 1.2 or HDMI 1.4 required to drive panel at its native resolution. The video card of the connected PC must be capable of supporting 2560 x 1440 at 60 Hz with 8-bit color using one DisplayPort™, HDMI. The video card of the connected PC must be capable of supporting 2560 x 1440 and include one DisplayPort™ or one HDMI outputs to drive the monitor at the preferred mode.
- [10] Included cables may vary by country.
- [11] Lock sold separately.

Learn more at
hp.com

© Copyright 2023 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

DisplayPort™ is a trademark owned by the Video Electronics Standards Association (VESA®) in the United States and other countries. USB Type-C® and USB-C® are registered trademarks of USB Implementers Forum. Microsoft, Encarta, MSN, and Windows are either registered trademarks or trademarks of Microsoft Corporation in the United States and/or other countries.

