



L A P T O P S

Raider GE78 HX 13V

RAIDER GE78HX 13VG-026CA

Specification

OS	Windows 11 Home
Color	Dark Grey
Screen Size / Type	17" 16:10 QHD+(2560 x 1600), 240Hz, 100% DCI-P3, IPS-level panel
Resolution/ Ratio	2560x1600 16:10
CPU/Processor	Intel® Core™ i7-13700HX
CPU Frequency	2.1-5.2 GHz
Chipset	Intel HM770
Graphics	NVIDIA® GeForce RTX™ 4070 Laptop GPU
Video Memory	8G GDDR6
System Memroy	DDR5 16GB*2
SoDimm	2 Sockets; Max Memory 64GB
HDD Capacity	1TB NVMe PCIe SSD
HDD Interface	NVMe
SSD	1 x NVMe M.2 SSD by PCIe Gen5 x4 1 x NVMe M.2 SSD by PCIe Gen4 x4
LAN	Killer E3100G
WLAN	Killer WiFi 6E AX1675(i)
BT	BT 5.2
Card Reader	SD7.0
HDMI-out	v2.1,
USB Type C	1x Thunderbolt™ 4; 1x USB 3.2 Gen 2/DP; 1x USB 3.2 Gen 2/DP&PD
USB	1x USB 3.2 Gen 2; 1x USB 3.2 Gen 1
Keyboard	SteelSeries per-Key RGB with Anti-Ghost key (99 Key)
Touch Pad	Multi Touch
Mic-in/ Headphone-out	1 Audio Combo (1/8")
Speaker	Sound by Dynaudio, 2x2W Speaker, 4x2W Duo Wave Woofer
Webcam	1080p FHD with shutter
Battery Pack	4 cell (99.9Whr) Li-Polymer
AC Adapter	280W
Unit weight	6.83 lbs
Unit Dimension	14.97"x 11.73"x 1.13"
UPC	824142316542
UCC-14	10824142316549
Warranty	1 year Limited warranty (Include 1 Year Global)