



## Modern 15 - B11M

MODERN 15 B11M-022US

## Specification

<b>Manufacturer Part #</b>	MOD1511022
<b>OS</b>	Windows 11 Pro
<b>CPU</b>	Intel® Core™ i7-1195G7
<b>CPU Speed</b>	2.9 - 5.0GHz
<b>Chipset</b>	-
<b>Color</b>	Classic Black
<b>Screen Size</b>	15.6" FHD, 60Hz 45%NTSC IPS-Level
<b>Resolution</b>	1920x1080 16:9
<b>GPU</b>	Intel® Iris® Xe
<b>Keyboard</b>	White backlight keyboard (84 Key)
<b>Speaker</b>	2x Speakers 2W
<b>Memory</b>	16GB (16GB*1) DDR4 3200MHz
<b>HDD Capacity</b>	1TB NVMe SSD
<b>HDD Interface</b>	NVMe
<b>LAN</b>	-
<b>WLAN</b>	Intel Wi-Fi 6 AX201(2*2 ax)
<b>Bluetooth</b>	BT 5.2
<b>Card Reader</b>	Micro SD
<b>Webcam</b>	720p HD Webcam
<b>USB</b>	1x USB 3.2 Gen 2; 2x USB 2.0
<b>Type-C Port</b>	1x USB 3.2 Gen 2 Type C
<b>Video Port</b>	HDMI HDMI 1.4 (4K @ 30Hz)
<b>Audio Port</b>	Mic-in/Headphone-out Combo
<b>AC Power Adaptor</b>	65W [DC-in]
<b>Battery Pack</b>	3 cell (39Whr) Li-Polymer
<b>Dimension</b>	14.05" x 9.20" x 0.67"
<b>Weight</b>	3.52 lbs
<b>Manufacturer Warranty</b>	3 year Limited warranty (Include 1 Year Global)