



TV-UVAWM

Universal VESA Articulating Wall Mount

For TVs and Monitors

Universal VESA Articulating Wall Mount for TVs and Monitors

This intuitive articulating wall mount offers flexibility and loads of viewing angles for home, conference rooms, offices, gyms, hospitality lobbies, and any place that needs a durable way to hang a screen. It's an ideal solution that can be hung on any studs, framing, drywall or solid wall. Screens can be seen from virtually any angle with not only three points of articulation, each with a 180-degree swivel, but also, a VESA head with +/-15-degree tilt capabilities and full rotation for use in portrait or landscape orientation. When the ideal angle is attained, simply lock in place by tightening a screw. The mount connects to monitors via standard VESA 75 x 75, 100 x 100, 200 x 100, or 200 x 200-millimeter plate, and holds screens up to 42 inches and 44 lbs. Cables can be neatly routed out of the way via clips at the bottom of the arms. This mount also has a slide-in VESA plate for quick attachment and detachment. For those looking for more secure placement, there is an optional anti-Theft Locking Hole for additional security preventing any unwanted removal (cable lock not included for this feature).



Features:

- Foldable compact mount arm
- 30-degree tilt adjustable at VESA joint
- Portrait to landscape orientation flexibility
- Cable routing clips beneath arm
- VESA-compatible 75 x 75, 100 x 100, 100 x 200, and 200 x 200-millimeter mount
- Swivel range at each hinge joint: 180-degrees
- Compatible monitors up to 42" and 44 lbs. rated

Specifications:

- Overall Dimensions: 16.4"x11.8"x8.7"
- Weight: 2 lbs.
- VESA max dimensions: 7.9" x 7.9"
- Wall canopy mount height: 6.2"

Package Includes:

- (1) Wall mount
- (1) Set tools and hardware



Multiple VESA Compliant



Portrait and Landscape Mounting



Adjustable Angles

	Quantity	Width	Height	Depth	Weight	UPC Barcode
Packaging	-	-	-	-	-	656777023515
Master	-	-	-	-	-	10656777023512