



OL10KRTHD | SMART APP ONLINE UPS SYSTEM


Safeguard mission-critical servers, applications, and network equipment with this space saving design and double-conversion power protection

The CyberPower Smart App Online OL10KRTHD high-density design offers more power in less space. In fact, it can be configured into 4U of rack space or as a tower, compared to 6U for similar competitive UPS models – giving you more room to grow. The OL10KRTHD features double-conversion topology for seamless power protection and a pre-installed RMCARD205.

For monitoring, this UPS offers a new state-of-the-art, multi-function, color matrix LCD screen that is simple to set up and easy to use. The color-coded alerts provide clear status of the UPS and the screen orientation rotates automatically when placed into a tower configuration.

The OL10KRTHD ensures maximum efficiency and capacity output with a Power Factor rating (PF) of one. The energy-saving GreenPower UPS™ ECO Mode enables > 98% efficiency while reducing power consumption and thermal dissipation. The variable seven-speed fan provides automatic thermal management, based on power load, to reduce noise.

The optional BP192VL2U01 Extended Battery Module (EBM) expands runtime and up to ten EBMs can be connected in a daisy-chain to the UPS for more backup power. Plus, it's all backed by a three-year warranty (including batteries) and a \$300,000 Connected Equipment Guarantee.



TYPICAL APPLICATIONS

- Core Network Equipment
- Hyperconverged Infrastructure (HCI)
- Server Rooms
- Server Virtualization Infrastructures
- Storage Systems
- VoIP Infrastructure
- Enterprise Servers
- Corporate Servers

FEATURES

- Capacity: 10,000 VA / 10,000 W
- High Density: 4U Size
- Power Factor (PF): 1
- Topology: Double-Conversion
- Waveform: Sine Wave
- Output: 200, 208, 220, 230, 240 VAC
User Configurable +/-2%
- Plug type: Hardwire
- Outlet types: 4 x NEMA L6-20R,
2 x NEMA L6-30R, Hardwire
- Communication Ports: USB, Serial, SNMP, EPO
- Management Software: PowerPanel® Business Edition
- Energy Saving: ECO Mode Efficiency >98%
- Warranty: Three-Year Limited

GENERAL	
Energy Saving	ECO Mode Efficiency > 98%
Energy Star Certified	Yes
UPS Topology	Online Double Conversion

INPUT	
Backfeed Protection	Yes
Circuit Breaker	70 A
Cold Start	Yes
Input Frequency Range	40 Hz to 70 Hz

OL10KRTHD | SMART APP ONLINE UPS SYSTEM

SPECIFICATIONS - CONT.

MANAGEMENT & COMMUNICATION	
Audible Alarms	Battery Mode Battery Low Overload UPS Fault
Dry Contacts	No
Emergency Power Off (EPO) Port	Yes
HID Compliant USB Port	Yes
LCD	Multifunction LCD
LED Indicators	Power On (White)
Management Cable	USB Cable
Removable LCD Control Panel Option	No
Rotatable LCD Control Panel Option	Yes
Serial Port	1 Serial
SNMP / HTTP Remote Monitoring	Yes - RMCARD205 pre-installed
Software (Free Download)	PowerPanel® Business Edition
PHYSICAL	
Chassis Color	Unpainted
Form Factor	Rack / Tower
Front Panel Color	Black
Material of Construction	Metal
Mounting Hardware	Yes

PHYSICAL DIMENSIONS	
Physical Dimensions - Width/Height/Depth (cm)	43.31 x 17.27 x 72.01 cm
Physical Dimensions - Width/Height/Depth (mm)	433 x 173 x 720 mm
Physical Dimensions - Width/Height/Depth (in.)	17.05 x 6.8 x 28.35 in.
Weight (kg)	71.21 kg
Weight (lb)	157 lbs.
SHIPPING DIMENSIONS	
Shipping Dimensions - Width/Height/Depth (cm)	59.94 x 45.21 x 88.9 cm
Shipping Dimensions - Width/Height/Depth (mm)	599 x 452 x 889 mm
Shipping Dimensions - Width/Height/Depth (in.)	23.23 x 17.8 x 35.04 in.
Shipping Weight (kg)	90.72 kg
Shipping Weight (lbs.)	200 lbs.
CERTIFICATIONS	
Safety	UL1778 CSA C22.2 No.107.3 FCC Part 15 Class A
Environmental	RoHS Compliant
WARRANTY	
Product Warranty	Three-Year Limited
Extended Warranty Option	WEXT5YR-U20B
Connected Equipment Guarantee	Lifetime
CEG Amount	\$300,000