




Let's Talk R230 Camera Specs

Ideal for flexible and temporary deployments



Camera starts at \$899

Rhombus 10-year Warranty included

- 5MP image sensor
2592 x 1944 resolution
- 1080 full HD recording
- 84.0° - 122.2° Diagonal FoV
74.6° - 110.1° Horizontal FoV
38.6° - 53.1° Vertical FoV
- 2.8 - 8mm focal length
- Up to 180 days of on-camera storage
- IP66 weather resistance
IK10 impact resistance
- Optional unlimited cloud archiving available

About the R230

No wired internet, no problem. The Rhombus R230 is a dome camera with built-in wifi capabilities and Rhombus Sensor Network compatibility. With simple setup, the R230 is flexible for deployments within range of a wifi signal.

Featuring a varifocal lens and 3X motorized zoom, users can adjust for optimal video recordings. The R230 delivers the perfect balance of performance and versatility, making it ideal for situations where running a dedicated internet line is unavailable.

Camera Specs

- WiFi:** 802.11ac, 802.11/g/n, 2.4Ghz and 5Ghz
- Night Vision:** Infrared illuminators (100ft in low light)
- Aperture:** f/1.6
- Pan / Tilt / Zoom:** Up to 2.8x optical zoom
- Ethernet:** 10 / 100Mbps
- Power-over-Ethernet:** Standard 802.3af for one-cable installation
- Power Consumption:** Max 9.4 watts
- Onboard Storage Included:** 128GB, 256GB, 512GB, or 1TB
- Dimensions:** 117mm (4.61in) x 83.5mm (3.29in)
- Operating Temperature:** -55° to 55°C (-67° to 131°F)
- Operating Humidity:** 10% - 90%, no condensation
- In the Box:** Mounting screws & anchors, RJ45 waterproofing grommet
- Baseline Steady State:** 10 - 30 Kbps per camera
- HD WAN Live Streaming:** 530 - 720 Kbps per camera
- FCC, CE, IC, RCM, UKCA, TAA Compliant**