



LATITUDE 5400, 5300 2-IN-1 CHROMEBOOK ENTERPRISE

# Latitude and Chrome Enterprise. Smarter together.



## TRUSTED LATITUDE WITH CHOICE OF CHROME ENTERPRISE

All the trusted Latitude features now with Chrome Enterprise. Versatility and performance meet a secure cloud-native experience with ProSupport. Set your team up anywhere with the widest global availability of any Chrome Enterprise devices.\* Designed for durability, withstanding 17 rigorous MIL-STD tests.



## START UP FAST, STAY UP & RUNNING LONGER

We offer three configurable battery options for the laptop, and two battery options for the 2-in-1. Plus, ExpressCharge™ can quickly charge your PC up to 80% in just one hour.



## SERVICEABLE, MOST POWERFUL 14” LAPTOP & 13” 2-IN-1 IN ITS CLASS\*\*

The only Chromebook Enterprise™ devices to offer options of 32GB memory, 512GB storage, and latest 8<sup>th</sup> Generation Intel® up to Core™ i7 processors for up to 3x faster app experience and up to 2x faster web browsing.\*\* Stay connected in areas without Wi-Fi with optional mobile broadband up to 450 Mbps. With our upgradeable and serviceable RAM, storage, battery and processor, you can easily customize for your business needs.



## MODERNIZE YOUR IT

Get quick and easy deployment, management, security, and support with Dell Technologies Unified Workspace and ProSupport. Add Drive Enterprise to streamline workflow with the collaboration features of Drive and tools like Docs, Sheets, Slides. Or simply upgrade to G Suite to have additional apps like Gmail and Hangouts at your fingertips.

# Recommended Accessories

LATITUDE 5400, 5300 2-IN-1 CHROMEBOOK ENTERPRISE

## ON-THE-GO



### DELL USB-C MOBILE ADAPTER | DA300

Connect your Latitude to almost any device with a convenient 6-in-1 compact adapter.



### DELL PRO BRIEFCASE 14 | PO1420C

With EVA foam cushioning the laptop vault of this dependable briefcase, you will securely protect your devices and other office essentials.



### DELL NOTEBOOK POWER BANK PLUS (18,000 MAH) | PW7015L

This lightweight and compact powerbank will keep your laptop or cellphone powered on-the-go without adding bulk to your bag.



### DELL WIRELESS MOUSE | WM326

Tidy up the cable clutter at your mobile workspace with this mouse. With up to 18 months of battery life, you can also enjoy reliable wireless performance, no matter where you are.

## AT THE DESK



### DELL DOCK | WD19

Work at full speed with Dell's powerful USB-C dock. Charge your system faster, support up to three displays and connect to your peripherals via a single cable.



### DELL ULTRASHARP 24 MONITOR | U2419H

Experience superb screen performance on this FHD monitor with a virtually borderless InfinityEdge, packaged in a sleek, space saving design.



### DELL WIRELESS KEYBOARD AND MOUSE COMBO | KM714

Give your workspace a modern and clean appearance with a stylish wireless keyboard and mouse that perfectly complements your PC.



### DELL DUAL MONITOR STAND | MDS19

This space-saving stand, mounts up to two 27-inch monitors, providing the screen real estate you need to be most productive.



### DELL PRO STEREO HEADSET | UC350

Hear every word clearly on your next call with the Dell Pro Stereo Headset, optimized to provide in-person call quality and certified for Microsoft Skype for Business.

# Built for business

## Modernize your IT with Dell Technologies Unified Workspace & Chrome Enterprise

Dell Technologies Unified Workspace is the most comprehensive solution to deploy, secure, manage and support virtually all devices from the cloud. We designed this revolutionary solution with intelligence and automation providing you with visibility across the entire endpoint environment. We help you save time, improve user experience, optimize resources and strengthen security.




### DEPLOY

Experience seamless deployment of Chromebooks into any environment. Custom Configuration Services are aligned to meet the needs of Chrome Enterprise solutions including asset tagging, laser etching and enrollment.



### SECURE

Latitude Chromebook Enterprise devices are secure by design with a read-only OS, Verified Boot, two versions of the Chrome OS in the event of security compromises, encrypted partition of data, sandboxing, and ephemeral mode for safe browsing.



### MANAGE

Deliver an intelligent, unified management experience across all your devices with Dell and VMware Workspace ONE.



### SUPPORT

Leverage ProSupport Plus for predictive, proactive and automated maintenance and 24/7 access to ProSupport Engineers who contact you when critical issues arise, so you can focus on your business.

# Features & Technical Specifications

## LATITUDE 5400, 5300 2-IN-1 CHROMEBOOK ENTERPRISE

Feature	Technical Specifications	Feature	Technical Specifications
<b>Model Number<sup>1</sup></b>	5300 2-in-1 Chrome	<b>Model Number<sup>1</sup></b>	5400 Chrome
<b>Processor Options<sup>1</sup></b>	8 <sup>th</sup> Generation Intel® Core™ Processors up to i7 4-Core	<b>Processor Options<sup>1</sup></b>	8 <sup>th</sup> Generation Intel® Core™ Processors up to i7 4-Core
<b>Operating System<sup>1</sup></b>	Google® Chrome	<b>Operating System<sup>1</sup></b>	Google® Chrome
<b>Memory Options<sup>1,2,3</sup></b>	DDR4 2666 MHz Non-ECC SDRAM operates at 2400 MHz with Intel® 8 <sup>th</sup> Generation Core i processors 2 slots supporting up to 32GB	<b>Memory Options<sup>1,2,3</sup></b>	DDR4 2666 MHz Non-ECC SDRAM operates at 2400 MHz with Intel® 8 <sup>th</sup> Generation Core i processors 2 slots supporting up to 32GB
<b>Chipset<sup>1</sup></b>	Integrated with the Processor	<b>Chipset<sup>1</sup></b>	Integrated with the Processor
<b>Intel Responsiveness Technologies<sup>1,7</sup></b>	Intel® Rapid Storage Technology	<b>Intel Responsiveness Technologies<sup>1,7</sup></b>	Intel® Rapid Storage Technology
<b>Graphics<sup>1,13</sup></b>	Intel® UHD Graphics 620 and 610 (Celeron Option)	<b>Graphics<sup>1,13</sup></b>	Intel® UHD Graphics 620 and 610 (Celeron Option)
<b>Display<sup>1</sup></b>	13.3" FHD WVA (1920 x 1080) Touch with Edge-to-Edge Gorilla Glass, Anti Glare, Anti Smudge, 255 Nits, Pen Support, Carbon Fiber Reinforced Polymer LCD Back	<b>Display<sup>1</sup></b>	14.0" HD (1366 x 768) Anti-glare (16:9) WLED, 220 nits, non-touch, Carbon Fiber Reinforced Polymer LCD Back 14.0" FHD WVA (1920 x 1080) Antiglare (16:9) WLED, 220 nits, non-touch, Carbon Fiber Reinforced Polymer LCD Back
<b>Storage Options<sup>1,3</sup></b>	SSD M.2 2230 PCIe/NVMe: up to 512GB	<b>Storage Options<sup>1,3</sup></b>	64GB eMMc up to 512GB SSDM.2 2230 PCIe/NVMe
<b>Security<sup>1</sup></b>	H1 TPM Nobel Wedge Lock Slot Optional Dell Data Security and Management Google® Chrome Enterprise Upgrade with Console VMware Workspace ONE Dell Data Guardian Cloud	<b>Security<sup>1</sup></b>	H1 TPM Nobel Wedge Lock Slot Optional Dell Data Security and Management Google® Chrome Enterprise Upgrade with Console VMware Workspace ONE Dell Data Guardian Cloud
<b>Docking<sup>1</sup></b>	Dell Dock- WD19 (optional, sold separately)	<b>Docking<sup>1</sup></b>	Dell Dock- WD19 (optional, sold separately)
<b>Optical Drive Options</b>	External Options Only	<b>Optical Drive Options</b>	External Options Only
<b>Multimedia<sup>1</sup></b>	High Quality Speakers Universal Audio jack Noise reducing dual array microphones HD RGB camera	<b>Multimedia<sup>1</sup></b>	High Quality Speakers Universal Audio jack Noise reducing array microphones HD RGB Camera with Dell Privacy Shutter
<b>Battery Options<sup>1,5</sup></b>	3 cell 42 WHr ExpressCharge™ Capable Battery 4 cell 60 WHr ExpressCharge™ Capable Battery 4 cell 60 WHr Long Life Battery (includes 3yr limited hardware warranty)	<b>Battery Options<sup>1,5</sup></b>	3 cell 42 WHr ExpressCharge™ Capable Battery (UMA only) 3 cell 51 WHr ExpressCharge™ Capable Battery 4 cell 68 WHr ExpressCharge™ Capable Battery 4 cell 68 WHr Long Life Battery (includes 3yr limited hardware warranty)
<b>Power Options<sup>1</sup></b>	65W adapter, 7.4mm barrel 65W BFR/PVC Halogen Free adapter, 7.4mm barrel 90W adapter, 7.4mm barrel 65W adapter, Type-C	<b>Power Options<sup>1</sup></b>	65W adapter, 7.4mm barrel 65W BFR/PVC Halogen Free adapter, 7.4mm barrel 90W adapter, 7.4mm barrel 65W adapter, Type-C 90W adapter, Type-C
<b>Connectivity options<sup>1,14</sup></b>	10/100/1000 Ethernet Intel® Dual-Band Wireless-AC 9560 Wi-Fi + Bluetooth 5.0 Wireless Card (2x2) Optional Mobile Broadband Options: <sup>8,10</sup> Intel XMM 7360 Global LTE-Advanced	<b>Connectivity options<sup>1,14</sup></b>	10/100/1000 Ethernet Intel® Dual-Band Wireless-AC 9560 Wi-Fi + Bluetooth 5.0 Wireless Card (2x2) Optional Mobile Broadband Options: <sup>8,10</sup> Intel XMM 7360 Global LTE-Advanced
<b>Ports, Slots &amp; Chassis<sup>1</sup></b>	1x USB Type C™ 3.1 Gen 2 with Power Delivery & DisplayPort 2x USB 3.1 Gen 1 (one with PowerShare) 1x HDMI 1.4 1x external uSIM card tray option 1x uSD 4.0 Memory card reader Noble Wedge Lock slot		



# Features & Technical Specifications

## LATITUDE 5400, 5300 2-IN-1 CHROMEBOOK ENTERPRISE

Feature	Technical Specifications	Feature	Technical Specifications
<b>Dimensions &amp; Weight</b> <sup>1,15</sup>	Width: 12.0" / 305.7mm Height: 0.66" / 16.9mm (front), 0.76" / 19.3mm (rear) Depth: 8.16" / 207.5mm Starting weight: 3.0 lbs. / 1.36kg (42Whr battery, M.2 SSD)	<b>Ports, Slots &amp; Chassis</b> <sup>1</sup>	1x USB Type C™ 3.1 Gen 2 with Power Delivery & DisplayPort 3x USB 3.1 Gen 1 (one with PowerShare) 1x HDMI 1.4 1x RJ-45 1x external uSIM card tray option 1x uSD 4.0 Memory card reader Noble Wedge Lock slot
<b>Regulatory and Environmental Compliance</b> <sup>1</sup>	Regulatory Model: P96G Regulatory Type: P96G002 ENERGY STAR EPEAT Registered. For specific country participation and rating, please see <a href="http://www.epeat.net">www.epeat.net</a> BFR/PVC free <sup>9</sup>	<b>Dimensions &amp; Weight</b> <sup>1,15</sup>	Width: 12.7" / 323.05mm Height (Non-Touch): 0.77" / 19.6mm (front) 0.82" / 20.85mm (rear) Depth: 8.5" / 216mm Starting weight: 3.24 lbs / 1.47 kg (42Whr battery, M.2 SSD, non touch FHD LCD, UMA)*
<b>Input</b> <sup>1</sup>	Single Pointing backlit Keyboard, Spill Resistant Touchpad	<b>Regulatory and Environmental Compliance</b> <sup>1</sup>	Regulatory Model: P96G Regulatory Type: P96G005 ENERGY STAR EPEAT Registered. For specific country participation and rating, please see <a href="http://www.epeat.net">www.epeat.net</a> BFR/PVC free <sup>9</sup>
<b>Systems Management</b> <sup>1</sup>	Google Chrome Management Console® (Tied to Chrome Enterprise Upgrade)	<b>Input</b> <sup>1</sup>	Single Pointing Non-Backlit Keyboard, Spill Resistant Single Pointing backlit Keyboard, Spill Resistant Touchpad
<b>Warranty and Service</b> <sup>1</sup>	Limited Hardware Warranty <sup>4</sup> Standard 1 year Mail-in Service after Remote Diagnosis <sup>11</sup> optional 2, 3, 4 and 5 year hardware warranty extensions and 3-5 year Dell ProSupport contracts available <sup>12</sup>	<b>Systems Management</b> <sup>1</sup>	Google Chrome Management Console® (Tied to Chrome Enterprise Upgrade)
<b>Peripheral Ecosystem</b> <sup>1</sup>	Purpose built ecosystem to enable productivity on the go or at the desk. Includes Dell Business Dock-WD19, Dell Power Companions, Dell Professional Briefcases, Dell 24" & 27" Monitors, and Dell Wireless Keyboard and Mouse, 90W Type-C Adapter	<b>Warranty and Service</b> <sup>1</sup>	Limited Hardware Warranty <sup>4</sup> Standard 1 year Mail-in Service after Remote Diagnosis <sup>11</sup> optional 2, 3, 4 and 5 year hardware warranty extensions and 3-5 year Dell ProSupport contracts available <sup>12</sup>
		<b>Peripheral Ecosystem</b> <sup>1</sup>	Purpose built ecosystem to enable productivity on the go or at the desk. Includes Dell Business Dock-WD19, Dell Power Companions, Dell Professional Briefcases, Dell 24" & 27" Monitors, and Dell Wireless Keyboard and Mouse, 90W Type-C Adapter



LATITUDE 5400, 5300 2-IN-1 CHROMEBOOK ENTERPRISE

# Latitude and Chrome Enterprise. Smarter together.

1 Offering may vary by country and by configuration

2 A 64-bit operating system is required to support 4GB or more of system memory.

3 GB means 1 billion bytes and TB equals 1 trillion bytes; actual capacity varies with preloaded material and operating environment and will be less.

4 Limited Hardware Warranty: For copy of Limited Hardware Warranty, write Dell USA LP, Attn: Warranties, One Dell Way, Round Rock, TX 78682 or see [www.dell.com/warranty](http://www.dell.com/warranty)

5 Battery support is dependent upon graphics support. Check technical guides for detailed support

6 COMPUTRACE Not a Dell offer. Certain conditions apply. For full details, see terms and conditions at [www.absolute.com/en/about/legal/agreements](http://www.absolute.com/en/about/legal/agreements). 7 Intel Rapid Storage Technology requires a HDD, mSATA, or an SSD, as primary storage device and Windows OS required

8 Wireless antenna available only at time of system purchase

9 Dell Latitude 5000 Series are brominated flame retardant free (BFR-free) and polyvinyl chloride free (PVC-free); meeting the definition of BFR-/PVC-free as set forth in the INEMI Position Statement on the 'Definition of Low-Halogen Electronics (BFR-/CFR-/PVC-free)'. Plastic parts contain less than 1,000 ppm (0.1%) of bromine (if the Br source is from BFRs) and less than 1,000 ppm (0.1%) of chlorine (if the Cl source is from CFRs or PVC or PVC copolymers). All printed circuit board (PCB) and substrate laminates contain bromine/chlorine total less than 1,500 ppm (0.15%) with a maximum chlorine of 900 ppm (0.09%) and maximum bromine being 900 ppm (0.09%).

10 Mobile Broadband Subject to service provider's broadband subscription and coverage area; additional charges apply.

11 Mail-in Service after Remote Diagnosis: Remote Diagnosis is determination by online/phone technician of cause of issue; may involve customer access to inside of system and multiple or extended sessions. If issue is covered by Limited Hardware Warranty ([www.dell.com/warranty](http://www.dell.com/warranty)) and not resolved remotely, technician and/or part will be dispatched, usually within 1 business day following completion of Remote Diagnosis. Availability varies. Other conditions apply.

12 Dell Services: Availability and terms of Dell Services vary by region. For more information, visit [www.dell.com/servicesdescriptions](http://www.dell.com/servicesdescriptions).

13 GB means 1 billion bytes and TB equals 1 trillion bytes; significant system memory may be used to support graphics, depending on system memory size and other factors. 15 \*Weights vary depending on configuration and manufacturing variability.

\* Based on Dell Footprint Area (X \* Y) internal analysis, June 2019

\*\* When equipped with Intel® Core i7 8665U processor with Integrated UHD 620 graphics, 32GB of DDR4 2400MHz memory capacity and 256 GB PCIe NVMe SSD storage. Based on Dell internal analysis of competitive Chromebook Enterprise devices, June 2019.

+ Based on Dell internal analysis, June 2019. Mobile Broadband: Subject to service provider's broadband subscription and coverage area; speeds may vary. Additional charges will apply. Contact your service provider for details.

++ Based on Intel testing in June 2019 using Google Drive application and Speedometer v2.0 benchmark on the Dell Latitude 5400 & 5300 2-in-1 Chromebook Enterprise equipped with Intel Core i7-8665U processor compared to the same systems with Intel Celeron N4305U. Actual performance will vary.

· Open Sheets File using Google Drive: measures the time it takes to open a large .xls file using the Google Drive application on Chromebook.

· Speedometer v2.0 (overall score): It tests a browser's Web app responsiveness by timing simulated user interactions. This benchmark simulates user actions for adding, completing, and removing to-do items using multiple examples in TodoMVC.